



THOMAS
LIGHTING



Catalog 9002



Thank you for considering our products; we hope that your selection proves to be a brilliant addition to your surroundings!

Our award winning team of international designers and engineers are visionary in their thinking, constantly striving to uncover the styles of the future while revitalizing themes from the past. They challenge convention in the search for designs that prompt emotions of nostalgia, tranquility and inspiration.

With the design collaboration of our companies – the unencumbered elegance of Thomas Lighting, the European design influences of ELK Lighting, the exquisite details of our Dimond Home lamp and decor company, the heritage collection of quality furniture from GuildMaster, to the aspirational elements of our Sterling home furnishings line – all of these creative threads converge into an array of complimentary home furnishing options.

We invite you to explore the websites listed on our back cover for a glimpse at our entire array of distinctive products, which are crafted to exceptionally high standards of quality, innovation, and design.

With sincerest gratitude,

A handwritten signature in black ink that reads "Bradford Smith".

BRADFORD SMITH
Chief Executive Officer
ELK Group International

A DIVISION OF



PERMANENT SHOWROOMS

Atlanta ♦ Dallas ♦ High Point ♦ Las Vegas ♦ New York
Toronto ♦ Hong Kong



CONTENTS

4 COLLECTIONS

118 PENDANTS

144 FOYER

152 CEILING

172 WALL SCONCES

186 BATH

248 TASK LIGHTING

264 RECESSED

274 STEP LIGHTING

286 OUTDOOR

324 INDEX



symbol denotes up or down mounting



symbol denotes wet location tolerable




symbol denotes an Energy Efficient Product



symbol denotes items that are compliant with the Americans with Disabilities requirements.



symbol denotes damp location tolerable



ALLURE 50



ARLINGTON 70



BECKETT 8



BELLA 66



BELLINGHAM 72



BRIGHTON 74



BRISTOL LANE 36



CASUAL MISSION 12



CHARLESTON 24



CHATHAM 112



CONWAY 90



ECLIPSE 82



FARMINGTON 25



GEORGETOWN 16



HARMONY 26



HAVEN 96

COLLECTIONS QUICK FIND



JACKSON 108



PARK CITY 6



PENDENZA 52



PITTMAN 57



PRESTIGE 30



RIVA 78



SANTE FE 44



TAHOE 62



TIA 86



TREME 100



TRIBECCA 47



TRITON 40



WHITMORE 94



WILLIAMSPORT 18



WRIGHT 104

COLLECTIONS QUICK FIND

COLLECTIONS





COLLECTIONS

CN160821

8 light chandelier in Oil Rubbed Bronze & Wood Grain

36"W x 38"H
8 lights x 100W Med
99" Overall height
{12' wire} {60" chain}

- light beige scavo glass



CN160521

5 light chandelier in Oil Rubbed Bronze & Wood Grain

25"W x 25"H
5 lights x 100W Med
86" Overall height
{12' wire} {60" chain}

- light beige scavo glass



CN160231

2 light flush mount in Oil Rubbed Bronze & Wood Grain

13"W x 6"H
2 lights x 60W Med

- light beige scavo glass



CN160321

3 light chandelier in Oil Rubbed Bronze & Wood Grain

19"W x 21"H
3 lights x 100W Med
82" Overall height
{12' wire} {60" chain}

- light beige scavo glass



CN160381

3 light pendant/semi flush dual mount in Oil Rubbed Bronze & Wood Grain

16"W x 13"H
3 lights x 100W Med
74" Overall height
{12' wire} {60" chain}

- light beige scavo glass



CN160151

1 light mini pendant in Oil Rubbed Bronze & Wood Grain

5"W x 8"H
1 light x 100W Med
44" Overall height
{12' wire} {60" chain}

- light beige scavo glass



PARK CITY

CN160171

1 light wall sconce in Oil Rubbed Bronze & Wood Grain

5"W x 7"H x 7"EXT

1 light x 60W MED

- light beige scavo glass

**CN160211**

2 light bath bar in Oil Rubbed Bronze & Wood Grain

14"W x 7"H x 7"EXT

2 lights x 60W MED

- light beige scavo glass

**CN160311**

3 light bath bar in Oil Rubbed Bronze & Wood Grain

22"W x 7"H x 7"EXT

3 lights x 60W MED

- light beige scavo glass

**CN160411**

4 light bath bar in Oil Rubbed Bronze & Wood Grain

30"W x 7"H x 7"EXT

4 lights x 60W MED

- light beige scavo glass



CN129821

5 light chandelier in Oil Rubbed Bronze
37"W x 23"H
8 lights x 60W MED **shown Bulb 1092***
84" Overall height
{12' wire} {60" chain}

- clear glass

**not included-See page 324*



CN129281

3 light pendant/semi flush dual mount in Oil Rubbed Bronze
14"W x 7"H
3 lights x 60W MED **shown Bulb 1092***
68" Overall height
{12' wire} {60" chain}

- clear glass

**not included-See page 324*




CN129521

5 light chandelier in Oil Rubbed Bronze
26"W x 16"H
5 lights x 60W MED **shown Bulb 1092***
77" Overall height
{12' wire} {60" chain}

- clear glass

**not included-See page 324*



CN129231

2 light flush mount in Oil Rubbed Bronze
14"W x 7"H
2 lights x 60W MED **shown Bulb 1092***

- clear glass

**not included-See page 324*



CN129321

3 light chandelier in Oil Rubbed Bronze
22"W x 16"H
3 lights x 60W MED **shown Bulb 1092***
77" Overall height
{12' wire} {60" chain}

- clear glass

**not included-See page 324*




CN129041

1 light pendant in Oil Rubbed Bronze
12"W x 13"H
1 light x 60W MED **shown Bulb 1092***
74" Overall height
{12' wire} {60" chain}

- clear white glass

**not included-See page 324*



CN129151

1 light mini pendant in Oil Rubbed Bronze
6"W x 7"H
1 light x 60W MED **shown Bulb 1092***
68" Overall height
{12' wire} {60" chain}

- clear glass

**not included-See page 324*



CN129121



1 light wall sconce in Oil Rubbed Bronze
6"W x 12"H x 7"EXT
1 light x 60W MED **shown Bulb 1092***
• clear glass
**not included—See page 324*



CN129211



2 light bath bar in Oil Rubbed Bronze
15"W x 11"H x 7"EXT
2 lights x 60W MED **shown Bulb 1092***
• clear glass
**not included—See page 324*



CN129311



3 light bath bar in Oil Rubbed Bronze
24"W x 11"H x 7"EXT
3 lights x 60W MED **shown Bulb 1092***
• clear glass
**not included—See page 324*



CN129411



4 light bath bar in Oil Rubbed Bronze
33"W x 11"H x 7"EXT
3 lights x 60W MED **shown Bulb 1092***
• clear glass
**not included—See page 324*



CN120821

8 light chandelier in Oil Rubbed Bronze
 37"W x 23"H
 8 lights x 60W MED*
 84" Overall height
 {12' wire} {60" chain}

- opal white glass

*not included—See page 324



CN120281

3 light pendant/semi flush dual mount in Oil Rubbed Bronze
 14"W x 7"H
 3 lights x 60W MED*
 68" Overall height
 {12' wire} {60" chain}

- opal white glass

*not included—See page 324



CN120521

5 light chandelier in Oil Rubbed Bronze
 26"W x 16"H
 5 lights x 60W MED*
 77" Overall height
 {12' wire} {60" chain}

- opal white glass

*not included—See page 324



CN120231

2 light flush mount in Oil Rubbed Bronze
 14"W x 7"H
 2 lights x 60W MED*
 • opal white glass

*not included—See page 324



CN120321

3 light chandelier in Oil Rubbed Bronze
 22"W x 16"H
 3 lights x 60W MED*
 77" Overall height
 {12' wire} {60" chain}

- opal white glass

*not included—See page 324




CN120041

1 light pendant in Oil Rubbed Bronze
 12"W x 13"H
 1 light x 60W MED*
 74" Overall height
 {12' wire} {60" chain}

- opal white glass

*not included—See page 324



CN120151

1 light mini pendant in Oil Rubbed Bronze
 6"W x 7"H
 1 light x 60W MED*
 68" Overall height
 {12' wire} {60" chain}

- opal white glass

*not included—See page 324



CN120121

1 light wall sconce in Oil Rubbed Bronze
 6"W x 12"H x 7"EXT
 1 light x 60W MED*
 • opal white glass
 *not included—See page 324

**CN120211**

2 light bath bar in Oil Rubbed Bronze
 15"W x 11"H x 7"EXT
 2 lights x 60W MED*
 • opal white glass
 *not included—See page 324

**CN120311**

3 light bath bar in Oil Rubbed Bronze
 24"W x 11"H x 7"EXT
 3 lights x 60W MED*
 • opal white glass
 *not included—See page 324

**CN120411**

4 light bath bar in Oil Rubbed Bronze
 33"W x 11"H x 7"EXT
 3 lights x 60W MED*
 • opal white glass
 *not included—See page 324



CN170922

9 light chandelier in Brushed Nickel
 29"W x 28"H
 9 lights x 100W Med
 89" Overall height
 {12" wire} {60" chain}
 • white lined glass

**CN170522**

5 light chandelier in Brushed Nickel
 22"W x 23"H
 5 lights x 100W Med
 84" Overall height
 {12" wire} {60" chain}
 • white lined glass

**CN170342**

3 light chandelier in Brushed Nickel
 21"W x 26"H
 3 lights x 100W Med
 87" Overall height
 {12" wire} {60" chain}
 • white lined glass

**CN170322**

3 light chandelier in Brushed Nickel
 17"W x 19"H
 3 lights x 100W Med
 80" Overall height
 {12" wire} {60" chain}
 • white lined glass

**CN170382**

3 light semi flush in Brushed Nickel
 20"W x 12"H
 3 lights x 100W Med
 • white lined glass

**CN170332**

3 light flush mount in Brushed Nickel
 13"W x 7"H
 3 lights x 60W Med
 • white lined glass

**CN170152**

1 light mini pendant in Brushed Nickel
 5"W x 7"H
 1 light x 100W Med
 44" Overall height
 • white lined glass

**CASUAL MISSION**

CN170172

1 light wall sconce in Brushed Nickel
5"W x 8"H x 6"EXT
1 light x 60W MED
• white lined glass

**CN170212**

2 light bath bar in Brushed Nickel
12"W x 9"H x 6"EXT
2 lights x 60W MED
• white lined glass

**CN170312**

3 light bath bar in Brushed Nickel
20"W x 9"H x 6"EXT
3 lights x 60W MED
• white lined glass

**CN170412**

4 light bath bar in Brushed Nickel
28"W x 9"H x 6"EXT
4 lights x 60W MED
• white lined glass



CN170921

9 light chandelier in Oil Rubbed Bronze
 29"W x 28"H
 9 lights x 100W Med
 89" Overall height
 {12' wire} {60" chain}
 • white lined glass

**CN170521**

5 light chandelier in Oil Rubbed Bronze
 22"W x 23"H
 5 lights x 100W Med
 84" Overall height
 {12' wire} {60" chain}
 • white lined glass

**CN170341**

3 light chandelier in Oil Rubbed Bronze
 21"W x 26"H
 3 lights x 100W Med
 87" Overall height
 {12' wire} {60" chain}
 • white lined glass

**CN170321**

3 light chandelier in Oil Rubbed Bronze
 17"W x 19"H
 3 lights x 100W Med
 80" Overall height
 {12' wire} {60" chain}
 • white lined glass

**CN170381**

3 light semi flush in Oil Rubbed Bronze
 20"W x 12"H
 3 lights x 100W Med
 • white lined glass

**CN170331**

3 light flush mount in Oil Rubbed Bronze
 13"W x 7"H
 3 lights x 60W Med
 • white lined glass

CN170151

1 light mini pendant in Oil Rubbed Bronze
 5"W x 7"H
 1 light x 100W Med
 44" Overall height
 • white lined glass

**CASUAL MISSION**

CN170171

1 light wall sconce in Oil Rubbed Bronze
 5"W x 8"H x 6"EXT
 1 light x 60W MED
 • white lined glass

**CN170211**

2 light bath bar in Oil Rubbed Bronze
 12"W x 9"H x 6"EXT
 2 lights x 60W MED
 • white lined glass

**CN170311**

3 light bath bar in Oil Rubbed Bronze
 20"W x 9"H x 6"EXT
 3 lights x 60W MED
 • white lined glass

**CN170411**

4 light bath bar in Oil Rubbed Bronze
 28"W x 9"H x 6"EXT
 4 lights x 60W MED
 • white lined glass



CN230927

9 light chandelier in Weathered Zinc
36"W x 35"H
9 lights x 100W Med*
96" Overall height
{12' wire} {60" chain}
• mercury glass
*not included-See page 324



CN230527

5 light chandelier in Weathered Zinc
27"W x 27"H
5 lights x 100W Med*
88" Overall height
{12' wire} {60" chain}
• mercury glass
*not included-See page 324



CN230157

1 light mini pendant in Weathered Zinc
6"W x 8"H
1 light x 100W Med*
61" Overall height
{12' wire} {60" chain}
• mercury glass
*not included-See page 324



CN230327

3 light chandelier in Weathered Zinc
23"W x 25"H
3 lights x 100W Med*
86" Overall height
{12' wire} {60" chain}
• mercury glass
*not included-See page 324



CN230387

3 light semi flush in Weathered Zinc
19"W x 16"H
3 lights x 100W Med*
• mercury glass
*not included-See page 324



CN230237

2 light flush mount in Weathered Zinc
16"W x 9"H
2 lights x 60W Med*
• mercury glass
*not included-See page 324



GEORGETOWN

CN230177

1 light wall sconce in Weathered Zinc
 6"W x 12"H x 8"EXT
 1 light x 60W MED*

- mercury glass

**not included-See page 324*

**CN230217**

2 light bath bar in Weathered Zinc
 16"W x 11"H x 7"EXT
 2 lights x 60W MED*

- mercury glass

**not included-See page 324*

**CN230317**

3 light bath bar in Weathered Zinc
 24"W x 12"H x 7"EXT
 3 lights x 60W MED*

- mercury glass

**not included-See page 324*

**CN230417**

4 light bath bar in Weathered Zinc
 33"W x 13"H x 7"EXT
 4 lights x 60W MED*

- mercury glass

**not included-See page 324*



1529CH/20

9 light chandelier in Brushed Nickel
34"W x 29"H
9 lights x 60W CAND
90" Overall height
{12' wire} {60" chain}



1525CH/20

5 light chandelier in Brushed Nickel
20"W x 23"H
5 lights x 60W CAND
84" Overall height
{12' wire} {60" chain}



CN15752

5 light chandelier in Brushed Nickel
19"W x 22"H
5 lights x 60W CAND **shown Bulb 1101***
83" Overall height
{12' wire} {60" chain}

- clear glass ball


**not included—See page 324*



CN15712

1 light pendant in Brushed Nickel
11"W x 15"H
1 light x 100W MED **shown Bulb 1092***
76" Overall height
{12' wire} {60" chain}

**not included—See page 324*



1533CH/20

3 light chandelier in Brushed Nickel
20"W x 22"H
3 lights x 60W CAND
83" Overall height
{12' wire} {60" chain}



1515CH/20

5 light chandelier in Brushed Nickel
18"W x 20"H
5 lights x 60W CAND
81" Overall height
{12' wire} {60" chain}



CN15862

6 light chandelier in oil Brushed Nickel
14"W x 21"H
6 lights x 60W MED shown Bulb 1092*
44" Overall height
**not included-See page 324*



1513CH/20

3 light chandelier in Brushed Nickel
13"W x 15"H
3 lights x 60W CAND
76" Overall height
{12' wire} {60" chain}



CN15832

3 light pendant in Brushed Nickel
10"W x 16"H
3 lights x 60W MED shown Bulb 1092*
44" Overall height
**not included-See page 324*



1502WS/20

2 light wall sconce in Brushed Nickel
12"W x 11"H x 8"EXT
2 lights x 60W CAND



1501WS/20

1 light wall sconce in Brushed Nickel
12"W x 11"H x 7"EXT
1 light x 60W CAND

1523CH/20

3 light chandelier in Brushed Nickel
12"W x 12"H
3 lights x 60W CAND
73" Overall height
{12' wire} {60" chain}



1509CH/10

9 light chandelier in Oil Rubbed Bronze
34"W x 31"H
9 lights x 60W CAND
92" Overall height
{12' wire} {60" chain}



1505CH/10

5 light chandelier in Oil Rubbed Bronze
20"W x 23"H
5 lights x 60W CAND
84" Overall height
{12' wire} {60" chain}



CN15751

5 light chandelier in Oil Rubbed Bronze
19"W x 22"H
5 lights x 60W CAND **shown Bulb 1101***
83" Overall height
{12' wire} {60" chain}

- clear glass ball


**not included-See page 324*



CN15711

1 light pendant in Oil Rubbed Bronze
11"W x 15"H
1 light x 100W MED **shown Bulb 1092***
76" Overall height
{12' wire} {60" chain}

**not included-See page 324*



1503CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 22"H
3 lights x 60W CAND
84" Overall height
{12' wire} {60" chain}



1529CH/10

9 light chandelier in Oil Rubbed Bronze
34"W x 29"H
9 lights x 60W CAND
90" Overall height
{12' wire} {60" chain}



CN15861

6 light chandelier in Oil Rubbed Bronze
14"W x 21"H
6 lights x 60W MED shown Bulb 1092*
44" Overall height
**not included-See page 324*



1525CH/10

5 light chandelier in Oil Rubbed Bronze
20"W x 23"H
5 lights x 60W CAND
84" Overall height
{12' wire} {60" chain}



CN15831

3 light pendant in Oil Rubbed Bronze
10"W x 16"H
3 lights x 60W MED shown Bulb 1092*
44" Overall height
**not included-See page 324*



1523CH/10

3 light chandelier in Oil Rubbed Bronze
12"W x 12"H
3 lights x 60W CAND
73" Overall length
{12' wire} {60" chain}



CN250641

6 light chandelier in Oil Rubbed Bronze
21"W x 12"H
6 lights x 60W CAND **shown Bulb 1101***
73" Overall height
{12' wire} {60" chain}
**not included-See page 324*



CN250541

5 light chandelier in Oil Rubbed Bronze
18"W x 20"H
5 lights x 60W CAND **shown Bulb 1101***
81" Overall height
{12' wire} {60" chain}
**not included-See page 324*




CN251641

6 light chandelier in Oil Rubbed Bronze
14"W x 21"H
6 lights x 60W CAND **shown Bulb 1101***
82" Overall height
{12' wire} {60" chain}
**not included-See page 324*



CN250151

1 light pendant in Oil Rubbed Bronze
8"W x 14"H
1 light x 100W MED **shown Bulb 1092***
75" Overall height
{12' wire} {60" chain}
**not included-See page 324*



CN250341

3 light chandelier in Oil Rubbed Bronze
15"W x 8"H
3 lights x 100W MED **shown Bulb 1092***
69" Overall height
{12' wire} {60" chain}
**not included-See page 324*



CN251551

1 light pendant in Oil Rubbed Bronze
15"W x 9"H
1 light x 100W MED **shown Bulb 1092***
70" Overall height
{12' wire} {60" chain}
**not included-See page 324*



1533CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 22"H
3 lights x 60W CAND
83" Overall length
{12' wire} {60" chain}



1515CH/10

5 light chandelier in Oil Rubbed Bronze
18"W x 20"H
5 lights x 60W CAND
81" Overall height
{12' wire} {60" chain}



1502WS/10

2 light wall sconce in Oil Rubbed Bronze
5"W x 11"H x 8"EXT
2 lights x 60W CAND



1501WS/10

1 light wall sconce in Oil Rubbed Bronze
5"W x 11"H x 7"EXT
1 light x 60W CAND

1513CH/10

3 light mini chandelier in Oil Rubbed Bronze
13"W x 15"H
3 lights x 60W CAND
76" Overall height
{12' wire} {60" chain}



1915CH/20

5 light chandelier in Brushed Nickel
26"W x 24"H
5 lights x 100W MED
85" Overall height
{12' wire} {60" chain}
• white glass



1915CH/10

5 light chandelier in Oil Rubbed Bronze
26"W x 24"H
5 lights x 100W MED
85" Overall height
{12' wire} {60" chain}
• white glass



1913CH/20

3 light chandelier in Brushed Nickel
21"W x 23"H
3 lights x 100W MED
84" Overall height
{12' wire} {60" chain}
• white glass



1913CH/10

3 light chandelier in Oil Rubbed Bronze
21"W x 23"H
3 lights x 100W MED
84" Overall height
{12' wire} {60" chain}
• white glass



CHARLESTON

CN110821

8 light chandelier in Oil Rubbed Bronze
36"W x 32"H
8 x 60W CAND
84" Overall height
{12' wire} {60" chain}



CN110521

5 light chandelier in Oil Rubbed Bronze
21"W x 21"H
5 x 60W CAND
82" Overall height
{12' wire} {60" chain}



CN110171

1 light wall sconce in Oil Rubbed Bronze
5"W x 14"H x 4"EXT
1 x 60W CAND



CN110321

3 light chandelier in Oil Rubbed Bronze
18"W x 18"H
3 x 60W CAND
79" Overall height
{12' wire} {60" chain}



SL880241

9 light chandelier in Satin Pewter
 31"W x 32"H
 9 lights x 60W MED
 104" Overall height
 {12' wire} {6' chain}
 • white marble glass

**SL880141**

5 light chandelier in Satin Pewter
 26"W x 24"H
 5 lights x 100W MED
 96" Overall height
 {12' wire} {6' chain}
 • white marble glass

**SL880341**

3 light chandelier in Satin Pewter
 20"W x 21"H
 3 lights x 100W MED
 69" Overall height
 {12' wire} {4' chain}
 • white marble glass

**SL824641**

3 light pendant in Satin Pewter
 21"W x 25"H
 3 lights x 100W MED
 97" Overall height
 {12' wire} {6' chain}
 • white marble glass

**SL866241**

2 light semi-flush in Satin Pewter
 16"W x 13"H
 2 lights x 100W MED
 • white marble glass

**SL825641**

1 light mini pendant in Satin Pewter
 7"W x 8"H
 1 light x 100W MED
 44" Overall height
 {12' wire} {2-12" + 2-6" rods}
 • white marble glass



SL869278

- 2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W MED
• etched alabaster style glass



SL760241

- 2 light bath bar in Satin Pewter
16"W x 8"H x 7"EXT
2 lights x 100W MED
• white marble glass



SL760341

- 3 light bath bar in Satin Pewter
24"W x 8"H x 7"EXT
3 lights x 100W MED
• white marble glass



SL760441

- 4 light bath bar in Satin Pewter
32"W x 8"H x 7"EXT
4 lights x 100W MED
• white marble glass



SL880262

9 light chandelier in Aged Bronze
31"W x 32"H
9 lights x 60W MED
104" Overall height
{12' wire} {6' chain}
• champagne marble glass



SL880162

5 light chandelier in Aged Bronze
26"W x 24"H
5 lights x 100W MED
96" Overall height
{12' wire} {6' chain}
• champagne marble glass



SL824662

3 light pendant in Aged Bronze
21"W x 25"H
3 lights x 100W MED
97" Overall height
{12' wire} {6' chain}
• champagne marble glass



SL880362

3 light chandelier in Aged Bronze
20"W x 21"H
3 lights x 100W MED
69" Overall height
{12' wire} {4' chain}
• champagne marble glass



SL866262

2 light semi flush in Aged Bronze
16"W x 13"H
2 lights x 100W MED
• champagne marble glass



SL825662

1 light mini pendant in Aged Bronze
7"W x 8"H
1 light x 100W MED
44" Overall height
{12' wire} {2-12" + 2-6" rods}
• champagne marble glass



HARMONY

SL877263

2 light flush mount in Painted Bronze
14"W x 6"H
2 lights x 60W MED
• golden cream swirl glass



SL760262 ↑↓

2 light bath bar in Aged Bronze
16"W x 8"H x 7"EXT
2 lights x 100W MED
• champagne marble glass



SL760362 ↑↓

3 light bath bar in Aged Bronze
24"W x 8"H x 7"
3 lights x 100W MED
• champagne marble glass



SL760462 ↑↓

4 light bath bar in Aged Bronze
32"W x 8"H x 7"EXT
4 lights x 100W MED
• champagne marble glass



SL863978

9 light chandelier in Brushed Nickel
34"W x 32"H
9 lights x 60W MED
104" Overall height
{12' wire} {6' chain}
• alabaster style glass




SL863678

6 light chandelier in Brushed Nickel
30"W x 26"H
6 lights x 100W MED
98" Overall height
{12' wire} {6' chain}
• alabaster style glass



SL863378

3 light chandelier in Brushed Nickel
27"W x 21"H
3 lights x 100W MED
93" Overall height
{12' wire} {6' chain}
• alabaster style glass



SL829278

3 light pendant in Brushed Nickel
18"W x 23"H
3 lights x 100W MED
95" Overall height
{12' wire} {6' chain}
• alabaster style glass



SL842078

2 light semi flush in Brushed Nickel
15"W x 14"H
2 lights x 100W MED
• alabaster style glass



SL869278

2 light flush in Brushed Nickel
14"W x 6"H
2 lights x 60W MED
• etched alabaster style glass

SL829678

1 light mini pendant in Brushed Nickel
10"W x 6"H
1 light x 100W MED
42" Overall height
{12' wire} {2-12" + 2-6" rods}
• alabaster style glass



PRESTIGE

SL748278 ↑↓

2 light bath bar in Brushed Nickel
17"W x 9"H x 9"EXT
2 lights x 100W MED
• alabaster style glass



SL748378 ↑↓

3 light bath bar in Brushed Nickel
27"W x 9"H x 9"EXT
3 lights x 100W MED
• alabaster style glass



SL748478 ↑↓

4 light bath bar in Brushed Nickel
36"W x 9"H x 9"EXT
4 lights x 100W MED
• alabaster style glass



SL748578 ↑↓

5 light bath bar in Brushed Nickel
46"W x 9"H x 9"EXT
5 lights x 100W MED
• alabaster style glass



SL748678 ↑↓

6 light bath bar in Brushed Nickel
55"W x 10"H x 9"EXT
6 lights x 100W MED
• alabaster style glass



TK0023217

15 light chandelier in Brushed Nickel
48"W x 45"H
15 lights x 40W MED
117" Overall height
{12' wire} {6' chain}
• alabaster style glass



TK0022217

5 light chandelier in Brushed Nickel
24"W x 21"H
5 lights x 100W MED
93" Overall height
{12' wire} {6' chain}
• alabaster style glass



SL854178



1 light wall sconce in Brushed Nickel
8"W x 9"H x 10"EXT
1 light x 100W MED
• alabaster style glass



TC0023217

4 light pendant in Brushed Nickel
17"W x 28"H
4 lights x 60W CAND
100" Overall height
{12' wire} {6' chain}



PRESTIGE

TK0023722

15 light chandelier in Sable Bronze
48"W x 45"H
15 lights x 40W MED
117" Overall height
{12' wire} {6' chain}
• cognac edged glass



TK0022722

5 light chandelier in Sable Bronze
24"W x 21"H
5 lights x 100W MED
93" Overall height
{12' wire} {6' chain}
• cognac edged glass



SL854122 

1 light wall sconce in Sable Bronze
8"W x 9"H x 10"EXT
1 light x 100W MED
• cognac edged glass



TC0023722

4 light pendant in Sable Bronze
17"W x 28"H
4 lights x 60W CAND
100" Overall height
{12' wire} {6' chain}



SL863922

9 light chandelier in Sable Bronze
34"W x 32"H
9 lights x 60W MED
104" Overall height
{12' wire} {6' chain}
• cognac edged glass



SL863622

6 light chandelier in Sable Bronze
30"W x 26"H
6 lights x 100W MED
98" Overall height
{12' wire} {6' chain}
• cognac edged glass



SL863322

3 light chandelier Sable Bronze
27"W x 21"H
3 lights x 100W MED
93" Overall height
{12' wire} {6' chain}
• cognac edged glass



SL829222

3 light pendant in Sable Bronze
18"W x 23"H
3 lights x 100W MED
95" Overall height
{12' wire} {6' chain}
• cognac edged glass



SL842022

2 light semi-flush in Sable Bronze
15"W x 14"H
2 lights x 100W MED
• cognac edged glass



SL877263

2 light flush in Painted Bronze
14"W x 6"H
2 lights x 60W MED
• golden cream swirl glass

SL829822

1 light mini pendant in Sable Bronze
10"W x 6"H
1 light x 100W MED
42" Overall height
{12' wire} {2-12" + 2-6" rods}
• cognac edged glass



SL748222 

2 light bath in Sable Bronze
17"W x 9"H x 9"EXT
2 lights x 100W MED
• cognac edged glass



SL748322 

3 light bath bar in Sable Bronze
27"W x 9"H x 9"EXT
3 lights x 100W MED
• cognac edged glass



SL748422 

4 light bath bar in Sable Bronze
36"W x 9"H x 9"EXT
4 lights x 100W MED
• cognac edged glass



SL748522 

5 light bath bar in Sable Bronze
46"W x 9"H x 9"EXT
5 lights x 100W MED
• cognac edged glass



SL748622 

6 light bath bar in Sable Bronze
55"W x 10"H x 9"EXT
6 lights x 100W MED
• cognac edged glass



2115CH/20

15 light chandelier in Brushed Nickel
45"W x 37"H
15 lights x 60W MED
98" Overall height
{12' wire} {60" chain}
• white glass



2109CH/20

9 light chandelier in Brushed Nickel
32"W x 25"H
9 lights x 60W MED
86" Overall height
{12' wire} {60" chain}
• white glass



2105CH/20

5 light chandelier in Brushed Nickel
27"W x 22"H
5 lights x 100W MED
83" Overall height
{12' wire} {60" chain}
• white glass



2103CH/20

3 light chandelier in Brushed Nickel
23"W x 20"H
3 lights x 100W MED
81" Overall height
{12' wire} {60" chain}
• white glass



2103SF/20

3 light semi-flush in Brushed Nickel
17"W x 12"H
3 lights x 60W MED
• white glass



2103FM/20

3 light flush mount in Brushed Nickel
17"W x 6"H
3 lights x 60W MED
• white glass



2101WS/20

1 light wall sconce in Brushed Nickel
7"W x 10"H x 10"EXT
1 light x 100W MED
• white glass



2101PS/20

1 light mini pendant in Brushed Nickel
7"W x 43"H
1 light x 100W MED
43" Overall length
• white glass



BRISTOL LANE





2115CH/10

15 light chandelier in Oil Rubbed Bronze
45"W x 37"H
15 lights x 60W MED
98" Overall height
{12' wire} {60" chain}

- white glass



2109CH/10

9 light chandelier in Oil Rubbed Bronze
32"W x 25"H
9 lights x 60W MED
86" Overall height
{12' wire} {60" chain}

- white glass



2105CH/10

5 light chandelier in Oil Rubbed Bronze
27"W x 22"H
5 lights x 100W MED
83" Overall height
{12' wire} {60" chain}

- white glass



2103CH/10

3 light chandelier in Oil Rubbed Bronze
23"W x 20"H
3 lights x 100W MED
81" Overall height
{12' wire} {60" chain}

- white glass



2103SF/10

3 light semi-flush in Oil Rubbed Bronze
17"W x 12"H
3 lights x 60W MED
• white glass



2103FM/10

3 light flush mount in Oil Rubbed Bronze
17"W x 6"H
3 lights x 60W MED
• white glass



2101WS/10

1 light wall sconce in Oil Rubbed Bronze
6"W x 10"H x 10"EXT
1 light x 100W MED
• white glass



2101PS/10

1 light mini pendant in Oil Rubbed Bronze
7"W x 43"H
1 light x 100W MED
43" Overall height
• white glass



SL808372

9 light chandelier in Moonlight Silver
31"W x 33"H
9 lights x 100W MED
81" Overall height
{12' wire} {4' chain}
• tea stained glass



SL808272

5 light chandelier in Moonlight Silver
26"W x 26"H
5 lights x 100W MED
74" Overall height
{12' wire} {4' chain}
• tea stained glass



SL808172

3 light chandelier in Moonlight Silver
20"W x 23"H
3 lights x 100W MED
70" Overall height
{12' wire} {4' chain}
• tea stained glass



SL893572

2 light pendant in Moonlight Silver
19"W x 24"H
2 lights x 100W MED
72" Overall height
{12' wire} {4' chain}
• tea stained glass



SL861672

2 light semi-flush in Moonlight Silver
16"W x 12"H
2 lights x 100W MED
• tea stained glass



SL893672

4 light pendant in Moonlight Silver
18"W x 33"H
4 lights x 60W CAND
81" Overall height
{12' wire} {4' chain}

SL893472

1 light mini pendant in Moonlight Silver
5"W x 12"H
1 light x 100W MED
48" Overall height
{12' wire} {2-12" + 2-6" rods}
• tea stained glass



SL861572

2 light flush mount in Moonlight Silver
13"W x 7"H
2 lights x 60W MED
• tea stained glass



SL717272

2 light bath bar in Moonlight Silver
12"W x 9"H x 9"EXT
2 lights x 100W MED
• tea stained glass



SL717372

3 light bath bar in Moonlight Silver
21"W x 9"H x 9"EXT
3 lights x 100W MED
• tea stained glass



SL717472

4 light bath bar in Moonlight Silver
29"W x 9"H x 9"EXT
4 lights x 100W MED
• tea stained glass



SL717572

5 light bath bar in Moonlight Silver
36"W x 9"H x 9"EXT
5 lights x 100W MED
• tea stained glass



SL808322

9 light chandelier in Sable Bronze
31"W x 33"H
9 lights x 100W MED
81" Overall height
{12' wire} {4' chain}
• tea stained glass



SL808222

5 light chandelier in Sable Bronze
26"W x 26"H
5 lights x 100W MED
74" Overall height
{12' wire} {4' chain}
• tea stained glass



SL808122

3 light chandelier in Sable Bronze
20"W x 23"H
3 lights x 100W MED
70" Overall height
{12' wire} {4' chain}
• tea stained glass



SL893522

2 light pendant in Sable Bronze
19"W x 24"H
2 lights x 100W MED
72" Overall height
{12' wire} {4' chain}
• tea stained glass



SL861622

2 light semi-flush in Sable Bronze
16"W x 12"H
2 lights x 100W MED
• tea stained glass



SL893622

4 light pendant in Sable Bronze
18"W x 33"H
4 lights x 60W CAND
81" Overall height
{12' wire} {4' chain}

SL893422

1 light mini pendant in Sable Bronze
5"W x 12"H
1 light x 100W MED
48" Overall height
{12' wire} {2-12" + 2-6" rods}
• tea stained glass



SL861522

2 light flush mount in Sable Bronze
13"W x 7"H
2 lights x 60W MED
• tea stained glass



SL717222

2 light bath bar in Sable Bronze
12"W x 9"H x 9"EXT
2 lights x 100W MED
• tea stained glass



SL717322

3 light bath bar in Sable Bronze
21"W x 9"H x 9"EXT
3 lights x 100W MED
• tea stained glass



SL717422

4 light bath bar in Sable Bronze
29"W x 9"H x 9"EXT
4 lights x 100W MED
• tea stained glass



SL717522

5 light bath bar in Sable Bronzer
36"W x 9"H x 9"EXT
5 lights x 100W MED
• tea stained glass



2209CH/10

9 light chandelier in Oil Rubbed Bronze
33"W x 29"H
9 lights x 60W MED
90" Overall height
{12' wire} {60" chain}
• white glass



2205CH/10

5 light chandelier in Oil Rubbed Bronze
28"W x 21"H
5 lights x 60W MED
82" Overall height
{12' wire} {60" chain}
• white glass



2203CH/10

3 light chandelier in Oil Rubbed Bronze
24"W x 22"H
3 lights x 60W MED
83" Overall height
{12' wire} {60" chain}
• white glass



2203PL/10

3 light pendant in Oil Rubbed Bronze
17"W x 14"H
3 lights x 100W MED
75" Overall height
{12' wire} {60" chain}
• white glass



2203IS/10

3 light island in Oil Rubbed Bronze
48"W x 24"H x 13" D
3 lights x 60W MED
85" Overall height
{60" chain}
• white glass



2203CS/10

3 light convertible pendant/semi flush in Oil Rubbed Bronze
17"W x 16"H
3 lights x 60W MED
77" Overall height
{12' wire} {60" chain}

- white glass



2201PS/10

1 light mini pendant in Oil Rubbed Bronze
6"W x 44"H
1 light x 100W MED
44" Overall height

- white glass



2201WS/10



1 light wall sconce in Oil Rubbed Bronze
6"W x 10"H x 9"EXT
1 light x 100W MED

- white glass



2201BB/10



2 light bath bar in Oil Rubbed Bronze
16"W x 9"H x 8"EXT
2 lights x 100W MED

- white glass



2203BB/10



3 light bath bar in Oil Rubbed Bronze
26"W x 9"H x 8"EXT
3 lights x 100W MED

- white glass



2204BB/10



4 light bath bar in Oil Rubbed Bronze
35"W x 9"H x 8"EXT
4 lights x 100W MED

- white glass





SANTE FE



TRIBECCA

2455CH/20

5 light chandelier in Brushed Nickel
25"W x 25"H
5 lights x 60W MED
86" Overall height
{12' wire} {60" chain}
• white glass



2453CH/20

3 light chandelier in Brushed Nickel
22"W x 24"H
3 lights x 60W MED
86" Overall height
{12' wire} {60" chain}
• white glass



2402SF/20

2 light semi flush in Brushed Nickel
12"W x 12"H
2 lights x 60W MED
• white glass



2451WS/20

1 light wall sconce in Brushed Nickel
9"W x 12"H x 10"EXT
1 light x 60W MED
• white glass

2401PL/20

1 light pendant in Brushed Nickel
12"W x 16"H
1 light x 60W CAND
77" Overall height
{12' wire} {60" chain}
• white glass



TRIBECCA

2455CH/10

5 light chandelier in Oil Rubbed Bronze
25"W x 25"H
5 lights x 60W MED
86" Overall height
{12' wire} {60" chain}
• white glass



2453CH/10

3 light chandelier in Oil Rubbed Bronze
22"W x 24"H
3 lights x 60W MED
86" Overall height
{12' wire} {60" chain}
• white glass



2402SF/10

2 light semi flush in Oil Rubbed Bronze
12"W x 12"H
2 lights x 60W MED
• white glass



2451WS/10

1 light wall sconce in Oil Rubbed Bronze
9"W x 12"H x 10"EXT
1 light x 60W MED
• white glass

2401PL/10

1 light pendant in Oil Rubbed Bronze
12"W x 16"H
1 light x 60W CAND
77" Overall height
{12' wire} {60" chain}
• white glass



M209778

6 light chandelier in Brushed Nickel

26"W x 25"H

6 lights x 40W CAND

74" Overall height

{12' wire} {1-4" + 1-8" + 1-12" + 1-24" rods}

- bone linen shimmer



M261678

3 light chandelier in Brushed Nickel

24"W x 34"H

3 lights x 60W CAND

82" Overall height

{12' wire} {1-4" + 1-8" + 1-12" + 1-24" rods}

- bone linen shimmer



M251878

1 light pendant in Brushed Nickel

6"W x 26"H

1 light x 100W MED

74" Overall height

{12' wire} {1-4" + 1-8" + 1-12" + 1-24" rods}

- bone linen shimmer



M271878

2 light flush in Brushed Nickel

15"W x 9"H

2 lights x 60W MED

- bone linen shimmer
- etched white diffuser



ALLURE



SL806978

6 light chandelier in Brushed Nickel
 42"L x 42"W x 23"H
 6 lights x 100W MED
 71" Overall height
 {12' wire} {4' chain}
 • etched glass

**TK0008217**

8 light chandelier in Brushed Nickel
 27"W x 27"H
 8 lights x 60W MED
 99" Overall height
 {12' wire} {6' chain}
 • etched glass

**SL806878**

3 light chandelier in Brushed Nickel
 20"W x 20"H
 3 lights x 100W MED
 68" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL806778**

5 light chandelier in Brushed Nickel
 24"W x 23"H
 5 lights x 100W MED
 70" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL860978**

2 light semi flush in Brushed Nickel
 16"W x 12"H
 2 lights x 60W MED
 • white cotton weave fabric shade
 • etched white diffuser

**SL806678**

3 light pendant in Brushed Nickel
 20"W x 19"H
 3 lights x 60W CAND
 67" Overall height
 {12' wire} {4' chain}
 • white cotton weave fabric shade

**SL891078**

1 light mini pendant in Brushed Nickel
 5"W x 20"H
 1 light x 100W MED
 68" Overall height
 {12' wire} {4' chain}
 • etched glass



SL878278

2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W MED
• etched glass



TN0005217



1 light wall sconce in Brushed Nickel
5"W x 12"H x 8"EXT
1 lights x 100W MED
• etched glass



TV0007217



2 light bath bar in Brushed Nickel
13"W x 12"H x 9"EXT
2 lights x 100W MED
• etched glass



SL715378



3 light bath bar in Brushed Nickel
20"W x 12"H x 9"EXT
3 lights x 100W MED
• etched glass



SL715478



4 light bath bar in Brushed Nickel
27"W x 12"H x 9"EXT
4 lights x 100W MED
• etched glass



SL806915

6 light chandelier in Oil Rubbed Bronze

42"L x 42"W x 23"H

6 lights x 100W MED

71" Overall height

{12' wire} {4' chain}

- etched glass

**TK0008715**

8 light chandelier in Oil Rubbed Bronze

27"W x 27"H

8 lights x 60W MED

99" Overall height

{12' wire} {6' chain}

- etched glass

**SL806815**

3 light chandelier in Oil Rubbed Bronze

20"W x 20"H

3 lights x 100W MED

68" Overall height

{12' wire} {4' chain}

- etched glass

**SL806715**

5 light chandelier in Oil Rubbed Bronze

24"W x 23"H

5 lights x 100W MED

70" Overall height

{12' wire} {4' chain}

- etched glass

**SL860915**

2 light semi flush in Oil Rubbed Bronze

16"W x 12"H

2 lights x 60W MED

- white cotton weave fabric shade

- etched white diffuser

**SL806615**

3 light pendant in Oil Rubbed Bronze

20"W x 19"H

3 lights x 60W CAND

67" Overall height

{12' wire} {4' chain}

- white cotton weave fabric shade

**SL891015**

1 light mini pendant in Oil Rubbed Bronze

5"W x 20"H

1 light x 100W MED

68" Overall height

{12' wire} {4' chain}

- etched glass



PENDENZA

SL878215

2 light flush mount in Oil Rubbed Bronze
14"W x 6"H
2 lights x 60W MED
• etched glass



TN0005715



1 light wall sconce in Oil Rubbed Bronze
5"W x 12"H x 8"EXT
1 lights x 100W MED
• etched glass



TV0007715



2 light bath bar in Oil Rubbed Bronze
13"W x 12"H x 9"EXT
2 lights x 100W MED
• etched glass



SL715315



3 light bath bar in Oil Rubbed Bronze
20"W x 12"H x 9"EXT
3 lights x 100W MED
• etched glass



SL715415



4 light bath bar in Oil Rubbed Bronze
27"W x 12"H x 9"EXT
4 lights x 100W MED
• etched glass





PENDENZA



PITTMAN

190042217

9 light chandelier in Brushed Nickel
 31"W x 29"H
 9 lights x 60W MED
 77" Overall height
 {12' wire} {4' chain}

- etched glass

**190041217**

5 light chandelier in Brushed Nickel
 24"W x 22"H
 5 lights x 100W MED
 70" Overall height
 {12' wire} {6' chain}

- etched glass

**190061217**

3 light pendant in Brushed Nickel
 18"W x 20"H
 3 lights x 100W MED
 68" Overall height
 {12' wire} {4' chain}

- etched glass

**190040217**

3 light chandelier in Brushed Nickel
 20"W x 20"H
 3 lights x 100W MED
 68" Overall height
 {12' wire} {4' chain}

- etched glass

**190043217**

2 light semi flush or pendant in Brushed Nickel
 15"W x 15"H
 2 lights x 100W MED
 60" Overall height
 {12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant

**190060217**

1 light mini pendant in Brushed Nickel
 5"W x 8"H
 1 light x 100W MED
 56" Overall height
 {12' wire} {1-4" + 1-8" + 1-12" = 1-24" rods}

- etched glass



190071217

- 2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W MED
- etched glass



190023217

- 1 light wall sconce in Brushed Nickel
5"W x 9"H x 6"EXT
1 lights x 100W MED
- etched glass



190022217

- 2 light bath bar in Brushed Nickel
12"W x 10"H x 6"EXT
2 lights x 100W MED
- etched glass



190024217

- 3 light bath bar in Brushed Nickel
19"W x 10"H x 6"EXT
3 lights x 100W MED
- etched glass



190025217

- 4 light bath bar in Brushed Nickel
24"W x 10"H x 6"EXT
4 lights x 100W MED
- etched glass



190042719

9 light chandelier in Sienna Bronze
31"W x 29"H
9 lights x 60W MED
77" Overall height
{12' wire} {4' chain}
• etched glass



190041719

5 light chandelier in Sienna Bronze
24"W x 22"H
5 lights x 100W MED
70" Overall height
{12' wire} {6' chain}
• etched glass



190061719

3 light pendant in Sienna Bronze
18"W x 20"H
3 lights x 100W MED
68" Overall height
{12' wire} {4' chain}
• etched glass



190040719

3 light chandelier in Sienna Bronze
20"W x 20"H
3 lights x 100W MED
68" Overall height
{12' wire} {4' chain}
• etched glass



190043719

2 light semi flush or pendant in Sienna Bronze
15"W x 15"H
2 lights x 100W MED
60" Overall height
{12' wire} {4' chain}
• etched glass
• convertible semi-flush or chain hung pendant



190060719

1 light mini pendant in Sienna Bronze
5"W x 8"H
1 light x 100W MED
56" Overall height
{12' wire} {1-4" + 1-8" + 1-12" = 1-24" rods}
• etched glass



190071719

- 2 light flush in Sienna Bronze
14"W x 6"H
2 lights x 60W MED
• etched glass



190023719



- 1 light wall sconce in Sienna Bronze
5"W x 9"H x 6"EXT
1 lights x 100W MED
• etched glass



190022719



- 2 light bath bar in Sienna Bronze
12"W x 10"H x 6"EXT
2 lights x 100W MED
• etched glass



190024719



- 3 light bath bar in Sienna Bronze
19"W x 10"H x 6"EXT
3 lights x 100W MED
• etched glass



190025719



- 4 light bath bar in Sienna Bronze
24"W x 10"H x 6"EXT
4 lights x 100W MED
• etched glass



SL801678

9 light chandelier in Brushed Nickel
 30"W x 29"H
 9 lights x 60W MED
 101" Overall height
 {12' wire} {6' chain}

- alabaster style glass

**SL801578**

5 light chandelier in Brushed Nickel
 24"W x 17"H
 5 lights x 100W MED
 65" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL823678**

3 light pendant in Brushed Nickel
 20"W x 28"H
 3 lights x 100W MED
 100" Overall height
 {12' wire} {6' chain}

- alabaster style glass
- etched white diffuser

**SL801478**

3 light chandelier in Brushed Nickel
 19"W x 17"H
 3 lights x 100W MED
 65" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL861478**

2 light semi flush or pendant in Brushed Nickel
 12"W x 11"H
 2 lights x 100W MED
 {12' wire} {4' chain}

- alabaster style glass
- convertible semi-flush or chain hung pendant

**SL823478**

1 light pendant in Brushed Nickel
 12"W x 9"H
 1 light x 150W MED
 57" Overall height
 {12' wire} {4' chain}

- alabaster style glass



SL758278

2 light bath bar in Brushed Nickel
 18"W x 9"H x 8"EXT
 2 lights x 100W MED
 • alabaster style glass

**SL869278**

2 light flush mount in Brushed Nickel
 14"W x 6"H
 2 lights x 60W MED
 • etched alabaster style glass

**SL758378**

3 light bath bar in Brushed Nickel
 24"W x 9"H x 8"EXT
 3 lights x 100W MED
 • alabaster style glass

**SL758478**

4 light bath bar in Brushed Nickel
 30"W x 9"H x 8"EXT
 4 lights x 100W MED
 • alabaster style glass

**SL758578**

5 light bath bar in Brushed Nickel
 36"W x 9"H x 8"EXT
 5 lights x 100W MED
 • alabaster style glass

**SL758678**

6 light bath bar in Brushed Nickel
 48"W x 9"H x 8"EXT
 6 lights x 100W MED
 • alabaster style glass



SL801663

9 light chandelier in Painted Bronze
 30"W x 29"H
 9 lights x 60W MED
 101" Overall height
 {12' wire} {6' chain}

- alabaster style glass

**SL801563**

5 light chandelier in Painted Bronze
 24"W x 17"H
 5 lights x 100W MED
 65" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL823663**

3 light pendant in Painted Bronze
 20"W x 28"H
 3 lights x 100W MED
 100" Overall height
 {12' wire} {6' chain}

- alabaster style glass
- etched white diffuser

**SL801463**

3 light chandelier in Painted Bronze
 19"W x 17"H
 3 lights x 100W MED
 65" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL861463**

2 light semi flush or pendant in Painted Bronze
 12"W x 11"H
 2 lights x 100W MED
 {12' wire} {4' chain}

- alabaster style glass
- convertible semi-flush or chain hung pendant

**SL823463**

1 light mini pendant in Painted Bronze
 12"W x 9"H
 1 light x 150W MED
 57" Overall height
 {12' wire} {4' chain}

- alabaster style glass



SL758263

2 light bath bar in Painted Bronze
 18"W x 9"H x 8"EXT
 2 lights x 100W MED
 • alabaster style glass

**SL869263**

2 light flush mount in Painted Bronze
 14"W x 6"H
 2 lights x 60W MED
 • etched alabaster style glass

**SL758363**

3 light bath bar in Painted Bronze
 24"W x 9"H x 8"EXT
 3 lights x 100W MED
 • alabaster style glass

**SL758463**

4 light bath bar in Painted Bronze
 30"W x 9"H x 8"EXT
 4 lights x 100W MED
 • alabaster style glass

**SL758563**

5 light bath bar in Painted Bronze
 36"W x 9"H x 8"EXT
 5 lights x 100W MED
 • alabaster style glass

**SL758663**

6 light bath bar in Painted Bronze
 48"W x 9"H x 8"EXT
 6 lights x 100W MED
 • alabaster style glass




SL805278

9 light chandelier in Brushed Nickel
 32"W x 29"H
 9 lights x 60W MED
 77" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL891678**

1 light pendant in Brushed Nickel
 16"W x 18"H
 1 light x 150W MED
 66" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL805178**

5 light chandelier in Brushed Nickel
 23"W x 20"H
 5 lights x 100W MED
 68" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL891778**

3 light pendant in Brushed Nickel
 20"W x 25"H
 3 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}
 • etched glass

**TK0003217**

3 light chandelier in Brushed Nickel
 20"W x 12"H
 3 lights x 100W MED
 60" Overall height
 • etched glass

**SL860778**

3 light semi-flush or pendant in Brushed Nickel
 16"W x 12"H
 3 lights x 60W MED
 59" Overall height
 {12' wire} {4' chain}
 • etched glass
 • convertible semi-flush or chain hung pendant

**SL891878**

6 light pendant in Brushed Nickel
 17"W x 32"H
 6 lights x 60W CAND
 79" Overall height
 {12' wire} {4' chain}

SL891578

1 light mini pendant in Brushed Nickel
 8"W x 15"H
 1 light x 100W MED
 63" Overall height
 {12' wire} {4' chain}
 • etched glass



SL878278

2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W MED
• etched glass



TN0003217



1 light wall sconce in Brushed Nickel
5"W x 9"H x 7"EXT
1 lights x 100W MED
• etched glass



SL714278



2 light bath bar in Brushed Nickel
13"W x 9"H x 7"EXT
2 lights x 100W MED
• etched glass



SL714378



3 light bath bar in Brushed Nickel
18"W x 9"H x 7"EXT
3 lights x 100W MED
• etched glass



SL714478



4 light bath bar in Brushed Nickel
25"W x 9"H x 7"EXT
4 lights x 100W MED
• etched glass



SL714578



5 light bath bar in Brushed Nickel
31"W x 9"H x 7"EXT
5 lights x 100W MED
• etched glass




SL805215

9 light chandelier in Oil Rubbed Bronze
 32"W x 29"H
 9 lights x 60W MED
 77" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL891615**

1 light pendant in Oil Rubbed Bronze
 16"W x 18"H
 1 light x 150W MED
 66" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL805115**

5 light chandelier in Oil Rubbed Bronze
 23"W x 20"H
 5 lights x 100W MED
 68" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL891715**

3 light pendant in Oil Rubbed Bronze
 20"W x 25"H
 3 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}
 • etched glass

**TK0003715**

3 light chandelier in Oil Rubbed Bronze
 20"W x 12"H
 3 lights x 100W MED
 60" Overall height
 • etched glass

**SL860715**

3 light semi-flush or pendant in Oil Rubbed Bronze
 16"W x 12"H
 3 lights x 60W MED
 59" Overall height
 {12' wire} {4' chain}
 • etched glass
 • convertible semi-flush or chain hung pendant

**SL891815**

6 light pendant in Oil Rubbed Bronze
 17"W x 32"H
 6 lights x 60W CAND
 79" Overall height
 {12' wire} {4' chain}

SL891515

1 light mini pendant in Oil Rubbed Bronze
 8"W x 15"H
 1 light x 100W MED
 63" Overall height
 {12' wire} {4' chain}
 • etched glass



SL878215

2 light flush mount in Oil Rubbed Bronze
14"W x 6"H
2 lights x 60W MED
• etched glass



TN0003715 

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 7"EXT
1 lights x 100W MED
• etched glass



SL714215 

2 light bath bar in Oil Rubbed Bronze
13"W x 9"H x 7"EXT
2 lights x 100W MED
• etched glass



SL714315 

3 light bath bar in Oil Rubbed Bronze
18"W x 9"H x 7"EXT
3 lights x 100W MED
• etched glass



SL714415 

4 light bath bar in Oil Rubbed Bronze
25"W x 9"H x 7"EXT
4 lights x 100W MED
• etched glass



SL714515 

5 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 7"EXT
5 lights x 100W MED
• etched glass



2009CH/10

9 light chandelier in Oil Rubbed Bronze
36"W x 33"H
9 lights x 60W MED
94" Overall height
{12' wire} {60" chain}
• white glass



2005CH/10

5 light chandelier in Oil Rubbed Bronze
27"W x 24"H
5 lights x 60W MED
85" Overall height
{12' wire} {60" chain}
• white glass



2003FM/10

3 light flush mount in Oil Rubbed Bronze
14"W x 6"H
3 lights x 60W MED
• white glass



2003CH/10

3 light chandelier in Oil Rubbed Bronze
22"W x 19"H
5 lights x 60W MED
80" Overall height
{12' wire} {60" chain}
• white glass







1905CH/20

5 light chandelier in Brushed Nickel
24"W x 23"H
5 lights x 100W MED
84" Overall height
{12' wire} {60" chain}

- white glass



1905CH/10

5 light chandelier in Oil Rubbed Bronze
24"W x 23"H
5 lights x 100W MED
84" Overall height
{12' wire} {60" chain}


- white glass



1903CH/20

3 light chandelier in Brushed Nickel
19"W x 20"H
3 lights x 100W MED
81" Overall height
{12' wire} {60" chain}

- white glass



1903CH/10

3 light chandelier in Oil Rubbed Bronze
22"W x 19"H
3 lights x 60W MED
81" Overall height
{12' wire} {60" chain}

- white glass



1009CH/20

9 light chandelier in Brushed Nickel
25"W x 29"H
9 lights x 60W MED
83" Overall height
{12' wire} {60" chain}
• white glass



1005CH/20

5 light chandelier in Brushed Nickel
22"W x 25"H
5 lights x 75W MED
86" Overall height
{12' wire} {60" chain}
• white glass



1003CH/20

3 light chandelier in Brushed Nickel
20"W x 24"H
3 lights x 75W MED
85" Overall height
{12' wire} {60" chain}
• white glass



1003PL/20

3 light large pendant in Brushed Nickel
13"W x 6"H
3 lights x 60W MED
83" Overall height
{12' wire} {60" chain}
• white glass



1001PS/20

1 light mini pendant in Brushed Nickel
6"W x 6"H
1 light x 75W MED
44" Overall height
• white glass



1003IS/20

3 light island in Brushed Nickel
18"W x 37"H
3 lights x 100W MED
44" Overall height
• white glass



BRIGHTON

1103FM/20

3 light flush mount in Brushed Nickel
13"W x 6"H
3 lights x 60W MED
• white glass



1002CS/20

2 light convertible in Brushed Nickel
16"W x 13"H
2 lights x 60W MED
74" Overall height
{12' wire} {60" chain}
• white glass



1001WS/20

1 light wall sconce in Brushed Nickel
6"W x 11"H x 8"EXT
1 light x 75W MED
• white glass



1002BB/20

2 light bath bar in Brushed Nickel
15"W x 11"H x 7"EXT
2 lights x 75W MED
• white glass



1003BB/20

3 light bath bar in Brushed Nickel
24"W x 11"H x 7"EXT
3 lights x 75W MED
• white glass



1004BB/20

4 light bath bar in Brushed Nickel
33"W x 11"H x 7"EXT
4 lights x 75W MED
• white glass



1059CH/10

9 light chandelier in Oil Rubbed Bronze
25"W x 29"H
9 lights x 60W MED
83" Overall length
{12' wire} {60" chain}
• white glass



1055CH/10

5 light chandelier in Oil Rubbed Bronze
22"W x 25"H
5 lights x 75W MED
86" Overall length
{12' wire} {60" chain}
• white glass



1053CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 24"H
3 lights x 75W MED
85" Overall length
{12' wire} {60" chain}
• white glass



1053PL/10

3 light large pendant in Oil Rubbed Bronze
13"W x 6"H
3 lights x 60W MED
83" Overall length
{12' wire} {60" chain}
• white glass



1051PS/10

1 light mini pendant in Oil Rubbed Bronze
6"W x 6"H
1 light x 75W MED
44" Overall length
• white glass



1053IS/10

3 light island in Oil Rubbed Bronze
18"W x 37"H
3 lights x 100W MED
44" Overall length
• white glass



1153FM/10

3 light flush mount in Oil Rubbed Bronze
 13"W x 6"H
 3 lights x 60W MED
 • white glass

**1052CS/10**

2 light convertible in Oil Rubbed Bronze
 16"W x 13"H
 2 lights x 60W MED
 74" Overall length
 (12' wire) (60" chain)
 • white glass

**1051WS/10** 

1 light wall sconce in Oil Rubbed Bronze
 6"W x 11"H x 8"EXT
 1 light x 75W MED
 • white glass

**1052BB/10** 

2 light bath bar in Oil Rubbed Bronze
 15"W x 11"H x 7"EXT
 2 lights x 75W MED
 • white glass

**1053BB/10** 

3 light bath bar in Oil Rubbed Bronze
 24"W x 11"H x 7"EXT
 3 lights x 75W MED
 • white glass

**1054BB/10** 

4 light bath bar in Oil Rubbed Bronze
 33"W x 11"H x 7"EXT
 4 lights x 75W MED
 • white glass



SL881378

9 light chandelier in Brushed Nickel
 32"W x 27"H
 9 lights x 60W MED
 99" Overall height
 {12' wire} {6' chain}

- reeded center column
- alabaster style glass

**SL881178**

5 light chandelier in Brushed Nickel
 25"W x 23"H
 5 lights x 100W MED
 71" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL881278**

3 light chandelier in Brushed Nickel
 19"W x 14"H
 3 lights x 100W MED
 62" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL826678**

3 light pendant in Brushed Nickel
 16"W x 19"H
 3 lights x 100W MED
 67" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL869678**

3 light semi flush in Brushed Nickel
 16"W x 12"H
 3 lights x 100W MED

- alabaster style glass

**SL869278**

2 light flush mount in Brushed Nickel
 14"W x 6"H
 2 lights x 60W MED

- alabaster style glass

**SL820678**

1 light mini pendant in Brushed Nickel
 6"W x 21"H
 1 light x 100W MED
 69" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass



SL758278 ↑↓

2 light bath bar in Brushed Nickel
18"W x 9"H x 8"EXT
2 lights x 100W MED
• alabaster style glass



SL758378 ↑↓

3 light bath bar in Brushed Nickel
24"W x 9"H x 8"EXT
3 lights x 100W MED
• alabaster style glass



SL758478 ↑↓

4 light bath bar in Brushed Nickel
30"W x 9"H x 8"EXT
4 lights x 100W MED
• alabaster style glass



SL758578 ↑↓

5 light bath bar in Brushed Nickel
36"W x 9"H x 8"EXT
5 lights x 100W MED
• alabaster style glass



SL758678 ↑↓

6 light bath bar in Brushed Nickel
48"W x 9"H x 8"EXT
6 lights x 100W MED
• alabaster style glass



SL881363

9 light chandelier in Painted Bronze
 32"W x 27"H
 9 lights x 60W MED
 99" Overall height
 {12' wire} {6' chain}

- reeded center column
- alabaster style glass

**SL881163**

5 light chandelier in Painted Bronze
 25"W x 23"H
 5 lights x 100W MED
 71" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL881263**

3 light chandelier in Painted Bronze
 19"W x 14"H
 3 lights x 100W MED
 62" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL826663**

3 light pendant in Painted Bronze
 16"W x 19"H
 3 lights x 100W MED
 67" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL869663**

3 light semi flush or pendant in Painted Bronze
 16"W x 12"H
 3 lights x 100W MED

- alabaster style glass

**SL869263**

2 light flush mount in Painted Bronze
 14"W x 6"H
 2 lights x 60W MED

- alabaster style glass

SL820663

1 light mini pendant in Painted Bronze
 6"W x 21"H
 1 light x 100W MED
 69" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass



SL758263 

2 light bath bar in Painted Bronze
18"W x 9"H x 8"EXT
2 lights x 100W MED
• alabaster style glass



SL758363 

3 light bath bar in Painted Bronze
24"W x 9"H x 8"EXT
3 lights x 100W MED
• alabaster style glass



SL758463 

4 light bath bar in Painted Bronze
30"W x 9"H x 8"EXT
4 lights x 100W MED
• alabaster style glass



SL758563 

5 light bath bar in Painted Bronze
36"W x 9"H x 8"EXT
5 lights x 100W MED
• alabaster style glass



SL758663 

6 light bath bar in Painted Bronze
48"W x 9"H x 8"EXT
6 lights x 100W MED
• alabaster style glass



SL811578

5 light chandelier in Brushed Nickel
 24"W x 24"H
 5 lights x 100W MED
 96" Overall height
 {12' wire} {6' chain}
 • alabaster style glass

**SL811378**

3 light chandelier in Brushed Nickel
 20"W x 22"H
 3 lights x 100W MED
 70" Overall height
 {12' wire} {4' chain}
 • alabaster style glass

**SL820078**

1 light pendant in Brushed Nickel
 18"W x 10"H
 1 light x 150W MED
 58" Overall height
 {12' wire} {4' chain}
 • alabaster style glass

**SL829178**

1 light mini pendant in Brushed Nickel
 6"W x 26"H
 1 light x 100W MED
 56" Overall height
 {12' wire} {2-12" + 1-6" rod}
 • alabaster style glass

**SL825378**

3 light semi flush or pendant in Brushed Nickel
 19"W x 15"H
 3 lights x 100W MED
 67" Overall height
 {12' wire} {4' chain}
 • alabaster style glass
 • convertible semi-flush or chain hung
 pendant. Height when ceiling mounted 15"
 • etched white diffuser

**SL869278**

2 light flush mount in Brushed Nickel
 14"W x 6"H
 2 lights x 60W MED
 • alabaster style glass



SL744278 

2 light bath bar in Brushed Nickel
18"W x 10"H x 8"EXT
2 lights x 100W MED
• alabaster style glass



SL744378 

3 light bath bar in Brushed Nickel
24"W x 10"H x 8"EXT
3 lights x 100W MED
• alabaster style glass



SL744478 

4 light bath bar in Brushed Nickel
36"W x 10"H x 8"EXT
4 lights x 100W MED
• alabaster style glass



SL744578 

5 light bath bar in Brushed Nickel
48"W x 10"H x 8"EXT
5 lights x 100W MED
• alabaster style glass



SL811563

5 light chandelier in Painted Bronze
 24"W x 24"H
 5 lights x 100W MED
 96" Overall height
 {12' wire} {6' chain}
 • alabaster style glass

**SL811363**

3 light chandelier in Painted Bronze
 20"W x 22"H
 3 lights x 100W MED
 70" Overall height
 {12' wire} {4' chain}
 • alabaster style glass

**SL820063**

1 light pendant in Painted Bronze
 18"W x 10"H
 1 light x 150W MED
 58" Overall height
 {12' wire} {4' chain}
 • alabaster style glass

**SL829163**

1 light mini pendant in Painted Bronze
 6"W x 26"H
 1 light x 100W MED
 56" Overall height
 {12' wire} {2-12" + 1-6" rod}
 • alabaster style glass

**SL825363**

3 light semi flush or pendant in Painted Bronze
 19"W x 15"H
 3 lights x 100W MED
 67" Overall height
 {12' wire} {4' chain}
 • alabaster style glass
 • convertible semi-flush or chain hung pendant.
 Height when ceiling mounted 15"
 • etched white diffuser

**SL869263**

2 light flush mount in Painted Bronze
 14"W x 6"H
 2 lights x 60W MED
 • alabaster style glass



SL744263 

2 light bath bar in Painted Bronze
18"W x 10"H x 8"EXT
2 lights x 100W MED
• alabaster style glass



SL744363 

3 light bath bar in Painted Bronze
24"W x 10"H x 8"EXT
3 lights x 100W MED
• alabaster style glass



SL744463 

4 light bath bar in Painted Bronze
36"W x 10"H x 8"EXT
4 lights x 100W MED
• alabaster style glass



SL744563 

5 light bath bar in Painted Bronze
48"W x 10"H x 8"EXT
5 lights x 100W MED
• alabaster style glass



190036117

9 light chandelier in Matte Nickel
26"W x 24"H
9 lights x 100W MED
72" Overall height
{12' wire} {4' chain}
• etched swirl glass



190006117

5 light chandelier in Matte Nickel
23"W x 20"H
5 lights x 100W MED
68" Overall height
{12' wire} {4' chain}
• etched swirl glass



190058117

3 light large pendant in Matte Nickel
16"W x 21"H
3 lights x 100W MED
69" Overall height
{12' wire} {4' chain}
• etched swirl glass



190005117

3 light chandelier in Matte Nickel
18"W x 14"H
3 lights x 100W MED
63" Overall height
{12' wire} {4' chain}
• etched swirl glass



190067117

2 light semi flush or pendant in Matte Nickel
12"W x 12"H
2 lights x 60W MED
{12' wire} {4' chain}
• etched swirl glass
• convertible semi-flush or chain hung pendant



190056117

1 light mini pendant in Matte Nickel
6"W x 6"H
1 light x 100W MED
42" Overall height
{12' wire} {2-12" + 2-6" rods}
• etched swirl glass



SL869278

- 2 light flush mount in Brushed Nickel
- 14"W x 6"H
- 2 lights x 60W MED
- etched swirl glass



190016117

- 2 light bath bar in Matte Nickel
- 16"W x 9"H x 8"EXT
- 2 lights x 100W MED
- etched swirl glass



190017117

- 3 light bath bar in Matte Nickel
- 23"W x 9"H x 8"EXT
- 3 lights x 100W MED
- etched swirl glass



190018117

- 4 light bath bar in Matte Nickel
- 31"W x 9"H x 8"EXT
- 4 lights x 100W MED
- etched swirl glass



190036763

9 light chandelier in Painted Bronze
26"W x 24"H
9 lights x 100W MED
72" Overall height
{12' wire} {4' chain}
• etched swirl glass



190006763

5 light chandelier in Painted Bronze
23"W x 20"H
5 lights x 100W MED
68" Overall height
{12' wire} {4' chain}
• etched swirl glass



190058763

3 light large pendant in Painted Bronze
16"W x 21"H
3 lights x 100W MED
69" Overall height
{12' wire} {4' chain}
• etched swirl glass



190005763

3 light chandelier in Painted Bronze
18"W x 14"H
3 lights x 100W MED
63" Overall height
{12' wire} {4' chain}
• etched swirl glass



190067763

2 light semi flush or pendant in Painted Bronze
12"W x 12"H
2 lights x 60W MED
{12' wire} {4' chain}
• etched swirl glass
• convertible semi-flush or chain hung pendant



190056763

1 light mini pendant in Painted Bronze
6"W x 6"H
1 light x 100W MED
42" Overall height
{12' wire} {2-12" + 2-6" rods}
• etched swirl glass



SL869263

2 light flush mount in Painted Bronze
14"W x 6"H
2 lights x 60W MED
• etched swirl glass



190016763



2 light bath bar in Painted Bronze
16"W x 9"H x 8"EXT
2 lights x 100W MED
• etched swirl glass



190017763



3 light bath bar in Painted Bronze
23"W x 9"H x 8"EXT
3 lights x 100W MED
• etched swirl glass



190018763



4 light bath bar in Painted Bronze
31"W x 9"H x 8"EXT
4 lights x 100W MED
• etched swirl glass



1205CH/20

5 light chandelier in Brushed Nickel
 26"W x 21"H
 5 lights x 60W MED
 82" Overall height
 {12' wire} {60" chain}
 • white glass



1203CH/20

3 light chandelier in Brushed Nickel
 19"W x 18"H
 3 lights x 60W MED
 79" Overall height
 {12' wire} {60" chain}
 • white glass



1201PL/20

1 light large pendant in Brushed Nickel
 15"W x 8"H
 1 light x 100W MED
 69" Overall height
 {12' wire} {60" chain}
 • white glass



1203PL/20

3 light large pendant in Brushed Nickel
 18"W x 25"H
 3 lights x 100W MED
 86" Overall height
 {12' wire} {6' chain}
 • white glass



1202CS/20

2 light convertible semi flush in Brushed Nickel
 15"W x 14"H
 2 lights x 100W MED
 75" Overall height
 {12' wire} {60" chain}
 • white glass
 • convertible semi-flush or chain hung pendant



1201PS/20

1 light mini pendant in Brushed Nickel
 8"W x 6"H
 1 light x 100W MED
 44" Overall height
 • white glass



1201WS/20 

1 light wall sconce in Brushed Nickel
6"W x 9"H x 8"EXT
1 light x 100W MED
• white glass



1202BB/20 

2 light bath bar in Brushed Nickel
15"W x 9"H x 7"EXT
2 lights x 100W MED
• white glass



1203BB/20 

3 light bath bar in Brushed Nickel
23"W x 9"H x 7"EXT
3 lights x 100W MED
• white glass



1204BB/20 

4 light bath bar in Brushed Nickel
32"W x 9"H x 7"EXT
4 lights x 100W MED
• white glass



1255CH/10

5 light chandelier in Oil Rubbed Bronze
26"W x 21"H
5 lights x 60W MED
82" Overall height
{12' wire} {60" chain}
• white glass




1253CH/10

3 light chandelier in Oil Rubbed Bronze
19"W x 18"H
3 lights x 60W MED
79" Overall height
{12' wire} {60" chain}
• white glass



1221PL/10

1 light large pendant in Oil Rubbed Bronze
15"W x 8"H
1 light x 100W MED
69" Overall height
{12' wire} {60" chain}
• white glass



1253PL/10

3 light large pendant in Oil Rubbed Bronze
18"W x 25"H
3 lights x 100W MED
86" Overall height
{12' wire} {60" chain}
• white glass



1252CS/10

2 light convertible semi flush in Oil Rubbed Bronze
15"W x 14"H
2 lights x 100W MED
75" Overall height
{12' wire} {60" chain}
• white glass
• convertible semi-flush or chain hung pendant



1251PS/10

1 light mini pendant in Oil Rubbed Bronze
8"W x 6"H
1 light x 100W MED
44" Overall height
• white glass



1251WS/10

1 light wall sconce in Oil Rubbed Bronze

6"W x 9"H x 8"EXT

1 light x 100W MED

- white glass

**1252BB/10**

2 light bath bar in Oil Rubbed Bronze

15"W x 9"H x 7"EXT

2 lights x 100W MED

- white glass

**1253BB/10**

3 light bath bar in Oil Rubbed Bronze

23"W x 9"H x 7"EXT

3 lights x 100W MED

- white glass

**1254BB/10**

4 light bath bar in Oil Rubbed Bronze

32"W x 9"H x 7"EXT

4 lights x 100W MED

- white glass



SL801078

5 light chandelier in Brushed Nickel
24"W x 13"H
5 lights x 100W MED
60" Overall height
{12' wire} {4' chain}
• etched glass



SL800378

5 light chandelier in Brushed Nickel
19"W x 16"H
5 lights x 60W CAND
64" Overall height
{12' wire} {4' chain}



M255078

1 light pendant in Brushed Nickel
16"W x 17"H
1 light x 150W MED
65" Overall height
{12' wire} {4' chain}
• alabaster style glass



SL801178

3 light chandelier in Brushed Nickel
21"W x 13"H
3 lights x 100W MED
60" Overall height
{12' wire} {4' chain}
• etched glass



SL847978

2 light pendant in Brushed Nickel
8"W x 12"H
2 lights x 60W CAND
60" Overall height
{12' wire} {4' chain}



SL823578

1 light pendant in Brushed Nickel
16"W x 13"H
1 light x 150W MED
61" Overall height
{12' wire} {4' chain}
• etched glass



SL861078

2 light convertible semi flush in Brushed Nickel
16"W x 13"H
2 lights x 100W MED
62" Overall height
{12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant.
Height when ceiling mounted 13"



SL878278

2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W MED
• etched glass

SL710341

3 light bath bar in Satin Pewter
24"W x 9"H x 8"EXT
3 lights x 100W MED
• etched glass



SL710441

4 light bath bar in Satin Pewter
30"W x 9"H x 8"EXT
4 lights x 100W MED
• etched glass



TK0018741

9 light chandelier in Satin Pewter
 29"W x 29"H
 9 lights x 60W MED
 51" Overall height
 {12' wire} {4' chain}
 • etched glass

**TK0017741**

5 lights chandelier in Satin Pewter
 24"W x 23"H
 5 lights x 100W MED
 51" Overall height
 {12' wire} {4' chain}
 • etched glass

**TK0016741**

3 light chandelier in Satin Pewter
 19"W x 23"H
 3 lights x 100W MED
 51" Overall height
 {12' wire} {4' chain}
 • etched glass

**TC0018741**

1 light pendant in Satin Pewter
 14"W x 9"H
 1 light x 100W MED
 57" Overall height
 {12' wire} {4' chain}
 • etched glass

**TC0015741**

2 light semi flush in Satin Pewter
 16"W x 14"H
 2 lights x 60W MED
 • etched glass

**TC0017741**

5 light pendant in Satin Pewter
 14"W x 26"H
 5 lights x 60W CAND
 74" Overall height
 {12' wire} {4' chain}

TC0016741

3 light pendant in Satin Pewter
 17"W x 24"H
 3 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}
 • etched glass



TN0009741 ↑↓

1 light wall sconce in Satin Pewter
5"W x 14"H x 6"EXT
1 light x 100W MED
• etched glass



TC0014741

1 light mini pendant in Satin Pewter
5"W x 8"H
1 light x 100W MED
44" Overall height
{12' wire} {3' chain}
• etched glass



TV0015741 ↑↓

2 light bath bar in Satin Pewter
18"W x 11"H x 7"EXT
2 lights x 100W MED
• etched glass



TV0016741 ↑↓

3 light bath bar in Satin Pewter
24"W x 11"H x 7"EXT
3 lights x 100W MED
• etched glass



TV0017741 ↑↓

4 light bath bar in Satin Pewter
30"W x 11"H x 7"EXT
4 lights x 100W MED
• etched glass



TV0018741 ↑↓

5 light bath bar in Satin Pewter
36"W x 11"H x 7"EXT
5 lights x 100W MED
• etched glass



TK0018704

9 light chandelier in Espresso
 29"W x 29"H
 9 lights x 60W MED
 51" Overall height
 {12' wire} {4' chain}
 • etched glass

**TK0017704**

5 lights chandelier in Espresso
 24"W x 23"H
 5 lights x 100W MED
 51" Overall height
 {12' wire} {4' chain}
 • etched glass

**TK0016704**

3 light chandelier in Espresso
 19"W x 23"H
 3 lights x 100W MED
 51" Overall height
 {12' wire} {4' chain}
 • etched glass

**TC0018704**

1 light pendant in Espresso
 14"W x 9"H
 1 light x 100W MED
 57" Overall height
 {12' wire} {4' chain}
 • etched glass

**TC0015704**

2 light semi flush in Espresso
 16"W x 14"H
 2 lights x 60W MED
 • etched glass

**TC0017704**

5 light pendant in Espresso
 14"W x 26"H
 5 lights x 60W CAND
 74" Overall height
 {12' wire} {4' chain}

TC0016704

3 light pendant in Espresso
 17"W x 24"H
 3 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}
 • etched glass



TN0009704 ↑↓

1 light wall sconce in Espresso
5"W x 14"H x 6"EXT
1 light x 100W MED
• etched glass



TC0014704

1 light mini pendant in Espresso
5"W x 8"H
1 light x 100W MED
44" Overall height
{12' wire} {3' chain}
• etched glass



TV0015704 ↑↓

2 light bath bar in Espresso
18"W x 11"H x 7"EXT
2 lights x 100W MED
• etched glass



TV0016704 ↑↓

3 light bath bar in Espresso
24"W x 11"H x 7"EXT
3 lights x 100W MED
• etched glass



TV0017704 ↑↓

4 light bath bar in Espresso
30"W x 11"H x 7"EXT
4 lights x 100W MED
• etched glass



TV0018704 ↑↓

5 light bath bar in Espresso
36"W x 11"H x 7"EXT
5 lights x 100W MED
• etched glass



TK0021217

9 light chandelier in Brushed Nickel
 30"W x 28"H
 9 lights x 100W MED
 76" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0020217**

5 light chandelier in Brushed Nickel
 25"W x 23"H
 5 lights x 100W MED
 71" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0019217**

3 light chandelier in Brushed Nickel
 20"W x 21"H
 3 lights x 100W MED
 69" Overall height
 {12' wire} {4' chain}

- etched white glass

**TC0021217**

3 light pendant in Brushed Nickel
 20"W x 24"H
 3 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}

- etched white glass

**TC0020217**

2 light semi flush in Brushed Nickel
 13"W x 12"H
 2 lights x 60W MED

- etched white glass

**TC0022217**

1 light pendant in Brushed Nickel
 13"W x 8"H
 1 light x 100W MED
 56" Overall height
 {12' wire} {4' chain}

- etched white glass

**TC0019217**

1 light mini pendant in Brushed Nickel
 5"W x 7"H
 1 light x 100W MED
 43" Overall height
 {12' wire} {3' chain}

- etched white glass



TN0010217

- 1 light wall sconce in Brushed Nickel
 5"W x 12"H x 8"EXT
 1 light x 100W MED
 • etched white glass

**TV0019217**

- 2 light bath bar in Brushed Nickel
 14"W x 7"H x 7"EXT
 2 lights x 100W MED
 • etched white glass

**TV0020217**

- 3 light bath bar in Brushed Nickel
 23"W x 7"H x 7"EXT
 3 lights x 100W MED
 • etched white glass

**TV0021217**

- 4 light bath bar in Brushed Nickel
 32"W x 7"H x 7"EXT
 4 lights x 100W MED
 • etched white glass

**TV0022217**

- 5 light bath bar in Brushed Nickel
 41"W x 7"H x 7"EXT
 5 lights x 100W MED
 • etched white glass



TK0021704

9 light chandelier in Espresso
 30"W x 28"H
 9 lights x 100W MED
 76" Overall height
 {12' wire} {4' chain}
 • champagne glass

**TK0020704**

5 light chandelier in Espresso
 25"W x 23"H
 5 lights x 100W MED
 71" Overall height
 {12' wire} {4' chain}
 • champagne glass

**TK0019704**

3 light chandelier in Espresso
 20"W x 21"H
 3 lights x 100W MED
 69" Overall height
 {12' wire} {4' chain}
 • champagne glass

**TC0021704**

3 light pendant in Espresso
 20"W x 24"H
 3 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}
 • champagne glass

**TC0020704**

2 light semi flush in Espresso
 13"W x 12"H
 2 lights x 60W MED
 • champagne glass

**TC0022704**

1 light pendant in Espresso
 13"W x 8"H
 1 light x 100W MED
 56" Overall height
 {12' wire} {4' chain}
 • champagne glass

**TC0019704**

1 light mini pendant in Espresso
 5"W x 7"H
 1 light x 100W MED
 43" Overall height
 {12' wire} {3' chain}
 • champagne glass



TN0010704 ↑↓

1 light wall sconce in Espresso
5"W x 12"H x 8"EXT
1 light x 100W MED
• champagne glass



TV0019704 ↑↓

2 light bath bar in Espresso
14"W x 7"H x 7"EXT
2 lights x 100W MED
• champagne glass



TV0020704 ↑↓

3 light bath bar in Espresso
23"W x 7"H x 7"EXT
3 lights x 100W MED
• champagne glass



TV0021704 ↑↓

4 light bath bar in Espresso
32"W x 7"H x 7"EXT
4 lights x 100W MED
• champagne glass



TV0022704 ↑↓

5 light bath bar in Espresso
41"W x 7"H x 7"EXT
5 lights x 100W MED
• champagne glass



TK0012117

9 light chandelier in Matte Nickel
 33"W x 34"H
 9 lights x 60W MED
 103" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0011117**

5 light chandelier in Matte Nickel
 26"W x 24"H
 5 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0010117**

3 light chandelier in Matte Nickel
 22"W x 21"H
 3 lights x 100W MED
 69" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0009117**

3 light chandelier in Matte Nickel
 20"W x 20"H
 3 lights x 100W MED
 90" Overall height
 {12' wire} {4' chain}

- etched white glass

**TG0002117**

3 light semi flush in Matte Nickel
 20"W x 12"H
 3 lights x 60W MED

- etched white glass

**TC0009117**

4 light chandelier in Matte Nickel
 27"W x 28"H
 4 lights x 100W MED
 76" Overall height
 {12' wire} {4' chain}

- etched white glass

TC0007117

1 light pendant in Matte Nickel
 16"W x 17"H
 1 light x 100W MED
 88" Overall height
 {12' wire} {4' chain}

- etched white glass



WRIGHT

TN0007117 

1 light wall sconce in Matte Nickel
5"W x 10"H x 7"EXT
1 light x 100W MED
• etched white glass



TC0008117

1 light mini pendant in Matte Nickel
5"W x 17"H
1 light x 100W MED
53" Overall height
{12' wire} {1-4" + 1-8" + 1-12" +
1-24" rods}
• etched white glass



TV0008117 

2 light bath bar in Matte Nickel
15"W x 11"H x 7"EXT
2 lights x 100W MED
• etched white glass



TV0009117 

3 light bath bar in Matte Nickel
24"W x 11"H x 7"EXT
3 lights x 100W MED
• etched white glass



TV0010117 

4 light bath bar in Matte Nickel
32"W x 11"H x 7"EXT
4 lights x 100W MED
• etched white glass



TK0012704

9 light chandelier in Espresso
 33"W x 34"H
 9 lights x 60W MED
 103" Overall height
 {12' wire} {4' chain}

- champagne glass

**190110704**

5 light chandelier in Espresso
 26"W x 24"H
 5 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}

- champagne glass

**190109704**

3 light chandelier in Espresso
 22"W x 21"H
 3 lights x 100W MED
 69" Overall height
 {12' wire} {4' chain}

- champagne glass

**TK0009704**

3 light chandelier in Espresso
 20"W x 20"H
 3 lights x 100W MED
 90" Overall height
 {12' wire} {4' chain}

- champagne glass

**190113704**

3 light semi flush in Espresso
 20"W x 12"H
 3 lights x 60W MED

- champagne glass

**190112704**

4 light pendant in Espresso
 27"W x 28"H
 4 lights x 100W MED
 76" Overall height
 {12' wire} {4' chain}

- champagne glass

TC0007704

1 light pendant in Espresso
 16"W x 17"H
 1 light x 100W MED
 88" Overall height
 {12' wire} {4' chain}

- champagne glass



TN0007704 ↑↓

1 light wall sconce in Espresso
5"W x 10"H x 7"EXT
1 light x 100W MED
• champagne glass



19011704

1 light mini pendant in Espresso
5"W x 17"H
1 light x 100W MED
53" Overall height
{12' wire} {1-4" + 1-8" + 1-12" +
1-24" rods}
• champagne glass



190114704 ↑↓

2 light bath bar in Espresso
15"W x 11"H x 7"EXT
2 lights x 100W MED
• champagne glass



190115704 ↑↓

3 light bath bar in Espresso
24"W x 11"H x 7"EXT
3 lights x 100W MED
• champagne glass



190116704 ↑↓

4 light bath bar in Espresso
32"W x 11"H x 7"EXT
4 lights x 100W MED
• champagne glass



1305CH/20

5 light chandelier in Brushed Nickel

22"W x 23"H
5 lights x 60W MED
84" Overall height
{12' wire} {60" chain}

- white glass



1303CH/20

3 light chandelier in Brushed Nickel

20"W x 13"H
3 lights x 60W MED
74" Overall height
{12' wire} {60" chain}

- white glass



1301PS/20

1 light mini pendant in Brushed Nickel

4"W x 6"H
1 light x 60W MED
44" Overall height

- white glass



1301PL/20

1 light large pendant in Brushed Nickel

14"W x 18"H
1 light x 100W MED
79" Overall height
{12' wire} {60" chain}

- white glass



1303FM/20

3 light flush mount in Brushed Nickel

15"W x 9"H
3 lights x 60W MED

- white glass

1301WS/20

- 1 light wall sconce in Brushed Nickel
 5"W x 8"H x 7"EXT
 1 light x 60W MED
 • white glass

**1302BB/20**

- 2 light bath bar in Brushed Nickel
 14"W x 9"H x 7"EXT
 2 lights x 60W MED
 • white glass

**1303BB/20**

- 3 light bath bar in Brushed Nickel
 22"W x 9"H x 7"EXT
 3 lights x 60W MED
 • white glass

**1304BB/20**

- 4 light bath bar in Brushed Nickel
 31"W x 9"H x 7"EXT
 4 lights x 60W MED
 • white glass



1355CH/10

5 light chandelier in Oil Rubbed Bronze
22"W x 23"H
84" Overall height
{12' wire} {60" chain}
• white glass



1353CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 13"H
3 lights x 60W MED
74" Overall height
{12' wire} {60" chain}
• white glass



1351PL/10

1 light large pendant in Oil Rubbed Bronze
14"W x 18"H
1 light x 100W MED
79" Overall height
{12' wire} {60" chain}
• white glass



1353FM/10

3 light flush mount in Oil Rubbed Bronze
15"W x 9"H
3 lights x 60W MED
• white glass



1351PS/10

1 light mini pendant in Oil Rubbed Bronze
4"W x 6"H
1 light x 60W MED
44" Overall height
• white glass



1351WS/10 

1 light wall sconce in Oil Rubbed Bronze
5"W x 8"H x 7"EXT
1 light x 60W MED
• white glass



1352BB/10 

2 light bath bar in Oil Rubbed Bronze
14"W x 9"H x 7"EXT
2 lights x 60W MED
• white glass



1353BB/10 

3 light bath bar in Oil Rubbed Bronze
22"W x 9"H x 7"EXT
3 lights x 60W MED
• white glass



1354BB/10 

4 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 7"EXT
4 lights x 60W MED
• white glass



1105CH/20

5 light chandelier in Brushed Nickel
22"W x 24"H
5 lights x 75W MED
85" Overall height
{12' wire} {60" chain}
• white glass



1103CH/20

3 light chandelier in Brushed Nickel
20"W x 22"H
3 lights x 70W MED
83" Overall height
{12' wire} {60" chain}
• white glass



1103FM/20

3 light flush mount in Brushed Nickel
13"W x 6"H
3 light x 60W MED
• white glass



1103PL/20

3 light large pendant in Brushed Nickel
18"W x 22"H
3 lights x 60W MED
83" Overall height
{12' wire} {60" chain}
• white glass



1102CS/20

2 light semi flush/pendant convertible in Brushed Nickel
17"W x 14"H
2 lights x 60W MED
75" Overall height
{12' wire} {60" chain}
• white glass



1101PS/20

1 light mini pendant in Brushed Nickel
5"W x 6"H
1 light x 75W MED
44" Overall height
• white glass



1101WS/20

- 1 light wall sconce in Brushed Nickel
5"W x 19"H x 7"EXT
1 light x 75W MED
- white glass



1102BB/20

- 2 light bath bar in Brushed Nickel
14"W x 11"H x 7"EXT
2 lights x 75W MED
- white glass



1103BB/20

- 3 light bath bar in Brushed Nickel
23"W x 11"H x 7"EXT
3 lights x 75W MED
- white glass



1104BB/20

- 4 light bath bar in Brushed Nickel
32"W x 11"H x 7"EXT
4 lights x 75W MED
- white glass





CHATHAM



1155CH/10

5 light chandelier in Oil Rubbed Bronze
22"W x 24"H
5 lights x 75W MED
85" Overall height
{12' wire} {60" chain}

- white glass



1153CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 22"H
3 lights x 70W MED
83" Overall height
{12' wire} {60" chain}

- white glass



1153FM/10

3 light flush mount in Oil Rubbed Bronze
13"W x 6"H
3 light x 60W MED

- white glass



1153PL/10

3 light large pendant in Oil Rubbed Bronze
18"W x 22"H
3 lights x 60W MED
83" Overall height
{12' wire} {60" chain}

- white glass



1152CS/10

2 light semi flush/pendant convertible in Oil Rubbed Bronze
17"W x 14"H
2 lights x 60W MED
75" Overall height
{12' wire} {60" chain}

- white glass



1151PS/10

1 light mini pendant in Oil Rubbed Bronze
5"W x 6"H
1 light x 75W MED
44" Overall height

- white glass



1151WS/20

- 1 light wall sconce in Oil Rubbed Bronze
- 5"W x 19"H x 7"EXT
- 1 light x 75W MED
- white glass



1152BB/20

- 2 light bath bar in Oil Rubbed Bronze
- 14"W x 11"H x 7"EXT
- 2 lights x 75W MED
- white glass



1153BB/20

- 3 light bath bar in Oil Rubbed Bronze
- 23"W x 11"H x 7"EXT
- 3 lights x 75W MED
- white glass



1154BB/20

- 4 light bath bar in Oil Rubbed Bronze
- 32"W x 11"H x 7"EXT
- 4 lights x 75W MED
- white glass



PENDANTS





PENDANTS

LC411-PW-15 **LED**

QUINCY
 1 light pendant in Chrome
 14"W x 7"H
 1 light x 12W LED, 3000K, 80
 CRI, 960 Lumens
 47" Overall height
 {12" wire} {4" chain}

- white glass
- dimmable

**CN770144**

CLASSIC LOFT
 1 light pendant in White
 11"W x 6"H
 1 light x 100W MED
 67" Overall height
 {12" wire}

**CN770148**

CLASSIC LOFT
 1 light pendant in Weathered Zinc
 11"W x 6"H
 1 light x 100W MED
 67" Overall height
 {12" wire}

**CN770141**

CLASSIC LOFT
 1 light pendant in Oil Rubbed Bronze
 11"W x 6"H
 1 light x 100W MED
 67" Overall height
 {12" wire}

**CN200142**

BLAKESLEY
 1 light pendant in Brushed Nickel
 14"W x 11"H
 1 light x 100W MED
 62" Overall height
 {12" wire} {60" chain}

- frosted glass

**CN200141**

BLAKESLEY
 1 light pendant in Oil Rubbed Bronze
 14"W x 11"H
 1 light x 100W MED
 62" Overall height
 {12" wire} {60" chain}

- frosted glass

**CN200152**

BLAKESLEY
 1 light pendant in Brushed Nickel
 8"W x 11"H
 1 light x 100W MED
 62" Overall height
 {12" wire} {60" chain}

- frosted glass

**CN200151**

BLAKESLEY
 1 light pendant in Oil Rubbed Bronze
 8"W x 11"H
 1 light x 100W MED
 62" Overall height
 {12" wire} {60" chain}

- frosted glass



PENDANTS



PENDANTS

7681PL/20

LIBERTY PARK

- 1 light pendant in Brushed Nickel
- 12"W x 12"H
- 1 light x 100W MED
- 73" Overall height {12' wire} {60" chain}
- prismatic clear glass



7681PL/10

LIBERTY PARK

- 1 light pendant in Oil Rubbed Bronze
- 12"W x 12"H
- 1 light x 100W MED
- 73" Overall height {12' wire} {60" chain}
- prismatic clear glass



7691PL/20

LIBERTY PARK

- 1 light mini pendant in Brushed Nickel
- 17"W x 17"H
- 1 light x 100W MED
- 78" Overall height {12' wire} {60" chain}
- prismatic clear glass



7691PL/10

LIBERTY PARK

- 1 light mini pendant Oil Rubbed Bronze
- 17"W x 17"H
- 1 light x 100W MED
- 78" Overall height {12' wire} {60" chain}
- prismatic clear glass



CN160381

PARK CITY

- 3 light pendant/semi flush dual mount in Oil Rubbed Bronze & Wood Grain
- 16"W x 13"H
- 3 lights x 100W Med
- 74" Overall height {12' wire} {60" chain}
- light beige scavo glass



CN129041

BECKETT

- 1 light pendant in Oil Rubbed Bronze
- 12"W x 13"H
- 1 light x 60W MED **shown Bulb 1092***
- 74" Overall height {12' wire} {60" chain}
- clear white glass
- *not included—See page 324*



CN120041

BECKETT

- 1 light pendant in Oil Rubbed Bronze
- 12"W x 13"H
- 1 light x 60W MED*
- 74" Overall height {12' wire} {60" chain}
- opal white glass
- *not included—See page 324*



PENDANTS

CN129281

BECKETT

3 light pendant/semi flush dual mount in
Oil Rubbed Bronze

14"W x 7"H

3 lights x 60W MED **shown Bulb 1092***

68" Overall height
{12' wire} {60" chain}

• clear glass

**not included—See page 324*



CN120281

BECKETT

3 light pendant/semi flush dual mount in
Oil Rubbed Bronze

14"W x 7"H

3 lights x 60W MED*

68" Overall height
{12' wire} {60" chain}

• opal white glass

**not included—See page 324*



CN15712

WILLIAMSPORT

1 light pendant in Brushed Nickel

11"W x 15"H

1 light x 100W MED **shown Bulb 1092***

76" Overall height
{12' wire} {60" chain}

**not included—See page 324*



CN15711

WILLIAMSPORT

1 light pendant in Oil Rubbed Bronze

11"W x 15"H

1 light x 100W MED **shown Bulb 1092***

76" Overall height
{12' wire} {60" chain}

**not included—See page 324*



CN15832

WILLIAMSPORT

3 light pendant in Brushed Nickel

10"W x 16"H

3 lights x 60W MED **shown Bulb 1092***

44" Overall height

**not included—See page 324*



CN15831

WILLIAMSPORT

3 light pendant in Oil Rubbed Bronze

10"W x 16"H

3 lights x 60W MED **shown Bulb 1092***

44" Overall height

**not included—See page 324*



CN250151

WILLIAMSPORT

1 light pendant in Oil Rubbed Bronze

8"W x 8"H

1 light x 100W MED **shown Bulb 1092***

75" Overall height
{12' wire} {60" chain}

**not included—See page 324*



CN251551

WILLIAMSPORT

1 light pendant in Oil Rubbed Bronze

15"W x 9"H

1 light x 100W MED **shown Bulb 1092***

70" Overall height
{12' wire} {60" chain}

**not included—See page 324*

**not included—See page 324*



PENDANTS

SL824641

HARMONY
 3 light pendant in Satin Pewter
 21"W x 25"H
 3 lights x 100W MED
 97" Overall height
 {12' wire} {6' chain}
 • white marble glass

**SL824662**

HARMONY
 3 light pendant in Aged Bronze
 21"W x 25"H
 3 lights x 100W MED
 97" Overall height
 {12' wire} {6' chain}
 • champagne marble glass

**SL829278**

PRESTIGE
 3 light pendant in Brushed Nickel
 18"W x 23"H
 3 lights x 100W MED
 95" Overall height
 {12' wire} {6' chain}
 • alabaster style glass

**SL829222**

PRESTIGE
 3 light pendant in Sable Bronze
 18"W x 23"H
 3 lights x 100W MED
 95" Overall height
 {12' wire} {6' chain}
 • cognac edged glass

**SL893572**

TRITON
 2 light pendant in Moonlight Silver
 19"W x 24"H
 2 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}
 • tea stained glass

**SL893522**

TRITON
 2 light pendant in Sable Bronze
 19"W x 24"H
 2 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}
 • tea stained glass

**2203CS/10**

SANTE FE
 3 light pendant in Oil Rubbed Bronze
 17"W x 16"H
 3 lights x 60W MED
 77" Overall height
 {12' wire} {60" chain}
 • white glass

**2203PL/10**

SANTE FE
 3 light pendant in Oil Rubbed Bronze
 17"W x 14"H
 3 lights x 100W MED
 75" Overall height
 {12' wire} {60" chain}
 • white glass



PENDANTS

2401PL/20

TRIBECCA

1 light pendant in Brushed Nickel

12"W x 16"H

1 light x 60W CAND

77" Overall height

{12' wire} {60" chain}

- white glass



2401PL/10

TRIBECCA

1 light pendant in Oil Rubbed Bronze

12"W x 16"H

1 light x 60W CAND

77" Overall height

{12' wire} {60" chain}

- white glass



SL806678

PENDENZA

3 light pendant in Brushed Nickel

20"W x 19"H

3 lights x 60W CAND

67" Overall height

{12' wire} {4' chain}

- white cotton weave fabric shade



SL806615

PENDENZA

3 light pendant in Oil Rubbed Bronze

20"W x 19"H

3 lights x 60W CAND

67" Overall height

{12' wire} {4' chain}

- white cotton weave fabric shade



190043217

PITTMAN

2 light pendant in Brushed Nickel

15"W x 15"H

2 lights x 100W MED

60" Overall height

{12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant



190043719

PITTMAN

2 light pendant in Sienna Bronze

15"W x 15"H

2 lights x 100W MED

60" Overall height

{12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant



190061217

PITTMAN

3 light pendant in Brushed Nickel

18"W x 20"H

3 lights x 100W MED

68" Overall height

{12' wire} {4' chain}

- etched glass



190061719

PITTMAN

3 light pendant in Sienna Bronze

18"W x 20"H

3 lights x 100W MED

68" Overall height

{12' wire} {4' chain}

- etched glass



PENDANTS

SL823478

TAHOE

- 1 light pendant in Brushed Nickel
 12"W x 9"H
 1 light x 150W MED
 57" Overall height
 {12' wire} {4' chain}
- alabaster style glass

**SL823463**

TAHOE

- 1 light mini pendant in Painted Bronze
 12"W x 9"H
 1 light x 150W MED
 57" Overall height
 {12' wire} {4' chain}
- alabaster style glass

**SL861478**

TAHOE

- 2 light pendant in Brushed Nickel
 12"W x 11"H
 2 lights x 100W MED
 {12' wire} {4' chain}
- alabaster style glass
 - convertible semi-flush or chain hung pendant

**SL861463**

TAHOE

- 2 light pendant in Painted Bronze
 12"W x 11"H
 2 lights x 100W MED
 {12' wire} {4' chain}
- alabaster style glass
 - convertible semi-flush or chain hung pendant

**SL823678**

TAHOE

- 3 light pendant in Brushed Nickel
 20"W x 28"H
 3 lights x 100W MED
 100" Overall height
 {12' wire} {6' chain}
- alabaster style glass
 - etched white diffuser

**SL823663**

TAHOE

- 3 light pendant in Painted Bronze
 20"W x 28"H
 3 lights x 100W MED
 100" Overall height
 {12' wire} {6' chain}
- alabaster style glass
 - etched white diffuser

**SL891678**

BELLA

- 1 light pendant in Brushed Nickel
 16"W x 18"H
 1 light x 150W MED
 66" Overall height
 {12' wire} {4' chain}
- etched glass

**SL891615**

BELLA

- 1 light pendant in Oil Rubbed Bronze
 16"W x 18"H
 1 light x 150W MED
 66" Overall height
 {12' wire} {4' chain}
- etched glass



PENDANTS

SL860778

BELLA

3 light pendant in Brushed Nickel

16"W x 12"H

3 lights x 60W MED

59" Overall height

{12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant

**SL860715**

BELLA

3 light pendant in Oil Rubbed Bronze

16"W x 12"H

3 lights x 60W MED

59" Overall height

{12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant

**SL891778**

BELLA

3 light pendant in Brushed Nickel

20"W x 25"H

3 lights x 100W MED

72" Overall height

{12' wire} {4' chain}

- etched glass

**SL891715**

BELLA

3 light pendant in Oil Rubbed Bronze

20"W x 25"H

3 lights x 100W MED

72" Overall height

{12' wire} {4' chain}

- etched glass

**1002CS/20**

BRIGHTON

2 light convertible in Brushed Nickel

16"W x 13"H

2 lights x 60W MED

74" Overall height

{12' wire} {60" chain}

- white glass

**1052CS/10**

BRIGHTON

2 light convertible in Oil Rubbed Bronze

16"W x 13"H

2 lights x 60W MED

74" Overall length

{12' wire} {60" chain}

- white glass

**1003PL/20**

BRIGHTON

3 light large pendant in Brushed Nickel

13"W x 6"H

3 lights x 60W MED

83" Overall height

{12' wire} {60" chain}

- white glass

**1053PL/10**

BRIGHTON

3 light large pendant in Oil Rubbed Bronze

13"W x 6"H

3 lights x 60W MED

83" Overall length

{12' wire} {60" chain}

- white glass

**PENDANTS**

SL826678

RIVA

3 light pendant in Brushed Nickel

16"W x 19"H

3 lights x 100W MED

67" Overall height

{12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL826663**

RIVA

3 light pendant in Painted Bronze

16"W x 19"H

3 lights x 100W MED

67" Overall height

{12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL825378**

ECLIPSE

3 light pendant in Brushed Nickel

19"W x 15"H

3 lights x 100W MED

67" Overall height

{12' wire} {4' chain}

- alabaster style glass
- convertible semi-flush or chain hung pendant. Height when ceiling mounted 15"
- etched white diffuser

**SL825363**

ECLIPSE

3 light pendant in Painted Bronze

19"W x 15"H

3 lights x 100W MED

67" Overall height

{12' wire} {4' chain}

- alabaster style glass
- convertible semi-flush or chain hung pendant. Height when ceiling mounted 15"
- etched white diffuser

**190067117**

TIA

2 light pendant in Matte Nickel

12"W x 12"H

2 lights x 60W MED

{12' wire} {4' chain}

- etched swirl glass
- convertible semi-flush or chain hung pendant

**190067763**

TIA

2 light semi flush or pendant in Painted Bronze

12"W x 12"H

2 lights x 60W MED

{12' wire} {4' chain}

- etched swirl glass
- convertible semi-flush or chain hung pendant

**190058117**

TIA

3 light large pendant in Matte Nickel

16"W x 21"H

3 lights x 100W MED

69" Overall height

{12' wire} {4' chain}

- etched swirl glass

**190058763**

TIA

3 light large pendant in Painted Bronze

16"W x 21"H

3 lights x 100W MED

69" Overall height

{12' wire} {4' chain}

- etched swirl glass



PENDANTS

SL823578

WHITMORE

- 1 light pendant in Brushed Nickel
 16"W x 13"H
 1 light x 150W MED
 61" Overall height
 {12' wire} {4' chain}
- etched glass

**SL861078**

WHITMORE

- 2 light convertible in Brushed Nickel
 16"W x 13"H
 2 lights x 100W MED
 62" Overall height
 {12' wire} {4' chain}
- etched glass
 - convertible semi-flush or chain hung pendant. Height when ceiling mounted 13"

**M255078**

WHITMORE

- 1 light pendant in Brushed Nickel
 16"W x 17"H
 1 light x 150W MED
 65" Overall height
 {12' wire} {4' chain}
- alabaster style glass

**TC0018741**

HAVEN

- 1 light pendant in Satin Pewter
 14"W x 9"H
 1 light x 100W MED
 57" Overall height
 {12' wire} {4' chain}
- etched glass

**TC0018704**

HAVEN

- 1 light pendant in Espresso
 14"W x 9"H
 1 light x 100W MED
 57" Overall height
 {12' wire} {4' chain}
- etched glass

**TC0016741**

HAVEN

- 3 light pendant in Satin Pewter
 17"W x 24"H
 3 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}
- etched glass

**TC0016704**

HAVEN

- 3 light pendant in Espresso
 17"W x 24"H
 3 lights x 100W MED
 72" Overall height
 {12' wire} {4' chain}
- etched glass

**PENDANTS**

1201PL/20

CONWAY
1 light large pendant in Brushed Nickel
15"W x 8"H
1 light x 100W MED
69" Overall height
{12' wire} {60" chain}
• white glass



1221PL/10

CONWAY
1 light large pendant in Oil Rubbed Bronze
15"W x 8"H
1 light x 100W MED
69" Overall height
{12' wire} {60" chain}
• white glass



1202CS/20

CONWAY
2 light pendant in Brushed Nickel
15"W x 14"H
2 lights x 100W MED
75" Overall height
{12' wire} {60" chain}
• white glass
• convertible semi-flush or chain hung pendant



1252CS/10

CONWAY
2 light pendant in Oil Rubbed Bronze
15"W x 14"H
2 lights x 100W MED
75" Overall height
{12' wire} {60" chain}
• white glass
• convertible semi-flush or chain hung pendant



1203PL/20

CONWAY
3 light large pendant in Brushed Nickel
18"W x 25"H
3 lights x 100W MED
86" Overall height
{12' wire} {6' chain}
• white glass



1253PL/10

CONWAY
3 light large pendant in Oil Rubbed Bronze
18"W x 25"H
3 lights x 100W MED
86" Overall height
{12' wire} {60" chain}
• white glass



TC0007117

WRIGHT
1 light pendant in Matte Nickel
16"W x 17"H
1 light x 100W MED
88" Overall height
{12' wire} {4' chain}
• etched white glass



TC0007704

WRIGHT
1 light pendant in Espresso
16"W x 17"H
1 light x 100W MED
88" Overall height
{12' wire} {4' chain}
• champagne glass



PENDANTS



PENDANTS



PENDANTS

TC0022217

TREME

1 light pendant in Brushed Nickel

13"W x 8"H

1 light x 100W MED

56" Overall height

{12' wire} {4' chain}

- etched white glass

**TC0022704**

TREME

1 light pendant in Espresso

13"W x 8"H

1 light x 100W MED

56" Overall height

{12' wire} {4' chain}

- champagne glass

**TC0021217**

TREME

3 light pendant in Brushed Nickel

20"W x 24"H

3 lights x 100W MED

72" Overall height

{12' wire} {4' chain}

- etched white glass

**TC0021704**

TREME

3 light pendant in Espresso

20"W x 24"H

3 lights x 100W MED

72" Overall height

{12' wire} {4' chain}

- champagne glass

**1301PL/20**

JACKSON

1 light large pendant in Brushed Nickel

14"W x 18"H

1 light x 100W MED

79" Overall height

{12' wire} {60" chain}

- white glass

**1351PL/10**

JACKSON

1 light large pendant in Oil Rubbed Bronze

14"W x 18"H

1 light x 100W MED

79" Overall height

{12' wire} {60" chain}

- white glass

**PENDANTS**

1102CS/20

CHATHAM

2 light semi flush/pendant
convertible in Brushed Nickel

17"W x 14"H

2 lights x 60W MED

75" Overall height

{12" wire} {60" chain}

- white glass



1152CS/10

CHATHAM

2 light semi flush/pendant convertible
in Oil Rubbed Bronze

17"W x 14"H

2 lights x 60W MED

75" Overall height

{12" wire} {60" chain}

- white glass



1103PL/20

CHATHAM

3 light large pendant in Brushed Nickel

18"W x 22"H

3 lights x 60W MED

83" Overall height

{12" wire} {60" chain}

- white glass



1153PL/10

CHATHAM

3 light large pendant in Oil Rubbed Bronze

18"W x 22"H

3 lights x 60W MED

83" Overall height

{12" wire} {60" chain}

- white glass



PENDANTS



PENDANTS

CN160151

PARK CITY

1 light mini pendant in Oil Rubbed Bronze & Wood Grain

5"W x 8"H
1 light x 100W Med
44" Overall height
{12" wire} {60" chain}

- light beige scavo glass



CN230157

GEORGETOWN

1 light mini pendant in Weathered Zinc

6"W x 8"H
1 light x 100W Med*
61" Overall height
{12" wire} {60" chain}

- mercury glass
- *not included—See page 324*



CN129151

BECKETT

1 light mini pendant in Oil Rubbed Bronze

6"W x 7"H
1 light x 60W MED* **shown Bulb 1092***
68" Overall height
{12" wire} {60" chain}

- clear glass
- *not included—See page 324*



CN120151

BECKETT

1 light mini pendant in Oil Rubbed Bronze

6"W x 7"H
1 light x 60W MED*
68" Overall height
{12" wire} {60" chain}

- opal white glass
- *not included—See page 324*



CN170152

CASUAL MISSION

1 light mini pendant in Brushed Nickel

5"W x 7"H
1 light x 100W Med
44" Overall height

- white lined glass



CN170151

CASUAL MISSION

1 light mini pendant in Oil Rubbed Bronze

5"W x 7"H
1 light x 100W Med
44" Overall height

- white lined glass



SL825641

HARMONY

1 light mini pendant in Satin Pewter

7"W x 8"H
1 light x 100W MED
44" Overall height
{12" wire} {2-12" + 2-6" rods}

- white marble glass



SL825662

HARMONY

1 light mini pendant in Aged Bronze

7"W x 8"H
1 light x 100W MED
44" Overall height
{12" wire} {2-12" + 2-6" rods}

- champagne marble glass




MINI PENDANTS

SL829678**PRESTIGE**

1 light mini pendant in Brushed Nickel
 10"W x 6"H
 1 light x 100W MED
 42" Overall height
 {12' wire} {2-12" + 2-6" rods}

- alabaster style glass

**SL829663****PRESTIGE**


1 light mini pendant in Painted Bronze
 10"W x 6"H
 1 light x 100W MED
 42" Overall height
 {12' wire} {2-12" + 2-6" rods}

- alabaster style glass

**SL829822****PRESTIGE**

1 light mini pendant in Sable Bronze
 10"W x 6"H
 1 light x 100W MED
 42" Overall height
 {12' wire} {2-12" + 2-6" rods}

- cognac edged glass

**2101PS/20****BRISTOL LANE**

1 light mini pendant in Brushed Nickel
 7"W x 43"H
 1 light x 100W MED
 43" Overall length

- white glass

**2101PS/10****BRISTOL LANE**

1 light mini pendant in Brushed Nickel
 7"W x 43"H
 1 light x 100W MED
 43" Overall height

- white glass

**SL893472****TRITON**

1 light mini pendant in Moonlight Silver
 5"W x 12"H
 1 light x 100W MED
 48" Overall height
 {12' wire} {2-12" + 2-6" rods}

- tea stained glass

**SL893422****TRITON**

1 light mini pendant in Sable Bronze
 5"W x 12"H
 1 light x 100W MED
 48" Overall height
 {12' wire} {2-12" + 2-6" rods}

- tea stained glass

**2201PS/10****SANTE FE**

1 light mini pendant in Oil Rubbed Bronze
 6"W x 44"H
 1 light x 100W MED
 44" Overall height

- white glass

**M251878****ALLURE**

1 light pendant in Brushed Nickel
 6"W x 26"H
 1 light x 100W MED
 74" Overall height
 {12' wire} {1-4" + 1-8" + 1-12" + 1-24" rods}

- bone linen shimmer



MINI PENDANTS

SL891078

PENDENZA
1 light mini pendant in Brushed Nickel
5"W x 20"H
1 light x 100W MED
68" Overall height
{12' wire} {4' chain}
• etched glass



SL891015

PENDENZA
1 light mini pendant in Oil Rubbed Bronze
5"W x 20"H
1 light x 100W MED
68" Overall height
{12' wire} {4' chain}
• etched glass



190060217

PITTMAN
1 light mini pendant in Brushed Nickel
5"W x 8"H
1 light x 100W MED
56" Overall height
{12' wire} {1-4" + 1-8" + 1-12" = 1-24" rods}
• etched glass



190060719

PITTMAN
1 light mini pendant in Sienna Bronze
5"W x 8"H
1 light x 100W MED
56" Overall height
{12' wire} {1-4" + 1-8" + 1-12" = 1-24" rods}
• etched glass



SL891578

BELLA
1 light mini pendant in Brushed Nickel
8"W x 15"H
1 light x 100W MED
63" Overall height
{12' wire} {4' chain}
• etched glass



SL891515

BELLA
1 light mini pendant in Oil Rubbed Bronze
8"W x 15"H
1 light x 100W MED
63" Overall height
{12' wire} {4' chain}
• etched glass



1001PS/20

BRIGHTON
1 light mini pendant in Brushed Nickel
6"W x 6"H
1 light x 75W MED
44" Overall height
• white glass



1051PS/10

BRIGHTON
1 light mini pendant in Oil Rubbed Bronze
6"W x 6"H
1 light x 75W MED
44" Overall length
• white glass



MINI PENDANTS



MINI PENDANTS

SL820678

RIVA

1 light mini pendant in Brushed Nickel

6"W x 21"H

1 light x 100W MED

69" Overall height

{12' wire} {4' chain}

- reeded center column
- alabaster style glass



SL820663

RIVA

1 light mini pendant in Painted Bronze

6"W x 21"H

1 light x 100W MED

69" Overall height

{12' wire} {4' chain}

- reeded center column
- alabaster style glass



SL829178

ECLIPSE

1 light mini pendant in Brushed Nickel

6"W x 26"H

1 light x 100W MED

56" Overall height

{12' wire} {2-12" + 1-6" rod}

- alabaster style glass



SL829163

ECLIPSE

1 light mini pendant in Painted Bronze

6"W x 26"H

1 light x 100W MED

56" Overall height

{12' wire} {2-12" + 1-6" rod}

- alabaster style glass



190056117

TIA

1 light mini pendant in Matte Nickel

6"W x 6"H

1 light x 100W MED

42" Overall height

{12' wire} {2-12" + 2-6" rods}

- etched swirl glass



190056763

TIA

1 light mini pendant in Painted Bronze

6"W x 6"H

1 light x 100W MED

42" Overall height

{12' wire} {2-12" + 2-6" rods}

- etched swirl glass



1201PS/20

CONWAY

1 light mini pendant in Brushed Nickel

8"W x 6"H

1 light x 100W MED

44" Overall height

- white glass



1251PS/10

CONWAY

1 light mini pendant in Oil Rubbed Bronze

8"W x 6"H

1 light x 100W MED

44" Overall height

- white glass



MINI PENDANTS

TC0014741

HAVEN

1 light mini pendant in Satin Pewter

5"W x 8"H

1 light x 100W MED

44" Overall height

{12' wire} {3' chain}

- etched glass

**TC0014704**

HAVEN

1 light mini pendant in Espresso

5"W x 8"H

1 light x 100W MED

44" Overall height

{12' wire} {3' chain}

- etched glass

**TC0019217**

TREME

1 light mini pendant in Brushed Nickel

5"W x 7"H

1 light x 100W MED

43" Overall height

{12' wire} {3' chain}

- etched white glass

**TC0019704**

TREME

1 light mini pendant in Espresso

5"W x 7"H

1 light x 100W MED

43" Overall height

{12' wire} {3' chain}

- champagne glass

**TC0008117**

WRIGHT

1 light mini pendant in Matte Nickel

5"W x 17"H

1 light x 100W MED

53" Overall height

{12' wire} {1-4" + 1-8" + 1-12" + 1-24" rods}

- etched white glass

**190111704**

WRIGHT

1 light mini pendant in Espresso

5"W x 17"H

1 light x 100W MED

53" Overall height

{12' wire} {1-4" + 1-8" + 1-12" + 1-24" rods}

- champagne glass

**1301PS/20**

JACKSON

1 light mini pendant in Brushed Nickel

4"W x 6"H

1 light x 60W MED

44" Overall height

- white glass

**1351PS/10**

JACKSON

1 light mini pendant in Oil Rubbed Bronze

4"W x 6"H

1 light x 60W MED

44" Overall height

- white glass

**MINI PENDANTS**



MINI PENDANTS

1101PS/20

CHATHAM

1 light mini pendant in Brushed Nickel

5"W x 6"H

1 light x 75W MED

{44" Overall height

- white glass



1151PS/10

CHATHAM

1 light mini pendant in Oil Rubbed Bronze

5"W x 6"H

1 light x 75W MED

44" Overall height

- white glass



7661PS/20

LIBERTY PARK

1 light mini pendant in Brushed Nickel

8"W x 8"H

1 light x 100W MED

72" Overall height

{12' wire} {60" chain}

- prismatic clear glass
- matching flush mounts available on page 162



7661PS/10

LIBERTY PARK

1 light mini pendant in Oil Rubbed Bronze

8"W x 8"H

1 light x 100W MED

72" Overall height

{12' wire} {60" chain}

- prismatic clear glass
- matching flush mounts available on page 162



LC413-10-80 **LED**

CHARLETON

1 light mini pendant in Chrome

8"W x 8"H

1 light x 7W LED, 3000L, 80 CRI

560 Lumens, Dimmable

46" Overall height

- white glass



MINI PENDANTS

FOYER





FOYER

TC0023217

PRESTIGE
4 light pendant in Brushed Nickel
17"W x 28"H
4 lights x 60W CAND
100" Overall height
{12' wire} {6' chain}



TC0023722

PRESTIGE
4 light pendant in Sable Bronze
17"W x 28"H
4 lights x 60W CAND
100" Overall height
{12' wire} {6' chain}



SL893672

TRITON
4 light pendant in Moonlight Silver
18"W x 33"H
4 lights x 60W CAND
81" Overall height
{12' wire} {4' chain}



SL893622

TRITON
4 light pendant in Sable Bronze
18"W x 33"H
4 lights x 60W CAND
81" Overall height
{12' wire} {4' chain}



SL891878

BELLA

6 light pendant in Brushed Nickel

17"W x 32"H

6 lights x 60W CAND

79" Overall height
{12' wire} {4' chain}



SL891815

BELLA

6 light pendant in Oil Rubbed Bronze

17"W x 32"H

6 lights x 60W CAND

79" Overall height
{12' wire} {4' chain}



TC0017741

HAVEN
5 light pendant in Satin Pewter
14"W x 26"H
5 lights x 60W CAND
74" Overall height
{12' wire} {4' chain}



TC0017704

HAVEN
5 light pendant in Espresso
14"W x 26"H
5 lights x 60W CAND
74" Overall height
{12' wire} {4' chain}



7704FY/20

4 light foyer in Brushed Nickel
11"W x 21"H
4 lights x 60W E12
82" Overall height
{12' wire} {60" chain}



7704FY/10

4 light foyer in Oil Rubbed Bronze
11"W x 21"H
4 lights x 60W E12
82" Overall height
{12' wire} {60" chain}



FOYER

SL847978

WHITMORE
2 light pendant in Brushed Nickel
8"W x 12"H
2 lights x 60W CAND
60" Overall height
{12' wire} {4' chain}

- clear glass



7713FY/10

3 light foyer in Oil Rubbed Bronze
7"W x 15"H
3 lights x 60W E12
88" Overall height
{6' wire} {6' chain}



7713FY/20

3 light foyer in Brushed Nickel
7"W x 15"H
3 lights x 60W E12
88" Overall height
{6' wire} {6' chain}





FOYER

7706FY/20

6 light large pendant in
Brushed Nickel
21"W x 39"H
6 lights x 100W MED
112" Overall height
{12' wire} {6' chain}
• white glass

**7726FY/10**

6 light large pendant in Oil
Rubbed Bronze
21"W x 39"H
6 lights x 100W MED
112" Overall height
{12' wire} {6' chain}
• white glass

**7703FY/20**

3 light large pendant in Brushed
Nickel
15"W x 27"H
2 lights x 100W MED
100" Overall height
{12' wire} {6' chain}
• white glass

**7723FY/10**

3 light large pendant in Oil
Rubbed Bronze
15"W x 27"H
2 lights x 100W MED
100" Overall height
{12' wire} {6' chain}
• white glass



CEILING





CEILING

CN160381

PARK CITY
 3 light semi flush dual mount in Oil Rubbed Bronze/wood grain
 16"W x 13"H
 3 lights x 100W Med
 • light beige scavo glass



FML801-PW-15 LED

QUINCY
 1 light semi flush Chrome
 14"W x 8"H
 12W LED, 3000K, 80 CRI
 (960 Lumens, Dimmable)
 • white glass



CN129281

BECKETT
 3 light semi flush dual mount in Oil Rubbed Bronze
 14"W x 7"H
 3 lights x 60W MED shown Bulb 1092*
 • clear glass
 *not included—See page 324



CN120281

BECKETT
 3 light semi flush in Oil Rubbed Bronze
 14"W x 7"H
 3 lights x 60W MED*
 • opal white glass
 *not included—See page 324



CN170382

CASUAL MISSION
 3 light semi flush in Brushed Nickel
 20"W x 12"H
 3 lights x 100W Med
 • white lined glass



CN170381

CASUAL MISSION
 3 light semi flush in Oil Rubbed Bronze
 20"W x 12"H
 3 lights x 100W Med
 • white lined glass



SL866241

HARMONY
 2 light semi-flush in Satin Pewter
 16"W x 13"H
 2 lights x 100W MED
 • white marble glass



SL866262

HARMONY
 2 light semi flush in Aged Bronze
 16"W x 13"H
 2 lights x 100W MED
 • champagne marble glass



CEILING

SL842078**PRESTIGE**

2 light semi flush in Brushed Nickel

15"W x 14"H

2 lights x 100W MED

- alabaster style glass

**SL842022****PRESTIGE**

2 light semi-flush in Sable Bronze

15"W x 14"H

2 lights x 100W MED

- cognac edged glass

**2103SF/20****BRISTOL LANE**

3 light semi-flush in Brushed Nickel

17"W x 12"H

3 lights x 60W MED

- white glass

**2103SF/10****BRISTOL LANE**

3 light semi-flush in Brushed Nickel

17"W x 12"H

3 lights x 60W MED

- white glass

**SL861672****TRITON**

2 light semi-flush in Moonlight Silver

16"W x 12"H

2 lights x 100W MED

- tea stained glass

**SL861622****TRITON**

2 light semi-flush in Sable Bronze

16"W x 12"H

2 lights x 100W MED

- tea stained glass

**CN230387****GEORGETOWN**

3 light semi flush in Brushed Nickel

19"W x 16"H

3 lights x 100W Med*

- mercury glass

*not included—See page 324

**2203CS/10****SANTE FE**

3 light semi flush in Oil Rubbed Bronze

17"W x 16"H

3 lights x 60W MED

77" Overall height

- white glass



2402SF/20

TRIBECA
 2 light semi flush in Brushed Nickel
 12"W x 12"H
 2 lights x 60W MED
 • white glass

**2402SF/10**

TRIBECA
 2 light semi flush in Brushed Nickel
 12"W x 12"H
 2 lights x 60W MED
 • white glass

**SL860978**

PENDENZA
 2 light semi flush in Brushed Nickel
 16"W x 12"H
 2 lights x 60W MED
 • white cotton weave fabric shade
 • etched white diffuser

**SL860915**

PENDENZA
 2 light semi flush in Oil Rubbed Bronze
 16"W x 12"H
 2 lights x 60W MED
 • white cotton weave fabric shade
 • etched white diffuser

**190043217**

PITTMAN
 2 light semi flush in Brushed Nickel
 15"W x 15"H
 2 lights x 100W MED
 • etched glass

**190043719**

PITTMAN
 2 light semi flush in Sienna Bronze
 15"W x 15"H
 2 lights x 100W MED
 • etched glass

**SL861478**

TAHOE
 2 light semi flush in Brushed Nickel
 12"W x 11"H
 2 lights x 100W MED
 • alabaster style glass

**SL861463**

TAHOE
 2 light semi flush in Painted Bronze
 12"W x 11"H
 2 lights x 100W MED
 • alabaster style glass



CEILING

SL860778

BELLA
 3 light semi-flush in Brushed Nickel
 16"W x 12"H
 3 lights x 60W MED
 • etched glass

**SL860715**

BELLA
 3 light semi-flush in Oil Rubbed Bronze
 16"W x 12"H
 3 lights x 60W MED
 • etched glass

**1002CS/20**

BRIGHTON
 2 light convertible in Brushed Nickel
 16"W x 13"H
 2 lights x 60W MED
 • white glass

**1052CS/10**

BRIGHTON
 2 light convertible in Oil Rubbed Bronze
 16"W x 13"H
 2 lights x 60W MED
 • white glass

**SL869678**

RIVA
 3 light semi flush in Brushed Nickel
 16"W x 12"H
 3 lights x 100W MED
 • etched alabaster style glass

**SL869663**

RIVA
 3 light semi flush in Painted Bronze
 16"W x 12"H
 3 lights x 100W MED
 • etched alabaster style glass

**SL825378**

ECLIPSE
 3 light semi flush in Brushed Nickel
 19"W x 15"H
 3 lights x 100W MED
 • alabaster style glass
 • etched white diffuser

**SL825363**

ECLIPSE
 3 light semi flush in Painted Bronze
 19"W x 15"H
 3 lights x 100W MED
 • alabaster style glass
 • etched white diffuser



190067117

TIA
2 light semi flush in Matte Nickel
12"W x 12"H
2 lights x 60W MED
• etched swirl glass



190067763

TIA
2 light semi flush in Matte Nickel
12"W x 12"H
2 lights x 60W MED
• etched swirl glass



1202CS/20

CONWAY
2 light convertible semi flush in
Brushed Nickel
15"W x 14"H
2 lights x 100W MED
• white glass



1252CS/10

CONWAY
2 light convertible semi flush in
Oil Rubbed Bronze
15"W x 14"H
2 lights x 100W MED
• white glass



TC0015741

HAVEN
2 light semi flush in Satin Pewter
16"W x 14"H
2 lights x 60W MED
• etched glass



TC0015704

HAVEN
2 light semi flush in Espresso
16"W x 14"H
2 lights x 60W MED
• etched glass



SL861078

WHITMORE
2 light convertible semi flush in
Brushed Nickel
16"W x 13"H
2 lights x 100W MED
• etched glass



CEILING

TC0020217

TREME

2 light semi flush in Brushed Nickel

13"W x 12"H

2 lights x 60W MED

- etched white glass

**TC0020704**

TREME

2 light semi flush in Espresso

13"W x 12"H

2 lights x 60W MED

- etched white glass

**TG0002117**

WRIGHT

3 light semi flush in Matte Nickel

20"W x 12"H

3 lights x 60W MED

- etched white glass

**190113704**

WRIGHT

3 light semi flush in Espresso

20"W x 12"H

3 lights x 60W MED

- champagne glass

**1102CS/20**

CHATHAM

2 light semi flush in Brushed Nickel

17"W x 14"H

2 lights x 60W MED

- etched white glass

**1152CS/10**

CHATHAM

2 light semi flush in Oil Rubbed Bronze

17"W x 14"H

2 lights x 60W MED

- etched white glass

**CN600362**

MORGAN

2 light semi flush in Brushed Nickel

15"W x 11"H

2 lights x 60W MED

- white glass diffuser
- white fabric shade

**CN600361**

MORGAN

2 light semi flush in Oil Rubbed Bronze

15"W x 11"H

2 lights x 60W MED

- white glass diffuser
- white fabric shade





CN160231

PARK CITY
2 light flush mount in Oil Rubbed Bronze/wood grain
13"W x 6"H
2 lights x 60W Med
• light beige scavo glass



CN230237

GEORGETOWN
2 light flush mount in Weathered Zinc
16"W x 9"H
2 lights x 60W Med*
• mercury glass
*not included—See page 324



CN129231

BECKETT
2 light flush mount in Oil Rubbed Bronze
14"W x 7"H
2 lights x 100W MED shown Bulb 1092*
• clear glass
*not included—See page 324



CN120231

BECKETT
2 light flush mount in Oil Rubbed Bronze
14"W x 7"H
2 lights x 100W MED*
• opal white glass
*not included—See page 324



CN170332

CASUAL MISSION
3 light flush mount in Brushed Nickel
13"W x 7"H
3 lights x 60W Med
• white lined glass



CN170331

CASUAL MISSION
3 light flush mount in Oil Rubbed Bronze
13"W x 7"H
3 lights x 60W Med
• white lined glass



1303FM/20

JACKSON
3 light flush mount in Brushed Nickel
15"W x 9"H
3 lights x 60W MED
• white glass



1353FM/10

JACKSON
3 light flush mount in Oil Rubbed Bronze
15"W x 9"H
3 lights x 60W MED
• white glass



190071217

PITTMAN
2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W MED
• etched glass

CEILING



190071719

PITTMAN
2 light flush mount in Sienna Bronze
14"W x 6"H
2 lights x 60W MED
• etched glass



2103FM/20

BRISTOL LANE
3 light flush mount in Brushed Nickel
17"W x 6"H
3 lights x 60W MED
• white glass



2103FM/10

BRISTOL LANE
3 light flush mount in Brushed Nickel
17"W x 6"H
3 lights x 60W MED
• white glass



SL861572

TRITON
2 light flush mount in Moonlight Silver
13"W x 7"H
2 lights x 60W MED
• tea stained glass



SL861522

TRITON
2 light flush mount in Sable Bronze
13"W x 7"H
2 lights x 60W MED
• tea stained glass



1103FM/20

CHATHAM
3 light flush mount in Brushed Nickel
13"W x 6"H
3 lights x 60W MED
• white glass



1053FM/10

GHATHAM
3 light flush mount in Oil Rubbed Bronze
13"W x 6"H
3 lights x 60W MED
• white glass



SL869218

PRESTIGE
2 light flush mount in Textured White
14"W x 6"H
2 lights x 60W MED
• etched alabaster style glass



SL877263

PRESTIGE
2 light flush mount in Painted Bronze
14"W x 6"H
2 lights x 60W MED
• golden cream swirl glass



2003FM/10

ARLINGTON

3 light flush mount in Oil Rubbed Bronze

14"W x 6"H

3 lights x 60W MED

- white glass



LIBERTY PARK

flush mount in Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
7672FM/20	10"	10"	2	60W
7683FM/20	12"	12"	3	60W
7693FM/20	17"	17"	3	60W

- prismatic clear glass
- matching pendants available on page 143



LIBERTY PARK

flush mount in Oil Rubbed Bronze

Model	Width	Body Height	No. Lights	Max. Watt.
7672FM/10	10"	10"	2	60W
7683FM/10	12"	12"	3	60W
7693FM/10	17"	17"	3	60W

- prismatic clear glass
- matching pendants available on page 143



SL876278

2 light flush mount in Brushed Nickel

14"W x 6"H

2 lights x 60W MED

- clear ribbed glass



SL84408

2 light flush mount in Matte White

10"W x 6"H

2 light x 60W MED

- clear ribbed glass



flush mount in Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
SL868178	12"	6"	1	100W
SL868278	14"	6"	2	60W

- etched melon glass



SL868218

2 light flush mount in Textured White

14"W x 6"H

2 lights x 60W MED

- etched melon glass



SL868263

2 light flush mount in Painted Bronze

14"W x 6"H

2 lights x 60W MED

- etched melon glass



SL878223

2 light flush mount in Colonial Bronze

14"W x 6"H

2 lights x 60W MED

- etched glass



SL869222

2 light flush mount in Sable Bronze
 14"W x 6"H
 2 lights x 60W MED
 • etched melon glass



M271878

2 light flush mount in Brushed Nickel
 15"W x 9"H
 2 lights x 60W MED
 • bone linen shimmer
 • etched white diffuser



SL928378



2 light flush mount in Brushed Nickel
 12"W x 6"H
 2 lights x 60W MED
 • etched alabaster style glass



190033217

2 light flush mount in Brushed Nickel
 15"W x 5"H
 2 lights x 60W MED
 • etched glass



190033715

2 light flush mount in Oil Rubbed Bronze
 15"W x 5"H
 2 lights x 60W MED
 • etched glass



flush mount in Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
SL878178	12"	6"	1	100W
SL878278	14"	6"	2	60W
SL878378	16"	7"	3	60W

• etched glass



flush mount in Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
SL869178	12"	6"	1	100W
SL869278	14"	6"	2	60W
SL869378	16"	7"	3	60W

• etched alabaster style glass



flush mount in Oil Rubbed Bronze

Model	Width	Body Height	No. Lights	Max. Watt.
SL878115	12"	6"	1	100W
SL878215	14"	6"	2	60W

• etched glass



flush mount in Painted Bronze

Model	Width	Body Height	No. Lights	Max. Watt.
SL869163	12"	6"	1	100W
SL869263	14"	6"	2	60W
SL869363	16"	6"	3	60W

• etched alabaster style glass

CEILING



CEILING



flush mount in Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
7002FM/20	11"	3"	2	60W
7003FM/20	13"	4"	2	60W
7013FM/20	15"	6"	3	60W

- etched glass



flush mount in White

Model	Width	Body Height	No. Lights	Max. Watt.
7002FM/40	11"	3"	2	60W
7003FM/40	13"	4"	2	60W
7013FM/40	15"	6"	3	60W

- etched glass



flush mount in Oil Rubbed Bronze

Model	Width	Body Height	No. Lights	Max. Watt.
7052FM/10	11"	3"	2	60W
7053FM/10	13"	4"	2	60W
7023FM/10	15"	6"	3	60W

- etched glass



flush mount in Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
7301FM/20	12"	5"	1	60W
7302FM/20	15"	5"	2	60W
7303FM/20	16"	6"	3	60W

- acid etched alabaster white glass



flush mount in Oil Rubbed Bronze

Model	Width	Body Height	No. Lights	Max. Watt.
7301FM/10	12"	5"	1	60W
7302FM/10	15"	5"	2	60W
7303FM/10	16"	6"	3	60W

- acid etched alabaster white glass



energy efficient flush mount in Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
190034217	12"	4"	1	13W GU24 CFL
190035217	15"	5"	2	13W GU24 CFL

- etched glass
- rate for 90° supply wire
- lamp included



flush mount in Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
SL845578	8"	5"	1	60W
SL845678	10"	6"	2	60W
SL869363	16"	6"	3	60W

- alabaster style glass



flush mount in White

Model	Width	Body Height	No. Lights	Max. Watt.
7351FM/40	7"	5"	1	60W
7352FM/40	10"	5"	2	60W

- white glass



flush mount in White

Model	Width	Body Height	No. Lights	Max. Watt.
SL3258	8"	5"	1	60W
SL3268	10"	6"	2	60W
SL3288	12"	6"	3	60W

- etched glass
- rate for 90° supply wire

**7021FM/40**

1 light flush mount in White
 8"W x 5"H
 1 light x 60W MED
 • white glass

**7021FM/20**

1 light flush mount in Brushed Nickel
 8"W x 5"H
 1 light x 60W MED
 • white glass

**7021FM/10**

1 light flush mount in Oil Rubbed Bronze
 8"W x 5"H
 1 light x 60W MED
 • white glass

**SL843678**

1 light flush mount in Brushed Nickel
 6"W x 8"H
 1 light x 60W MED
 • white glass globe

**SL84368**

1 light flush mount in Matte White
 6"W x 8"H
 1 light x 60W MED
 • white glass globe

**SL123**

2 light flush mount in White
 12"W x 6"H
 2 lights x 60W MED
 • white glass

**CN734299**

SUNGLOW
 2 light flush mount in Oil Rubbed Bronze
 13"W x 4"H
 2 light x 60W MED
 • white glass
 • Brushed Nickel clips included

**CN734399**

SUNGLOW
 3 light flush mount in Oil Rubbed Bronze
 17"W x 5"H
 3 light x 60W MED
 • white glass
 • Brushed Nickel clips included



KALONA flush mount in White

LED

Model	Width	Body Height	No. Lights	Max. Watt.
CL783004	11"	5"	1	13W LED, 762 LUMENS, CRI 90
CL783014	13"	4"	1	24W LED, 1050 LUMENS, CRI 90
CL783024	15"	5"	1	28.5W LED, 1265 Lumens, CRI 90

• white acrylic diffuser

CEILING



flush mount in Satin Nickel

LED

Model	Width	Body Height	Max. Watt.
FML2000-10-16M	5"	2"	7.5W LED, 3000K, 80 CRI, 600 Lumens
FML2020-10-16M	8"	3"	2 x 5W LED, 3000K, 80 CRI, 800 Lumens
FML2030-10-16M	9"	3"	2 x 7.5W LED, 3000K, 80 CRI, 1200 Lumens

- opal white glass
- dimmable



flush mount in Satin Nickel

LED

Model	Width	Body Height	Max. Watt.
FML4025-10-16M	6"	2"	7.5W LED, 3000K, 80 CRI, 600 Lumens
FML4050-10-16M	9"	3"	11W LED, 3000K, 80 CRI, 900 Lumens
FML4075-10-16M	11"	3"	20W LED, 3000K, 80 CRI, 1600 Lumens

- opal white glass
- dimmable



flush mount in Satin Nickel

LED

Model	Width	Body Height	Max. Watt.
FML7125-10-16M	8"	4"	7.5W LED, 3000K, 80 CRI, 600 Lumens
FML7150-10-16M	11"	4"	16W LED, 3000K, 80 CRI, 900 Lumens
FML7175-10-16M	13"	5"	20W LED, 3000K, 80 CRI, 1600 Lumens

- opal white glass
- dimmable



flush mount in Satin Nickel

LED

Model	Width	Body Height	Max. Watt.
FML4225-10-16M	12"	3"	11W LED, 3000K, 80 CRI, 900 Lumens
FML4250-10-16M	15"	4"	20W LED, 3000K, 80 CRI, 1600 Lumens

- opal white glass
- dimmable



flush mount in Chrome

LED

Model	Width	Body Height	Max. Watt.
FML4925-10-15	12"	4"	16W LED, 3000K, 80 CRI, 1300 Lumens
FML4950-10-15	15"	4"	20W LED, 3000K, 80 CRI, 1600 Lumens

- opal white glass
- dimmable



flush mount in Chrome

LED

Model	Width	Body Height	Max. Watt.
FML4725-10-15	13"	3"	11W LED, 3000K, 80 CRI, 900 LUMENS
FML4750-10-15	16"	4"	20W LED, 3000K, 80 CRI, 1600 Lumens

- opal white glass
- dimmable



SL705378

2 light flush mount in Brushed Nickel
33"W x 5"H x 17"EXT
2 lights x 32W FC12T9 (32W)

- white acrylic lens
- 120V electronic ballast



TITAN flush mount in White

LED

Model	Width	Body Height	No. Lights	Max. Watt.
CL781034	6"	1"	1	11W LED, 600 Lumens, CRI 90
CL781134	8"	1"	1	14W LED, 1000 Lumens, CRI 90
CL781234	10"	1"	1	17W LED, 1800 Lumens, CRI 90

- white acrylic diffuser



TITAN flush mount in Oil Rubbed Bronze

LED

Model	Width	Body Height	No. Lights	Max. Watt.
CL781031	6"	1"	1	11W LED, 600 Lumens, CRI 90
CL781131	8"	1"	1	14W LED, 1000 Lumens, CRI 90
CL781231	10"	1"	1	17W LED, 1800 Lumens, CRI 90

- white acrylic diffuser

CEILING



LED

CLARION flush mount in Brushed Nickel

Model	Width	Body Height	No. Lights	Max. Watt.
CL782012	11"	4"	1	13W LED, 563 Lumens, CRI 90
CL782022	16"	4"	1	24W LED, 860 Lumens, CRI 90
CL782032	18"	4"	1	28.5W LED, 983 Lumens, CRI 90

- white acrylic diffuser



LED

CLARION flush mount in Oil Rubbed Bronze

Model	Width	Body Height	No. Lights	Max. Watt.
CL782011	11"	4"	1	13W LED, 563 Lumens, CRI 90
CL782021	16"	4"	1	24W LED, 860 Lumens, CRI 90
CL782031	18"	4"	1	28.5W LED, 983 Lumens, CRI 90

- white acrylic diffuser



LED

flush mount in Chrome

Model	Width	Body Height	Max. Watt.
FML4525-10-15	12"	3"	11W LED, 3000K, 80 CRI, 900 Lumens
FML4550-10-15	15"	3"	20W LED, 3000K, 80 CRI, 1600 Lumens

- opal white glass
- dimmable



LED

PLANDOME surface mount in White

Model	Dimensions	Max. Watt.
MLE1200-5-30	5"W x 1"H	9W LED, 3000K, 90CRI, 550 Lumens, Dimmable
MLE1500-5-30	6"W x 1"H	14W LED, 3000K, 90CRI, 850 Lumens, Dimmable
MLE1201-5-30	7"W x 1"H	15W LED, 3000K, 90CRI, 850 Lumens, Dimmable



LED

flush mount in Matte White

Model	Width	Body Height	Max. Watt.
FML5125-AC-30	5"	2"	8W LED, 3000K, 80 CRI, 640 Lumens
FML5150-AC-30	7"	2"	12W LED, 3000K, 80 CRI, 960 Lumens
FML5175-AC-30	9"	2"	16W LED, 3000K, 80 CRI, 1280 Lumens

- dimmable



LED

flush mount in Matte White

Model	Width	Body Height	Max. Watt.
FML6125-AC-30	5"	2"	8W LED, 3000K, 80 CRI, 640 Lumens
FML6150-AC-30	7"	2"	12W LED, 3000K, 80 CRI, 960 Lumens
FML6175-AC-30	9"	2"	16W LED, 3000K, 80 CRI, 1280 Lumens

- dimmable

CEILING



CEILING

FWN432EB

- energy efficient flush mount
48"L x 14"W x 3"H
4 lights x F32T8 (32W)
- clear acrylic prismatic lens
 - 120V electronic ballast



FWN232EB

- energy efficient flush mount
48"L x 8"W x 3"H
2 lights x F32T8 (32W)
- clear acrylic prismatic lens
 - 120V electronic ballast



FWN217EB

- energy efficient flush mount
24"L x 8"W x 3"H
2 lights x F17T8 (17W)
- clear acrylic prismatic lens
 - 120V electronic ballast



FCN432EB

- energy efficient flush mount in White
50"L x 17"W x 5"H
4 lights x F32T8 (32W)
- soft white acrylic diffuser
 - 120V electronic ballast



FCN232EB

energy efficient flush mount in White

50"L x 12"W x 5"H
2 lights x F32T8 (32W)

- soft white acrylic diffuser
- 120V electronic ballast



SL1217EB

energy efficient flush mount in White

27"W x 6"H x 5"EXT
2 lights x 17W F17T8 (17W)

- may be mounted on wall or ceiling
- 120V electronic ballast



FCN231BEB

energy efficient flush mount in White

28"L x 26"W x 6"H
2 lights x FB32U6T8 (32W)

- soft white acrylic diffuser
- 120V electronic ballast



WALL SCONCES





WALL SCONCES

CN160171 ↑↓

PARK CITY
1 light wall sconce in Oil Rubbed Bronze & Wood Grain
5"W x 7"H x 7"EXT
1 light x 60W MED
• light beige scavo glass



CN230177 ↑↓

GEORGETOWN
1 light wall sconce in Weathered Zinc
6"W x 12"H x 8"EXT
1 light x 100W MED
• mercury glass



CN129121 ↑↓

BECKETT
1 light wall sconce in Oil Rubbed Bronze
6"W x 12"H x 7"EXT
1 light x 60W MED
• clear glass



CN120121 ↑↓

BECKETT
1 light wall sconce in Oil Rubbed Bronze
6"W x 12"H x 7"EXT
1 light x 60W MED
• opal white glass



CN170172 ↑↓

CASUAL MISSION
1 light wall sconce in Brushed Nickel
5"W x 8"H x 6"EXT
1 light x 100W MED
• white lined glass



CN170171 ↑↓

CASUAL MISSION
1 light wall sconce in Oil Rubbed Bronze
5"W x 8"H x 6"EXT
1 light x 100W MED
• white lined glass



2101WS/20

BRISTOL LANE
1 light wall sconce in Brushed Nickel
7"W x 10"H x 10"EXT
1 light x 100W MED
• white glass



2101WS/10

BRISTOL LANE
1 light wall sconce in Oil Rubbed Bronze
7"W x 10"H x 10"EXT
1 light x 100W MED
• white glass



WALL SCONCES

CN579172 ↑↓

SUMMIT PLACE
1 light wall sconce in Brushed Nickel
5"W x 9"H x 6" EXT
1 lights x 100W MED
• opal white glass



CN579171 ↑↓

SUMMIT PLACE
1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 6" EXT
1 lights x 100W MED
• opal white glass



CN575172 ↑↓

BELMAR
1 light wall sconce in Brushed Nickel
5"W x 9"H x 6" EXT
1 light x 100W MED
• opal white glass



CN575171 ↑↓

BELMAR
1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 6" EXT
1 light x 100W MED
• opal white glass



TN0003217 ↑↓

BELLA
1 light wall sconce in Brushed Nickel
5"W x 9"H x 8" EXT
1 lights x 100W MED
• etched glass



TN0003715 ↑↓

BELLA
1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 8" EXT
1 lights x 100W MED
• etched glass



1001WS/20 ↑↓

BRIGHTON
1 light wall sconce in Brushed Nickel
6"W x 11"H x 8" EXT
1 light x 75W MED
• white glass



1051WS/10 ↑↓

BRIGHTON
1 light wall sconce in Oil Rubbed Bronze
6"W x 11"H x 8" EXT
1 light x 75W MED
• white glass



WALL SCONCES



FARMINGTON

1501WS/20

WILLIAMSPORT
1 light wall sconce in Brushed Nickel
5"W x 11"H x 7"EXT
1 light x 60W CAND



1501WS/10

WILLIAMSPORT
1 light wall sconce in Oil Rubbed Bronze
5"W x 11"H x 7"EXT
1 light x 60W CAND



1502WS/20

WILLIAMSPORT
2 light wall sconce in Brushed Nickel
12"W x 11"H x 8"EXT
2 lights x 60W CAND



1502WS/10

WILLIAMSPORT
2 light wall sconce in Oil Rubbed Bronze
12"W x 11"H x 8"EXT
2 lights x 60W CAND



2201WS/10



SANTE FE
1 light wall sconce in Oil Rubbed Bronze
6"W x 10"H x 9"EXT
1 light x 100W MED
• white glass



CN110171



FARMINGTON
1 light wall sconce in Oil Rubbed Bronze
5"W x 14"H x 4"EXT
1 light x 60W CAND



SL854178



PRESTIGE
1 light wall sconce in Brushed Nickel
8"W x 9"H x 10"EXT
1 light x 100W MED
• alabaster style glass



SL854122



PRESTIGE
1 light wall sconce in Sable Bronze
8"W x 9"H x 10"EXT
1 light x 100W MED
• cognac edged glass



WALL SCONCES



symbol denotes up or down mounting

2451WS/20

TRIBECA
 1 light wall sconce in Brushed Nickel
 9"W x 12"H x 10" EXT
 1 light x 60W MED
 • white glass

**2451WS/10**

TRIBECA
 1 light wall sconce in Oil Rubbed Bronze
 9"W x 12"H x 10" EXT
 1 light x 60W MED
 • white glass

**TN0005217** 

PENDENZA
 1 light wall sconce in Brushed Nickel
 5"W x 12"H x 8"EXT
 1 lights x 100W MED
 • etched glass

**TN0005715** 

PENDENZA
 1 light wall sconce in Oil Rubbed Bronze
 5"W x 12"H x 8"EXT
 1 lights x 100W MED
 • etched glass

**190023217** 

PITTMAN
 1 light wall sconce in Brushed Nickel
 5"W x 9"H x 6"EXT
 1 lights x 100W MED
 • etched glass

**190023719** 

PITTMAN
 1 light wall sconce in Sienna Bronze
 5"W x 9"H x 6"EXT
 1 lights x 100W MED
 • etched glass

**CN578172** 

RAVENDALE
 1 light wall sconce in Brushed Nickel
 5"W x 9"H x 7"EXT
 1 lights x 100W MED
 • opal white glass

**CN578171** 

RAVENDALE
 1 light wall sconce in Oil Rubbed Bronze
 5"W x 9"H x 7"EXT
 1 lights x 100W MED
 • opal white glass



WALL SCONCES



RAVENDALE

1201WS/20

CONWAY

- 1 light wall sconce in Brushed Nickel
 6"W x 9"H x 8"EXT
 1 light x 100W MED
 • white glass

**1251WS/20**

CONWAY

- 1 light wall sconce in Oil Rubbed Bronze
 6"W x 9"H x 8"EXT
 1 light x 100W MED
 • white glass

**TN0009741**

HAVEN

- 1 light wall sconce in Satin Pewter
 5"W x 14"H x 6"EXT
 1 light x 100W MED
 • etched glass

**TN0009704**

HAVEN

- 1 light wall sconce in Espresso
 5"W x 14"H x 6"EXT
 1 light x 100W MED
 • etched glass

**TN0010217**

TREME

- 1 light wall sconce in Brushed Nickel
 5"W x 12"H x 8"EXT
 1 light x 100W MED
 • etched white glass

**TN0010704**

TREME

- 1 light wall sconce in Espresso
 5"W x 12"H x 8"EXT
 1 light x 100W MED
 • etched white glass

**TN0007117**

WRIGHT

- 1 light wall sconce in Matte Nickel
 5"W x 10"H x 7"EXT
 1 light x 100W MED
 • etched white glass

**TN0007704**

WRIGHT

- 1 light wall sconce in Espresso
 5"W x 10"H x 7"EXT
 1 light x 100W MED
 • champagne glass



WALL SCONCES



1301WS/20 

JACKSON

1 light wall sconce in Brushed Nickel

5"W x 8"H x 7"EXT

1 light x 60W MED

- white glass



1351WS/10 

JACKSON

1 light wall sconce in Oil Rubbed Bronze

5"W x 8"H x 7"EXT

1 light x 60W MED

- white glass



1101WS/20 

CHATHAM

1 light wall sconce in Brushed Nickel

5"W x 19"H x 7"EXT

1 light x 75W MED

- white glass



1151WS/20 

CHATHAM

1 light wall sconce in Oil Rubbed Bronze

5"W x 19"H x 7"EXT

1 light x 75W MED

- white glass



CN570172 

CALIFON

1 light wall sconce in Brushed Nickel

5"W x 9"H x 8"EXT

1 lights x 100W MED

- white glass



CN570171 

CALIFON

1 light wall sconce in Oil Rubbed Bronze

5"W x 9"H x 8"EXT

1 lights x 100W MED

- white glass



CN573171 

SINCLAIR

1 light wall sconce in Brushed Nickel

5"W x 10"H x 5"EXT

1 light x 60W MED

- frosted white glass



CN573172 

SINCLAIR

1 light wall sconce in Polished Chrome

5"W x 10"H x 5"EXT

1 light x 60W MED

- frosted white glass



WALL SCONCES

WSL820-10-16M**LED****ADA**

- MAXFIELD
 2 light double wall sconce in Satin Nickel
 4"W x 20"H x 4"EXT
 2 lights x 2.5W LED, 3000K, 80 CRI
- opal white glass
 - 1200 Lumens, dimmable

**WSL825-10-15M****LED****ADA**

- MAXFIELD
 1 light double wall sconce in Chrome
 4"W x 10"H x 4"EXT
 1 lights x 2.5W LED, 3000K, 80 CRI
- opal white glass
 - 600 Lumens, dimmable

**WSL1601-PW-15****LED****ADA**

- MIDTOWN
 1 light wall sconce in Polished Chrome
 5"W x 11"H x 4"EXT
 1 light x 4W LED, 3000K, 80 CRI
- white glass
 - 480 Lumens, dimmable

**WSL140-5-15****LED****ADA**

- PORTAL
 1 light wall sconce in Polished Chrome
 6"W x 9"H x 3"EXT
 1 light x 3W LED, 3000K, 80 CRI
- frosted white glass
 - 240 Lumens, dimmable

**5181WS/20****ADA**

- 1 light wall sconce in Brushed Nickel
 7"W x 10"H x 4"EXT
 1 light x 60W MED
- white glass

**5381WS/10****ADA**

- 1 light wall sconce in Oil Rubbed Bronze
 6"W x 10"H x 4"EXT
 1 light x 60W MED
- white glass

**5102WS/20****ADA**

- 2 light wall sconce in Brushed Nickel
 8"W x 14"H x 4"EXT
 2 lights x 60W CAND
- white glass diffuser

**5302WS/10****ADA**

- 2 light wall sconce in Oil Rubbed Bronze
 8"W x 14"H x 4"EXT
 2 lights x 60W CAND
- white glass diffuser



WALL SCONCES

5111WS/20 **ADA**

1 light wall sconce in Brushed Nickel
 8"W x 12"H x 4"EXT
 1 light x 60W CAND
 • white glass diffuser



5131WS/20

1 light wall sconce in Brushed Nickel
 11"W x 6"H x 6"EXT
 1 light x 60W MED
 • white glass diffuser



SL746078 **ADA**

1 light wall sconce in Brushed Nickel
 9"W x 11"H x 4"EXT
 1 light x 26W MED
 • white acrylic diffuser
 • 120V electronic blast



5161WS/20 **ADA**

1 light wall sconce in Brushed Nickel
 7"W x 12"H x 4" EXT
 1 light x 60W CAND
 • white glass diffuser



WS1330-10-15

1 light wall sconce in Chrome
 6"W x 12"H x 5" EXT
 1 light x 100W MED
 • opal white glass



5121WS/20 **ADA**

1 light wall sconce in Brushed Nickel
 9"W x 8"H x 4"EXT
 1 light x 60W MED
 {includes turn sets}
 • white glass diffuser



TITAN wall sconce in White

ADA **LED**

Model	Width	Body Height	No. Lights	Max. Watt.
CL781034	6"	1"	1	11W LED, 600 Lumens, CRI 90
CL781134	8"	1"	1	14W LED, 1000 Lumens, CRI 90
CL781234	10"	1"	1	17W LED, 1800 Lumens, CRI 90

• white acrylic diffuser



TITAN wall sconce in Oil Rubbed Bronze

ADA **LED**

Model	Width	Body Height	No. Lights	Max. Watt.
CL781031	6"	1"	1	11W LED, 600 Lumens, CRI 90
CL781131	8"	1"	1	14W LED, 1000 Lumens, CRI 90
CL781231	10"	1"	1	17W LED, 1800 Lumens, CRI 90

• white acrylic diffuser



WALL SCONCES



WALL SCONCES

5171WS/20

1 light wall sconce in Brushed Nickel

12"W x 5"H x 6"EXT
1 light x 100W MED

- white glass

**5371WS/10**

1 light wall sconce in Oil Rubbed Bronze

12"W x 5"H x 6"EXT
1 light x 100W MED

- white glass

**5151WS/20**

1 light wall sconce in Brushed Nickel

11"W x 5"H x 5" EXT
1 light x 60W CAND

- white glass

**5151WS/10**

1 light wall sconce in Oil Rubbed Bronze

11"W x 5"H x 5"EXT
1 light x 60W CAND

- white glass

**SL853178 ADA**

1 light wall sconce in Brushed Nickel

14"W x 9"H x 4"EXT
1 light x 100W MED

- alabaster style glass

**SL853163 ADA**

1 light wall sconce in Painted Bronze

14"W x 9"H x 4"EXT
1 light x 100W MED

- alabaster style glass

**SL853122 ADA**

1 light wall sconce in Sable Bronze


14"W x 9"H x 4"EXT
1 light x 100W MED

- cognac edged glass



WALL SCONCES

BATH





BATH

PARK CITY

CN160171

1 light wall sconce in Oil Rubbed Bronze & Wood Grain

5"W x 7"H x 7"EXT

1 light x 60W MED

- light beige scavo glass



CN160211

2 light bath bar in Oil Rubbed Bronze & Wood Grain

14"W x 7"H x 7"EXT

2 lights x 60W MED

- light beige scavo glass



CN160311

3 light bath bar in Oil Rubbed Bronze & Wood Grain

22"W x 7"H x 7"EXT

3 lights x 60W MED

- light beige scavo glass



CN160411

4 light bath bar in Oil Rubbed Bronze & Wood Grain

30"W x 7"H x 7"EXT

4 lights x 60W MED

- light beige scavo glass



BATH

SANTE FE

2201WS/10

1 light wall sconce in Oil Rubbed Bronze
6"W x 10"H x 9"EXT
1 light x 100W MED
• white glass



2201BB/10

2 light bath bar in Oil Rubbed Bronze
16"W x 9"H x 8"EXT
2 lights x 100W MED
• white glass



2203BB/10

3 light bath bar in Oil Rubbed Bronze
26"W x 9"H x 8"EXT
3 lights x 100W MED
• white glass



2204BB/10

4 light bath bar in Oil Rubbed Bronze
35"W x 9"H x 8"EXT
4 lights x 100W MED
• white glass



BATH

CN129121

1 light wall sconce in Oil Rubbed Bronze
6"W x 12"H x 7"EXT
1 light x 60W MED **shown Bulb 1092***
• clear glass
**not included—See page 324*



CN129211

2 light bath bar in Oil Rubbed Bronze
15"W x 11"H x 7"EXT
2 lights x 60W MED **shown Bulb 1092***
• clear glass
**not included—See page 324*



CN129311

3 light bath bar in Oil Rubbed Bronze
24"W x 11"H x 7"EXT
3 lights x 60W MED **shown Bulb 1092***
• clear glass
**not included—See page 324*



CN129411

4 light bath bar in Oil Rubbed Bronze
33"W x 11"H x 7"EXT
3 lights x 60W MED **shown Bulb 1092***
• clear glass
**not included—See page 324*



CN120121

1 light wall sconce in Oil Rubbed Bronze
6"W x 12"H x 7"EXT
1 light x 60W MED*
• opal white glass
**not included—See page 324*



CN120211

2 light bath bar in Oil Rubbed Bronze
15"W x 11"H x 7"EXT
2 lights x 60W MED*
• opal white glass
**not included—See page 324*



CN120311

3 light bath bar in Oil Rubbed Bronze
24"W x 11"H x 7"EXT
3 lights x 60W MED*
• opal white glass
**not included—See page 324*



CN120411

4 light bath bar in Oil Rubbed Bronze
33"W x 11"H x 7"EXT
3 lights x 60W MED*
• opal white glass
**not included—See page 324*



CASUAL MISSION

CN170172



1 light wall sconce in Brushed Nickel
5"W x 8"H x 6"EXT
1 light x 100W MED
• white lined glass



CN170212



2 light bath bar in Brushed Nickel
12"W x 9"H x 6"EXT
2 lights x 100W MED
• white lined glass



CN170312



3 light bath bar in Brushed Nickel
20"W x 9"H x 6"EXT
3 lights x 100W MED
• white lined glass



CN170412



4 light bath bar in Brushed Nickel
28"W x 9"H x 6"EXT
4 lights x 100W MED
• white lined glass



BATH

CASUAL MISSION

CN170171



1 light wall sconce in Oil Rubbed Bronze
5"W x 8"H x 6"EXT
1 light x 100W MED
• white lined glass



CN170211



2 light bath bar in Oil Rubbed Bronze
12"W x 9"H x 6"EXT
2 lights x 100W MED
• white lined glass



CN170311



3 light bath bar in Oil Rubbed Bronze
20"W x 9"H x 6"EXT
3 lights x 100W MED
• white lined glass



CN170411



4 light bath bar in Oil Rubbed Bronze
28"W x 9"H x 6"EXT
4 lights x 100W MED
• white lined glass



BATH

GEORGETOWN

CN230177

1 light wall sconce in Weathered Zinc
6"W x 12"H x 8"EXT
1 light x 100W MED*
• mercury glass
**not included—See page 324*



CN230217

2 light bath bar in Weathered Zinc
16"W x 11"H x 7"EXT
2 lights x 100W MED*
• mercury glass
**not included—See page 324*



CN230317

3 light bath bar in Weathered Zinc
24"W x 12"H x 7"EXT
3 lights x 100W MED*
• mercury glass
**not included—See page 324*



CN230417

4 light bath bar in Weathered Zinc
33"W x 13"H x 7"EXT
4 lights x 100W MED*
• mercury glass
**not included—See page 324*



BATH



BATH

PRESTIGE

SL854178

PRESTIGE
1 light wall sconce in Brushed Nickel
8"W x 9"H x 10"EXT
1 light x 100W MED
• alabaster style glass



SL748278

2 light bath bar in Brushed Nickel
17"W x 9"H x 9"EXT
2 lights x 100W MED
• alabaster style glass



SL748378

3 light bath bar in Brushed Nickel
27"W x 9"H x 9"EXT
3 lights x 100W MED
• alabaster style glass



SL748478

4 light bath bar in Brushed Nickel
36"W x 9"H x 9"EXT
4 lights x 100W MED
• alabaster style glass



SL748578

5 light bath bar in Brushed Nickel
46"W x 9"H x 9"EXT
5 lights x 100W MED
• alabaster style glass



SL748678

6 light bath bar in Brushed Nickel
55"W x 10"H x 9"EXT
6 lights x 100W MED
• alabaster style glass



BATH

PRESTIGE

SL854122

PRESTIGE

1 light wall sconce in Sable Bronze

8"W x 9"H x 10"EXT

1 light x 100W MED

- cognac edged glass



SL748222

2 light bath bar in Sable Bronze

17"W x 9"H x 9"EXT

2 lights x 100W MED

- cognac edged glass



SL748322

3 light bath bar in Sable Bronze

27"W x 9"H x 9"EXT

3 lights x 100W MED

- cognac edged glass



SL748422

4 light bath bar in Sable Bronze

36"W x 9"H x 9"EXT

4 lights x 100W MED

- cognac edged glass



SL748522

5 light bath bar in Sable Bronze

46"W x 9"H x 9"EXT

5 lights x 100W MED

- cognac edged glass



SL748622

6 light bath bar in Sable Bronze

55"W x 10"H x 9"EXT

6 lights x 100W MED

- cognac edged glass



BATH

TRITON

SL717272

2 light bath bar in Moonlight Silver
12"W x 9"H x 9"EXT
2 lights x 100W MED
• tea stained glass



SL717372

3 light bath bar in Moonlight Silver
21"W x 9"H x 9"EXT
3 lights x 100W MED
• tea stained glass



SL717472

4 light bath bar in Moonlight Silver
29"W x 9"H x 9"EXT
4 lights x 100W MED
• tea stained glass



SL717572

5 light bath bar in Moonlight Silver
36"W x 9"H x 9"EXT
5 lights x 100W MED
• tea stained glass



BATH

TRITON

SL717222

2 light bath bar in Sable Bronze
12"W x 9"H x 9"EXT
2 lights x 100W MED
• tea stained glass



SL717322

3 light bath bar in Sable Bronze
21"W x 9"H x 9"EXT
3 lights x 100W MED
• tea stained glass



SL717422

4 light bath bar in Sable Bronze
29"W x 9"H x 9"EXT
4 lights x 100W MED
• tea stained glass



SL717522

5 light bath bar in Sable Bronze
36"W x 9"H x 9"EXT
5 lights x 100W MED
• tea stained glass



HARMONY

SL760241

2 light bath bar in Satin Pewter
16"W x 8"H x 7"EXT
2 lights x 100W MED
• white marble glass



SL760341

3 light bath bar in Satin Pewter
24"W x 8"H x 7"EXT
3 lights x 100W MED
• white marble glass



SL760441

4 light bath bar in Satin Pewter
32"W x 8"H x 7"EXT
4 lights x 100W MED
• white marble glass



SL760262

2 light bath bar in Aged Bronze
16"W x 8"H x 7"EXT
2 lights x 100W MED
• champagne marble glass



SL760362

3 light bath bar in Aged Bronze
24"W x 8"H x 7"EXT
3 lights x 100W MED
• champagne marble glass



SL760462

4 light bath bar in Aged Bronze
32"W x 8"H x 7"EXT
4 lights x 100W MED
• champagne marble glass



BATH

190016117 

2 light bath bar in Matte Nickel
 16"W x 9"H x 8"EXT
 2 lights x 100W MED
 • etched swirl glass

**190017117** 

3 light bath bar in Matte Nickel
 23"W x 9"H x 8"EXT
 3 lights x 100W MED
 • etched swirl glass

**190018117** 

4 light bath bar in Matte Nickel
 31"W x 9"H x 8"EXT
 4 lights x 100W MED
 • etched swirl glass

**190016763** 

2 light bath bar in Painted Bronze
 16"W x 9"H x 8"EXT
 2 lights x 100W MED
 • etched swirl glass

**190017763** 

3 light bath bar in Painted Bronze
 23"W x 9"H x 8"EXT
 3 lights x 100W MED
 • etched swirl glass

**190018763** 

4 light bath bar in Painted Bronze
 31"W x 9"H x 8"EXT
 4 lights x 100W MED
 • etched swirl glass



RAVENDALE

CN578172

1 light wall sconce in Brushed Nickel
5"W x 9"H x 7"EXT
1 lights x 100W MED
• opal white glass



CN578212

2 light bath bar in Brushed Nickel
12"W x 9"H x 7"EXT
2 lights x 100W MED
• opal white glass



CN578312

3 light bath bar in Brushed Nickel
20"W x 9"H x 7"EXT
3 lights x 100W MED
• opal white glass



CN578412

4 light bath bar in Brushed Nickel
27"W x 9"H x 7"EXT
4 lights x 100W MED
• opal white glass



BATH

RAVENDALE

CN578171

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 7"EXT
1 lights x 100W MED
• opal white glass



CN578211

2 light bath bar in Oil Rubbed Bronze
12"W x 9"H x 7"EXT
2 lights x 100W MED
• opal white glass



CN578311

3 light bath bar in Oil Rubbed Bronze
20"W x 9"H x 7"EXT
3 lights x 100W MED
• opal white glass



CN578411

4 light bath bar in Oil Rubbed Bronze
27"W x 9"H x 7"EXT
4 lights x 100W MED
• opal white glass



SUMMIT PLACE

CN579172

1 light wall sconce in Brushed Nickel
5"W x 9"H x 6"EXT
1 lights x 100W MED
• opal white glass



CN579212

2 light bath bar in Brushed Nickel
12"W x 8"H x 7"EXT
2 lights x 100W MED
• opal white glass



CN579312

3 light bath bar in Brushed Nickel
21"W x 9"H x 6"EXT
3 lights x 100W MED
• opal white glass



CN579412

4 light bath bar in Brushed Nickel
21"W x 9"H x 6"EXT
4 lights x 100W MED
• opal white glass



BATH

SUMMIT PLACE

CN579171

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 6"EXT
1 lights x 100W MED
• opal white glass



CN579211

2 light bath bar in Oil Rubbed Bronze
12"W x 8"H x 7"EXT
2 lights x 100W MED
• opal white glass



CN579311

3 light bath bar in Oil Rubbed Bronze
21"W x 9"H x 6"EXT
3 lights x 100W MED
• opal white glass



CN579411

4 light bath bar in Oil Rubbed Bronze
21"W x 9"H x 6"EXT
4 lights x 100W MED
• opal white glass



BELMAR

CN575172

1 light wall sconce in Brushed Nickel
5"W x 9"H x 6"EXT
1 light x 100W MED
• opal white glass



CN575212

2 light bath bar in Brushed Nickel
13"W x 9"H x 6"EXT
2 lights x 100W MED
• opal white glass



CN575312

3 light bath bar in Brushed Nickel
22"W x 9"H x 6"EXT
3 lights x 100W MED
• opal white glass



CN575412

4 light bath bar in Brushed Nickel
31"W x 9"H x 6"EXT
4 lights x 100W MED
• opal white glass



BATH

BELMAR

CN575171

- 1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 6"EXT
1 light x 100W MED
• opal white glass



CN575211

- 2 light bath bar in Oil Rubbed Bronze
13"W x 9"H x 6"EXT
2 lights x 100W MED
• opal white glass



CN575311

- 3 light bath bar in Oil Rubbed Bronze
22"W x 9"H x 6"EXT
3 lights x 100W MED
• opal white glass



CN575411

- 4 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 6"EXT
4 lights x 100W MED
• opal white glass



PENDENZA

TN0005217



1 light wall sconce in Brushed Nickel
5"W x 12"H x 8"EXT
1 lights x 100W MED
• etched glass



TV0007217



2 light bath bar in Brushed Nickel
13"W x 12"H x 9"EXT
2 lights x 100W MED
• etched glass



SL715378



3 light bath in Brushed Nickel
20"W x 12"H x 9"EXT
3 lights x 100W MED
• etched glass



SL715478



4 light bath in Brushed Nickel
27"W x 12"H x 9"EXT
4 lights x 100W MED
• etched glass



BATH

PENDENZA

TN0005715

1 light wall sconce in Oil Rubbed Bronze
5"W x 12"H x 8"EXT
1 lights x 100W MED
• etched glass



TV0007715

2 light bath bar in Oil Rubbed Bronze
13"W x 12"H x 9"EXT
2 lights x 100W MED
• etched glass



SL715315

3 light bath bar in Oil Rubbed Bronze
20"W x 12"H x 9"EXT
3 lights x 100W MED
• etched glass



SL715415

4 light bath bar in Oil Rubbed Bronze
27"W x 12"H x 9"EXT
4 lights x 100W MED
• etched glass





PITTMAN



TIA

PITTMAN

190023217

1 light wall sconce in Brushed Nickel
5"W x 9"H x 6"EXT
1 lights x 100W MED
• etched glass



190022217

2 light bath bar in Brushed Nickel
12"W x 10"H x 6"EXT
2 lights x 100W MED
• etched glass



190024217

3 light bath bar in Brushed Nickel
19"W x 10"H x 6"EXT
3 lights x 100W MED
• etched glass



190025217

4 light bath bar in Brushed Nickel
24"W x 10"H x 6"EXT
4 lights x 100W MED
• etched glass



BATH

PITTMAN

190023719

1 light wall sconce in Sienna Bronze
5"W x 9"H x 6"EXT
1 lights x 100W MED
• etched glass



190022719

2 light bath bar in Sienna Bronze
12"W x 10"H x 6"EXT
2 lights x 100W MED
• etched glass



190024719

3 light bath bar in Sienna Bronze
19"W x 10"H x 6"EXT
3 lights x 100W MED
• etched glass



190025719

4 light bath bar in Sienna Bronze
24"W x 10"H x 6"EXT
4 lights x 100W MED
• etched glass



WRIGHT

TN0007117



- 1 light bath bar in Matte Nickel
5"W x 10"H x 7"EXT
1 light x 100W MED
• etched white glass



TV0008117



- 2 light bath bar in Matte Nickel
15"W x 11"H x 7"EXT
2 lights x 100W MED
• etched white glass



TV0009117



- 3 light bath bar in Matte Nickel
24"W x 11"H x 7"EXT
3 lights x 100W MED
• etched white glass



TV0010117



- 4 light bath bar in Matte Nickel
32"W x 11"H x 7"EXT
4 lights x 100W MED
• etched white glass



BATH

WRIGHT

TN0007704



- 1 light wall sconce in Espresso
- 5"W x 10"H x 7"EXT
- 1 light x 100W MED
- champagne glass



190114704



- 2 light bath bar in Espresso
- 15"W x 11"H x 7"EXT
- 2 lights x 100W MED
- champagne glass



190115704



- 3 light bath bar in Espresso
- 24"W x 11"H x 7"EXT
- 3 lights x 100W MED
- champagne glass



190116704



- 4 light bath bar in Espresso
- 32"W x 11"H x 7"EXT
- 4 lights x 100W MED
- champagne glass



BATH

SINCLAIR

CN573171

1 light wall sconce in Brushed Nickel
5"W x 10"H x 5"EXT
1 light x 100W MED
• frosted white glass



CN573211

2 light bath bar in Brushed Nickel
15"W x 9"H x 6"EXT
2 lights x 100W MED
• frosted white glass



CN573311

3 light bath bar in Brushed Nickel
22"W x 9"H x 6"EXT
3 lights x 100W MED
• frosted white glass



CN573411

3 light bath bar in Brushed Nickel
30"W x 9"H x 6"EXT
4 lights x 100W MED
• frosted white glass



BATH

CN573172

1 light wall sconce in Polished Chrome

5"W x 10"H x 5"EXT

1 light x 100W MED

- frosted white glass



CN573212

2 light bath bar in Polished Chrome

15"W x 9"H x 6"EXT

2 lights x 100W MED

- frosted white glass



CN573312

3 light bath bar in Polished Chrome

22"W x 9"H x 6"EXT

3 lights x 100W MED

- frosted white glass



CN573412

3 light bath bar in Polished Chrome

30"W x 9"H x 6"EXT

4 lights x 100W MED

- frosted white glass



TREME

TN0010217

1 light wall sconce in Brushed Nickel
5"W x 12"H x 8"EXT
1 light x 100W MED
• etched white glass



TV0019217

2 light bath in Brushed Nickel
14"W x 7"H x 7"EXT
2 lights x 100W MED
• etched white glass



TV0020217

3 light bath bar in Brushed Nickel
23"W x 7"H x 7"EXT
3 lights x 100W MED
• etched white glass



TV0021217

4 light bath bar in Brushed Nickel
32"W x 7"H x 7"EXT
4 lights x 100W MED
• etched white glass



TV0022217

5 light bath bar in Brushed Nickel
41"W x 7"H x 7"EXT
5 lights x 100W MED
• etched white glass



BATH

TREME

TN0010704

1 light wall sconce in Espresso
5"W x 12"H x 8"EXT
1 light x 100W MED
• champagne glass



TV0019704

2 light bath bar in Espresso
14"W x 7"H x 7"EXT
2 lights x 100W MED
• champagne glass



TV0020704

3 light bath bar in Espresso
23"W x 7"H x 7"EXT
3 lights x 100W MED
• champagne glass



TV0021704

4 light bath bar in Espresso
32"W x 7"H x 7"EXT
4 lights x 100W MED
• champagne glass



TV0022704

5 light bath bar in Espresso
41"W x 7"H x 7"EXT
5 lights x 100W MED
• champagne glass



BRIGHTON

1001WS/20

1 light wall sconce in Brushed Nickel
6"W x 11"H x 8"EXT
1 light x 75W MED
• white glass



1002BB/20

2 light bath bar in Brushed Nickel
15"W x 11"H x 7"EXT
2 lights x 75W MED
• white glass



1003BB/20

3 light bath bar in Brushed Nickel
24"W x 11"H x 7"EXT
3 lights x 75W MED
• white glass



1004BB/20

4 light bath bar in Brushed Nickel
33"W x 11"H x 7"EXT
4 lights x 75W MED
• white glass



BATH

BRIGHTON

1051WS/10

1 light wall sconce in Oil Rubbed Bronze
6"W x 11"H x 8"EXT
1 light x 75W MED
• white glass



1052BB/10

2 light bath bar in Oil Rubbed Bronze
15"W x 11"H x 7"EXT
2 lights x 75W MED
• white glass



1053BB/10

3 light bath bar in Oil Rubbed Bronze
24"W x 11"H x 7"EXT
3 lights x 75W MED
• white glass



1054BB/10

4 light bath bar in Oil Rubbed Bronze
33"W x 11"H x 7"EXT
4 lights x 75W MED
• white glass



1201WS/20

1 light wall sconce in Brushed Nickel
6"W x 9"H x 8"EXT
1 light x 100W MED
• white glass



1202BB/20

2 light bath bar in Brushed Nickel
15"W x 9"H x 7"EXT
2 lights x 100W MED
• white glass



1203BB/20

3 light bath bar in Brushed Nickel
23"W x 9"H x 7"EXT
3 lights x 100W MED
• white glass



1204BB/20

4 light bath bar in Brushed Nickel
32"W x 9"H x 7"EXT
4 lights x 100W MED
• white glass



1251WS/20

1 light wall sconce in Oil Rubbed Bronze
6"W x 9"H x 8"EXT
1 light x 100W MED
• white glass



1252BB/20

2 light bath bar in Oil Rubbed Bronze
15"W x 9"H x 7"EXT
2 lights x 100W MED
• white glass



1253BB/20

3 light bath bar in Oil Rubbed Bronze
23"W x 9"H x 7"EXT
3 lights x 100W MED
• white glass



1254BB/20

4 light bath bar in Oil Rubbed Bronze
32"W x 9"H x 7"EXT
4 lights x 100W MED
• white glass



CN570172

1 light wall sconce in Brushed Nickel

5"W x 9"H x 8"EXT

1 lights x 100W MED

- white glass



CN570212

2 light bath bar in Brushed Nickel

13"W x 9"H x 8"EXT

2 lights x 100W MED

- white glass



CN570312

3 light bath bar in Brushed Nickel

17"W x 9"H x 8"EXT

3 lights x 100W MED

- white glass



CN570412

4 light bath bar in Brushed Nickel

23"W x 9"H x 8"EXT

4 lights x 100W MED

- white glass



CN570171

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 8"EXT
1 lights x 100W MED
• white glass



CN570211

2 light bath bar in Oil Rubbed Bronze
13"W x 9"H x 8"EXT
2 lights x 100W MED
• white glass



CN570311

3 light bath bar in Oil Rubbed Bronze
17"W x 9"H x 8"EXT
3 lights x 100W MED
• white glass



CN570411

4 light bath bar in Oil Rubbed Bronze
23"W x 9"H x 8"EXT
4 lights x 100W MED
• white glass



BELLA

TN0003217

1 light wall sconce in Brushed Nickel
5"W x 9"H x 7"EXT
1 lights x 100W MED
• etched glass



SL714278

2 light bath bar in Brushed Nickel
13"W x 9"H x 7"EXT
2 lights x 100W MED
• etched glass



SL714378

3 light bath bar in Brushed Nickel
18"W x 9"H x 7"EXT
3 lights x 100W MED
• etched glass



SL714478

4 light bath bar in Brushed Nickel
25"W x 9"H x 7"EXT
4 lights x 100W MED
• etched glass



SL714578

5 light bath bar in Brushed Nickel
31"W x 9"H x 7"EXT
5 lights x 100W MED
• etched glass



BATH

BELLA

TN0003715

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 7"EXT
1 lights x 100W MED
• etched glass



SL714215

2 light bath bar in Oil Rubbed Bronze
13"W x 9"H x 7"EXT
2 lights x 100W MED
• etched glass



SL714315

3 light bath bar in Oil Rubbed Bronze
18"W x 9"H x 7"EXT
3 lights x 100W MED
• etched glass



SL714415

4 light bath bar in Oil Rubbed Bronze
25"W x 9"H x 7"EXT
4 lights x 100W MED
• etched glass



SL714515

5 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 7"EXT
5 lights x 100W MED
• etched glass



1301WS/20

1 light wall sconce in Brushed Nickel
5"W x 8"H x 7"EXT
1 light x 60W MED
• white glass



1302BB/20

2 light bath bar in Brushed Nickel
14"W x 9"H x 7"EXT
2 lights x 60W MED
• white glass



1303BB/20

3 light bath bar in Brushed Nickel
22"W x 9"H x 7"EXT
3 lights x 60W MED
• white glass



1304BB/20

4 light bath bar in Brushed Nickel
31"W x 9"H x 7"EXT
4 lights x 60W MED
• white glass



JACKSON

1351WS/10

1 light wall sconce in Oil Rubbed Bronze
5"W x 8"H x 7"EXT
1 light x 60W MED
• white glass



1352BB/10

2 light bath bar in Oil Rubbed Bronze
14"W x 9"H x 7"EXT
2 lights x 60W MED
• white glass



1353BB/10

3 light bath bar in Oil Rubbed Bronze
22"W x 9"H x 7"EXT
3 lights x 60W MED
• white glass



1354BB/10

4 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 7"EXT
4 lights x 60W MED
• white glass



BATH

CHATHAM



1101WS/20

1 light wall sconce in Brushed Nickel
5"W x 19"H x 7"EXT
1 light x 75W MED
• white glass



1102BB/20



2 light bath bar in Brushed Nickel
14"W x 11"H x 7"EXT
2 lights x 75W MED
• white glass



1103BB/20



3 light bath bar in Brushed Nickel
23"W x 11"H x 7"EXT
3 lights x 75W MED
• white glass



1104BB/20



4 light bath bar in Brushed Nickel
32"W x 11"H x 7"EXT
4 lights x 75W MED
• white glass

BATH

CHATHAM

1151WS/20

1 light wall sconce in Oil Rubbed Bronze
5"W x 19"H x 7"EXT
1 light x 75W MED
• white glass



1152BB/20

2 light bath bar in Oil Rubbed Bronze
14"W x 11"H x 7"EXT
2 lights x 75W MED
• white glass



1153BB/20

3 light bath bar in Oil Rubbed Bronze
23"W x 11"H x 7"EXT
3 lights x 75W MED
• white glass



1154BB/20

4 light bath bar in Oil Rubbed Bronze
32"W x 11"H x 7"EXT
4 lights x 75W MED
• white glass



HAVEN

TN0009741



1 light wall sconce in Satin Pewter
5"W x 14"H x 6"EXT
1 light x 100W MED
• etched glass



TV0015741



2 light bath bar in Satin Pewter
18"W x 11"H x 7"EXT
2 lights x 100W MED
• etched glass



TV0016741



3 light bath bar in Satin Pewter
24"W x 11"H x 7"EXT
3 lights x 100W MED
• etched glass



TV0017741



4 light bath bar in Satin Pewter
30"W x 11"H x 7"EXT
4 lights x 100W MED
• etched glass



TV0018741



5 light bath bar in Satin Pewter
36"W x 11"H x 7"EXT
5 lights x 100W MED
• etched glass



BATH

HAVEN

TN0009704

1 light wall sconce in Espresso
5"W x 14"H x 6"EXT
1 light x 100W MED
• etched glass



TV0015704

2 light bath bar in Espresso
18"W x 11"H x 7"EXT
2 lights x 100W MED
• etched glass



TV0016704

3 light bath bar in Espresso
24"W x 11"H x 7"EXT
3 lights x 100W MED
• etched glass



TV0017704

4 light bath bar in Espresso
30"W x 11"H x 7"EXT
4 lights x 100W MED
• etched glass



TV0018704

5 light bath bar in Espresso
36"W x 11"H x 7"EXT
5 lights x 100W MED
• etched glass



ECLIPSE

SL744178 

1 light wall sconce in Brushed Nickel
6"W x 10"H x 8"EXT
1 light x 100W MED
• alabaster style glass



SL744278 

1 light bath bar in Brushed Nickel
18"W x 10"H x 8"EXT
2 lights x 100W MED
• alabaster style glass



SL744378 

3 light bath bar in Brushed Nickel
24"W x 10"H x 8"EXT
3 lights x 100W MED
• alabaster style glass



SL744478 

4 light bath bar in Brushed Nickel
36"W x 10"H x 8"EXT
4 lights x 100W MED
• alabaster style glass



SL744578 

5 light bath bar in Brushed Nickel
48"W x 10"H x 8"EXT
5 lights x 100W MED
• alabaster style glass



BATH

ECLIPSE

SL744163 

1 light wall sconce in Painted Bronze
6"W x 10"H x 8"EXT
1 light x 100W MED
• alabaster style glass



SL744263 

2 light bath bar in Painted Bronze
18"W x 10"H x 8"EXT
2 lights x 100W MED
• alabaster style glass



SL744363 

3 light bath bar in Painted Bronze
24"W x 10"H x 8"EXT
3 lights x 100W MED
• alabaster style glass



SL744463 

4 light bath bar in Painted Bronze
36"W x 10"H x 8"EXT
4 lights x 100W MED
• alabaster style glass



SL744563 

5 light bath bar in Painted Bronze
48"W x 10"H x 8"EXT
5 lights x 100W MED
• alabaster style glass



BATH

HOMESTEAD - ALSO USED IN RIVA & TAHOE COLLECTIONS

SL758178

1 light wall sconce in Brushed Nickel
6"W x 12"H x 8"EXT
1 light x 100W MED
• alabaster style glass



SL758278

2 light bath bar in Brushed Nickel
18"W x 9"H x 8"EXT
2 lights x 100W MED
• alabaster style glass



SL758378

3 light bath bar in Brushed Nickel
24"W x 9"H x 8"EXT
3 lights x 100W MED
• alabaster style glass



SL758478

4 light bath bar in Brushed Nickel
30"W x 9"H x 8"EXT
4 lights x 100W MED
• alabaster style glass



SL758578

5 light bath bar in Brushed Nickel
36"W x 9"H x 8"EXT
5 lights x 100W MED
• alabaster style glass



SL758678

6 light bath bar in Brushed Nickel
48"W x 9"H x 8"EXT
6 lights x 100W MED
• alabaster style glass



HOMESTEAD

SL75824

2 light bath bar in Chrome
18"W x 9"H x 8"EXT
2 lights x 100W MED
• alabaster style glass



SL75834

3 light bath bar in Chrome
24"W x 9"H x 8"EXT
3 lights x 100W MED
• alabaster style glass



SL75844

4 light bath bar in Chrome
30"W x 9"H x 8"EXT
4 lights x 100W MED
• alabaster style glass



SL75854

5 light bath bar in Chrome
36"W x 9"H x 8"EXT
5 lights x 100W MED
• alabaster style glass



SL75864

6 light bath bar in Chrome
48"W x 9"H x 8"EXT
6 lights x 100W MED
• alabaster style glass



BATH

HOMESTEAD - ALSO USED ON RIVA & TAHOE COLLECTIONS

SL758263

2 light bath bar in Painted Bronze
18"W x 9"H x 8"EXT
2 lights x 100W MED
• alabaster style glass



SL758363

3 light bath bar in Painted Bronze
24"W x 9"H x 8"EXT
3 lights x 100W MED
• alabaster style glass



SL758463

4 light bath bar in Painted Bronze
30"W x 9"H x 8"EXT
4 lights x 100W MED
• alabaster style glass



SL758563

5 light bath bar in Painted Bronze
36"W x 9"H x 8"EXT
5 lights x 100W MED
• alabaster style glass



SL758663

6 light bath in Painted Bronze
48"W x 9"H x 8"EXT
6 lights x 100W MED
• alabaster style glass



BATH

HOMESTEAD - *ALSO USED ON WHITMORE COLLECTION

SL710341

3 light bath bar in Satin Pewter*
24"W x 9"H x 8"EXT
3 lights x 100W MED
• etched glass



SL710441

4 light bath bar in Satin Pewter*
30"W x 9"H x 8"EXT
4 lights x 100W MED
• etched glass



SL710323

3 light bath bar in Colonial Bronze
24"W x 9"H x 8"EXT
3 lights x 100W MED
• etched glass



SHELBURNE

5501BB/20

1 light wall sconce in Brushed Nickel
8"W x 7"H x 9"EXT
1 light x 75W MED
• white etched glass



5502BB/20

2 light bath bar in Brushed Nickel
15"W x 6"H x 9"EXT
2 lights x 75W MED
• white etched glass



5503BB/20

3 light bath bar in Brushed Nickel
25"W x 6"H x 9"EXT
3 lights x 75W MED
• white etched glass



5504BB/20

4 light bath bar in Brushed Nickel
33"W x 6"H x 9"EXT
4 lights x 75W MED
• white etched glass



BATH

SHELBURNE

5551BB/10

1 light wall sconce in Oil Rubbed Bronze
8"W x 7"H x 9"EXT
1 light x 75W MED
• white etched glass



5552BB/10

2 light bath bar in Oil Rubbed Bronze
15"W x 6"H x 9"EXT
2 lights x 75W MED
• white etched glass



5553BB/10

3 light bath bar in Oil Rubbed Bronze
25"W x 6"H x 9"EXT
3 lights x 75W MED
• white etched glass



5554BB/10

4 light bath in Oil Rubbed Bronze
33"W x 6"H x 9"EXT
4 lights x 75W MED
• white etched glass



SHELBURNE

5501BB/30

1 light wall sconce in Polished Chrome
8"W x 7"H x 9"EXT
1 light x 75W MED
• white etched glass



5502BB/30

2 light bath bar in Polished Chrome
15"W x 6"H x 9"EXT
2 lights x 75W MED
• white etched glass



5503BB/30

3 light bath bar in Polished Chrome
25"W x 6"H x 9"EXT
3 lights x 75W MED
• white etched glass



5504BB/30

4 light bath bar in Polished Chrome
33"W x 6"H x 9"EXT
4 lights x 75W MED
• white etched glass



BATH

SADBURY

5601BB/30

1 light wall sconce in Polished Chrome
6"W x 10"H x 8"EXT
1 light x 75W MED
• white glass



5602BB/30

2 light bath bar in Polished Chrome
15"W x 10"H x 8"EXT
2 lights x 75W MED
• white glass



5603BB/30

3 light bath bar in Polished Chrome
23"W x 10"H x 8"EXT
3 lights x 75W MED
• white glass



5604BB/30

4 light bath bar in Polished Chrome
32"W x 10"H x 8"EXT
4 lights x 75W MED
• white glass



BATH

SUDBURY

5601BB/20

1 light wall sconce in Brushed Nickel
6"W x 10"H x 8"EXT
1 light x 75W MED
• white glass



5602BB/20

2 light bath bar in Brushed Nickel
15"W x 10"H x 8"EXT
2 lights x 75W MED
• white glass



5603BB/20

3 light bath bar in Brushed Nickel
23"W x 10"H x 8"EXT
3 lights x 75W MED
• white glass



5604BB/20

4 light bath bar in Brushed Nickel
32"W x 10"H x 8"EXT
4 lights x 75W MED
• white glass



BATH

SUDBURY

5651BB/10

1 light wall sconce in Oil Rubbed Bronze
6"W x 10"H x 8"EXT
1 light x 75W MED
• white glass



5652BB/10

2 light bath bar in Oil Rubbed Bronze
15"W x 10"H x 8"EXT
2 lights x 75W MED
• white glass



5653BB/10

3 light bath bar in Oil Rubbed Bronze
23"W x 10"H x 8"EXT
3 lights x 75W MED
• white glass



5654BB/10

4 light bath bar in Oil Rubbed Bronze
32"W x 10"H x 8"EXT
4 lights x 75W MED
• white glass



SL706178

3 light bath bar in Brushed Nickel

49"W x 5"H x 12"EXT

3 lights x 32W F32T8 (32W)

- white acrylic diffuser
- 120V electronic ballast



SL716578 ADA

2 light bath bar in Brushed Nickel

Model	Width	Body Height	HCO*	Extends	No. Lights	Recom. Lamp
SL716578	25"	5"	2 1/2"	4"	2	F17T8 (17W)
SL716778	49"	5"	2 1/2"	4"	2	F32T8 (32W)

- white acrylic diffuser
- 120V electronic ballast



VANITY STRIPS



SL74134 3 light strip in Chrome (shown)

Width	Body Height	Extends	No. Lights	Max. Watt.
18"	5"	3"	3	100W

- also available in **SL741378** Brushed Nickel

SL73244 4 light strip in Chrome; beveled mirror

Width	Body Height	Extends	No. Lights	Max. Watt.
25"	5"	3"	4	100W

SL74024 4 light strip in Chrome (shown)

Width	Body Height	Extends	No. Lights	Max. Watt.
24"	5"	3"	4	100W

- also available in **SL74028** matte white and **SL740278** Brushed Nickel

SL741578 5 light strip in Brushed Nickel (shown)

Width	Body Height	Extends	No. Lights	Max. Watt.
30"	5"	3"	5	100W

- also available in **SL74154** Chrome



SL74184 6 light strip in Chrome (shown)

Width	Body Height	Extends	No. Lights	Max. Watt.
36"	5"	3"	6	100W

- also available in **SL741878** Brushed Nickel



SL742578 8 light strip in Brushed Nickel (shown)

Width	Body Height	Extends	No. Lights	Max. Watt.
48"	5"	3"	8	100W

- also available in **SL74254** Chrome



BATH



BATH

TASK LIGHTING






TASK LIGHTING

ZeeLED PRO linear lighting



Product Code	Fixture Dimensions	Lamp
LV012RSF (White) 12" ZeeLED Pro	12" W x 4" D x 1" H	6W LED, 3000K, 4000K & 6000K mode switch, 90 CRI 450 Lumens, Dimmable, High/Low switch
LV018RSF (White) 18" ZeeLED Pro	18" W x 4" D x 1" H	9W LED, 3000K, 4000K & 6000K mode switch, 90 CRI 550 Lumens, Dimmable, High/Low switch
LV024RSF (White) 24" ZeeLED Pro	24" W x 4" D x 1" H	12W LED, 3000K, 4000K & 6000K mode switch, 90 CRI 1000 Lumens, Dimmable, High/Low switch
LV032RSF (White) 32" ZeeLED Pro	32" W x 4" D x 1" H	16W LED, 3000K, 4000K & 6000K mode switch, 90 CRI 550 Lumens, Dimmable, High/Low switch

ZeeLED Pro Accessories



ZeeStick Inline Connector
ZSBUTT-N-30
(White)

ZeeStick 12" Flexible Joiner
ZSCON12-N-30
(White)

ZeeStick 24" Flexible Joiner for Hardwire
ZSCON24-N-30
(White)


ZeeStick 72" Cord and Plug
ZSPUG-N-30
(White)

TASK LIGHTING

ZeeLITE low voltage xenon linear lighting



9", 17½", 26", 34½", or 48"



white

stainless steel

bronze



HZ000-COR
zeelite cord & plug

Energy-saving xenon lamps with a rated average lamp life of 10,000 hours that evenly distribute light while producing 35% less heat than halogen bulbs. Zeelite is available in three metal finishes, and comes complete with a transformer.

Product Highlights

- More diffuse glass
- Easy-to-use friction clips for door release
- Captioned door provides easy lamp and installation access
- Mounting screws come captioned and ready to install
- Wiring assembly is easily accessed via captioned wing nuts
- Standard ¼" knockouts for wiring
- Easy-to-use High/Off/Low switch
- Xenon lamp technology
- Installs in minutes.

Performance Notes

- To obtain a uniform light, space units 10" apart
- Position opening toward front of cabinet

Lamp (included)
18W 12V wedge base xenon
Indoor use only

	Product Code	Fixture Dimensions	Lamp
9"	HZ009RSF (White)	9"L x 4¾"W x 1⅝"D	18W 12V wedge base xenon included L5 Replacement Lamp
	HZ109RSF (Stainless Steel)		
	HZ309RSF (Bronze)		
17"	HZ017RSF (White)	17½"L x 4¾"W x 1⅝"D	2 x 18W 12V wedge base xenon included L5 Replacement Lamp
	HZ117RSF (Stainless Steel)		
	HZ317RSF (Bronze)		
26"	HZ026RSF (White)	26"L x 4¾"W x 1⅝"D	3 x 18W 12V wedge base xenon included L5 Replacement Lamp
	HZ126RSF (Stainless Steel)		
	HZ326RSF (Bronze)		
34"	HZ035RSF (White)	34½" W x 4¾"W x 1⅝"D	4 x 18W 12V wedge base xenon included L5 Replacement Lamp
	HZ135RSF (Stainless Steel)		
	HZ335RSF (Bronze)		
48"	HZ048RSF (White)	48" W x 4¾"W x 1⅝"D	6 x 18W 12V wedge base xenon included L5 Replacement Lamp
	HZ148RSF (Stainless Steel)		
	HZ348RSF (Bronze)		

TASK LIGHTING


ZeeLINE line voltage xenon linear lighting



9", 17½", 26", 34½", or 48"

bronze white

Install 10" apart and 7K" from backsplash for even illumination.



All the benefits of Alico's famous Zeeline but as a 120V line-voltage fixture.

Product Highlights

- More diffuse glass
- Easy-to-use friction clips for door release
- Captioned door provides easy lamp and installation access
- Mounting screws come captioned and ready to install
- Wiring assembly is easily accessed via captioned wing nuts
- Standard Y"Ø knockouts for wiring
- Easy-to-use High/Off/Low switch
- Xenon lamp technology
- Installs in minutes.

Performance Notes

- To obtain a uniform light, space units 10" apart
- Position opening toward front of cabinet


Lamp (included)
25W 120V wedge based xenon
Indoor use only

Product Code

Fixture Dimensions

Lamp

9"	ZL009RSF (White)	9"L x 4¾"W x 1 ⁵ / ₁₆ "D	25W 120V wedge base xenon included
	ZL309RSF (Bronze)		L9 Replacement Lamp
17"	ZL017RSF (White)	17½"L x 4¾"W x 1 ⁵ / ₁₆ "D	2 x 25W 120V wedge base xenon included
	ZL317RSF (Bronze)		L9 Replacement Lamp
26"	ZL026RSF (White)	26"L x 4¾"W x 1 ⁵ / ₁₆ "D	3 x 25W 120V wedge base xenon included
	ZL326RSF (Bronze)		L9 Replacement Lamp
34"	ZL035RSF (White)	34½" W x 4¾"W x 1 ⁵ / ₁₆ "D	4 x 25W 120V wedge base xenon included
	ZL335RSF (Bronze)		L9 Replacement Lamp
48"	ZL048RSF (White)	48" W x 4¾"W x 1 ⁵ / ₁₆ "D	5 x 25W 120V wedge base xenon included
	ZL348RSF (Bronze)		L9 Replacement Lamp



Matte White

Model	Width	Body Height	Length	No. Lights	Recom. Lamp
UCX2008	3½"	1¼"	12"	2	G8 20W
UCX3008	3½"	1¼"	18"	3	G8 20W

- White steel housing
- Etched glass diffuser
- Hi / Low switch included
- 120V lamps included

TASK LIGHTING

MLE301-5-16M **LED**

TUXEDO

puk light in satin nickel
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable

- includes:
- 1x puk + 1 connector included
 - 1x 6' power cord with plug and line switch

**MLE313-5-16MK** **LED**

TUXEDO

3 puk light in satin nickel
 2¾"W x 1"H
 3 x 4WLED, 3000K, 80CRI
 600 Lumens, dimmable

- includes:
- 1x puk with 1 connector
 - 2 x puks with 2 connectors
 - 1 x 6' power cord with plug and line switch
 - 2 x 6" jumper cords

Mounting distance between puks: 12-18";
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**MLE301-5-30** **LED**

TUXEDO

puk light in white
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable

- includes:
- 1x puk + 1 connector included
 - 1x 6' power cord with plug and line switch

**MLE313-5-30K** **LED**

TUXEDO

3 puk light in white
 3"W x 1"H
 2¾" x 4WLED, 3000K, 80CRI
 600 Lumens, dimmable

- includes:
- 1x puk with 1 connector
 - 2 x puks with 2 connectors
 - 1 x 6' power cord with plug and line switch
 - 2 x 6" jumper cords

Mounting distance between puks: 12-18";
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**MLE301-5-31** **LED**

TUXEDO

puk light in black
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable

- includes:
- 1x puk + 1 connector included
 - 1x 6' power cord with plug and line switch

**MLE313-5-31K** **LED**

TUXEDO

3 puk light in black
 2¾"W x 1"H
 3 x 4WLED, 3000K, 80CRI
 600 Lumens, dimmable

- includes:
- 1x puk with 1 connector
 - 2 x puks with 2 connectors
 - 1 x 6' power cord with plug and line switch
 - 2 x 6" jumper cords

Mounting distance between puks: 12-18";
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"



MLE201-5-16M **LED**

TUXEDO

puk light in satin nickel
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable
 includes:

- 1x puk + 2 connectors included

**MLE316-5-16MK** **LED**

TUXEDO

6 puk light in satin nickel
 2¾"W x 1"H
 6 x 4WLED, 3000K, 80CRI
 1200 Lumens, dimmable
 includes:

- 1x puk with 1 connector
- 5 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between pucks: 12-18";
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**MLE201-5-30** **LED**

TUXEDO

puk light in white
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable
 includes:

- 1x puk + 2 connectors included

**MLE316-5-30K** **LED**

TUXEDO

6 puk light in white
 2¾"W x 1"H
 6 x 4WLED, 3000K, 80CRI
 1200 Lumens, dimmable
 includes:

- 1x puk with 1 connector
- 5 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between pucks: 12-18";
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**MLE201-5-31** **LED**

TUXEDO

puk light in white
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable
 includes:

- 1x puk + 2 connectors included

**MLE316-5-31K** **LED**

TUXEDO

6 puk light in black
 2¾"W x 1"H
 6 x 4WLED, 3000K, 80CRI
 1200 Lumens, dimmable
 includes:

- 1x puk with 1 connector
- 5 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between pucks: 12-18";
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**TASK LIGHTING**

MLE423-5-16MK**LED**

TUXEDO SWIVEL

puk light in satin nickel
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable
 includes:

- 1x puk + 1 connector included
- 1x 6' power cord with plug and line switch

**MLE433-5-16MK****LED**

TUXEDO SWIVEL

3 puk light in satin nickel
 2¾"W x 1"H
 3 x 4WLED, 3000K, 80CRI
 600 Lumens, dimmable
 includes:

- 1x puk with 1 connector
- 2 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 2 x 6" jumper cords

Mounting distance between pucks: 12-18"
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**MLE423-5-30K****LED**

TUXEDO SWIVEL

puk light in white
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable
 includes:

- 1x puk + 1 connector included
- 1x 6' power cord with plug and line switch

**MLE433-5-30K****LED**

TUXEDO SWIVEL

3 puk light in white
 2¾"W x 1"H
 3 x 4WLED, 3000K, 80CRI
 600 Lumens, dimmable
 includes:

- 1x puk with 1 connector
- 2 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 2 x 6" jumper cords

Mounting distance between pucks: 12-18"
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**MLE423-5-31K****LED**

TUXEDO SWIVEL

puk light in black
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable
 includes:

- 1x puk + 1 connector included
- 1x 6' power cord with plug and line switch

**MLE433-5-31K****LED**

TUXEDO SWIVEL

3 puk light in black
 2¾"W x 1"H
 3 x 4WLED, 3000K, 80CRI
 600 Lumens, dimmable
 includes:

- 1x puk with 1 connector
- 2 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 2 x 6" jumper cords

Mounting distance between pucks: 12-18"
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**TASK LIGHTING**

MLE401-5-16M**LED**

TUXEDO SWIVEL
 puk light in satin nickel
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable
 includes:

- 1x puk + 2 connectors included

**MLE426-5-16MK****LED**

TUXEDO SWIVEL
 6 puk light in satin nickel
 3"W x 1"H
 6 x 4WLED, 3000K, 80CRI
 1200 Lumens, dimmable
 includes:

- 1x puk with 1 connector
- 5 x puks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between puks: 12-18";
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**MLE401-5-30****LED**

TUXEDO SWIVEL
 puk light in white
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable
 includes:

- 1x puk + 2 connectors included

**MLE426-5-30K****LED**

TUXEDO SWIVEL
 6 puk light in white
 3"W x 1"H
 6 x 4WLED, 3000K, 80CRI
 1200 Lumens, dimmable
 includes:

- 1x puk with 1 connector
- 5 x puks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between puks: 12-18";
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**MLE401-5-31****LED**

TUXEDO SWIVEL
 puk light in white
 2¾"W x 1"H
 4WLED, 3000K, 80CRI
 200 Lumens, dimmable
 includes:

- 1x puk + 2 connectors included

**MLE426-5-31K****LED**

TUXEDO SWIVEL
 6 puk light in black
 3"W x 1"H
 6 x 4WLED, 3000K, 80CRI
 1200 Lumens, dimmable
 includes:

- 1x puk with 1 connector
- 5 x puks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between puks: 12-18";
 Join the 6" connectors together for 12" or add the
 (included) 6" jumper between for 18"

**TASK LIGHTING**

PARTS and ACCESSORIES

ACLJB-N-30

hardwire junction box for PUK light
2"W x 1"H
• white



ACL24-N-30

jumper cord for PUK lights
24" length
• white



ACL12-N-30

jumper cord for PUK lights
12" length
• white



ACL36-N-30

jumper cord for PUK lights
36" length
• white



ACL18-N-30

jumper cord
18" length
• white



ZeeSTICK LEDPRO linear lighting **LED**

Fully Integrated, Modular, Continuous

ZeeStick is a SMD powered, fully encapsulated and dimmable family of LED fixtures that enable a myriad of task, undercabinet, cove and accent lighting applications. As a fully integrated, energy conscious linear lighting solution, ZeeStick has no equal.

Features

- 120V AC
- Only 4.2W per foot
- Available in three color temperatures–
 - 2700K Warm White
 - 3500K Natural White
 - 6000K Pure White (special order)
- SMD LED Hi Power Factor
- Integral driver built into every fixture
- Available in four sizes–
 - 12" (5W)
 - 23-3/4" (10W)
 - 39-1/2" (14W)
 - 47-3/8" (18W)

ZeeStick enables the architect and lighting designer the ability to create various applications utilizing a common color temperature. Even the slightest difference in kelvin temperature can create a visual imbalance that may subtly challenge the esthetics of your interior. Using ZeeStick in a combination of applications within the same space will help to successfully create a lighting solution across several platforms while achieving unity in color temperature.

Thanks to a full complement of custom connectors and joiners, ZeeStick is able to achieve longer runs. Inline connectors eliminate cold spots and provide a seamless installation. With the addition of a custom joiner box and ZeeStick cord and plug, installation can be as close as the nearest outlet.



TASK LIGHTING



TASK LIGHTING

ZeeSTICK LED linear lighting **LED**

Specifications

ZeeStick is a modular line of dimmable SMD LEDs soldered to a rigid PC board with integral driver, encapsulated in an extruded aluminum SP body with CF color (white) and polycarbonate frosted diffuser lens. ZeeStick is designed to provide a long and consistent color over its 50,000 hour lamp life due to superior thermal management of the SMD's and quality phosphors used in production. ZeeStick provides an even glow at a huge energy savings over linear fluorescent or halogen.

- 120V AC
- 4.2W per Foot
- Exceeds Title 24
- ROHS Compliant
- ETL Approved



LED Specs:

Color Temp.	Lumens per Watt	Lumens per Foot	Total CRI
2700K	41	202	73
4000K	48	240	75
6000K	63	316	78

ZeeSTICK Accessories



ZeeStick Inline Connector
ZSBUTT-N-30 (White)



ZeeStick 12" Flexible Joiner
ZSCON12-N-30 (White)



ZeeStick 24" Flexible Joiner for Hardwire
ZSCON24-N-30 (White)



ZeeStick 72" Cord and Plug
ZSPUG-N-30 (White)



ZeeStick 120V Wiring Box
ZSBOX-N-30 (White)



ZeeStick LED T-Shaped Connector
4W LED, 220 Lumens
Non-dimmable
ZST-N-98 (Aluminum)



ZeeStick LED L-Shaped Connector, Left Handed
2W LED, 160 Lumens
Non-dimmable
ZSL-N-98 (Aluminum)



ZeeStick LED L-Shaped Connector, Right Handed
2W LED, 160 Lumens
Non-dimmable
ZSR-N-98 (Aluminum)



ZeeStick 90 Degree Clip
ZS-CLIP90-N-15 (Chrome)



ZeeStick Adjustable Clip
ZS-CLIPADJ-N-15 (Chrome)

TASK LIGHTING

ZeeSTICK ordering information **LED**



ZeeStick 120V - 5W Linear Lensed SMD LED Fixture*

Cat. No.	Length	Wattage	Color	Lumens	Color Temp.
ZS303RSF	12"	5W	White	202	2700K
ZS403RSF	12"	5W	White	240	4000K
ZS603RSF	12"	5W	White	316	6000K



ZeeStick 120V - 10W Linear Lensed SMD LED Fixture*

Cat. No.	Length	Wattage	Color	Lumens	Color Temp.
ZS306RSF	23 ³ / ₄ "	10W	White	404	2700K
ZS406RSF	23 ³ / ₄ "	10W	White	480	4000K
ZS606RSF	23 ³ / ₄ "	10W	White	632	6000K



ZeeStick 120V - 14W Linear Lensed SMD LED Fixture*


Cat. No.	Length	Wattage	Color	Lumens	Color Temp.
ZS310RSF	39 ¹ / ₂ "	14W	White	606	2700K
ZS410RSF	39 ¹ / ₂ "	14W	White	720	4000K
ZS610RSF	39 ¹ / ₂ "	14W	White	948	6000K



ZeeStick 120V - 18W Linear Lensed SMD LED Fixture*

Cat. No.	Length	Wattage	Color	Lumens	Color Temp.
ZS312RSF	47 ³ / ₈ "	18W	White	808	2700K
ZS412RSF	47 ³ / ₈ "	18W	White	960	4000K
ZS612RSF	47 ³ / ₈ "	18W	White	1264	6000K

* Each fixture comes with (2) mounting clips, (1) inline connector and (1) power connector for hardware. See NOTE below.



NOTE: Zee-Stick comes complete with standard spring metal brackets and screws. CUSTOM ANGLED BRACKETS ARE AVAILABLE. Consult factory. Interconnectable utilizing Alico ZeeStick connectors. Maximum run per feed is 12 units un-dimmed, six units dimmed.

TASK LIGHTING



TASK LIGHTING

ZeeSTICK LED linear lighting

Applications

ZeeStick is an architectural quality luminaire that was manufactured for the following applications and environments:

- Undercabinet Lighting
- Cove Lighting
- Toe Kick
- Task
- Architectural Detail
- Food Prep and Buffet
- Hospitality
- Entertainment Unit
- Linear Recessed
- Bath and Vanity
- Retail and Display
- Institutional



Photometrics

ZeeSTICK 120V - 5W LINEAR LENSED SMD LED FIXTURE

Category	Result
TOTAL LUMENS	350.16
INPUT VOLTAGE (VAC)	120.00
INPUT CURRENT (AMP)	0.05
INPUT POWER (W)	4.82
INPUT POWER FACTOR	0.79
EFFICACY	72.66
COLOR RENDERING INDEX (CRI)	74.85

ZeeSTICK 120V - 10W LINEAR LENSED SMD LED FIXTURE

Category	Result
TOTAL LUMENS	694.38
INPUT VOLTAGE (VAC)	120.00
INPUT CURRENT (AMP)	0.09
INPUT POWER (W)	9.21
INPUT POWER FACTOR	0.89
EFFICACY	75.43
COLOR RENDERING INDEX (CRI)	74.59

ZeeSTICK 120V - 14W LINEAR LENSED SMD LED FIXTURE

Category	Result
TOTAL LUMENS	1012.06
INPUT VOLTAGE (VAC)	120.00
INPUT CURRENT (AMP)	0.12
INPUT POWER (W)	12.53
INPUT POWER FACTOR	0.85
EFFICACY	80.75
COLOR RENDERING INDEX (CRI)	74.85

ZeeSTICK 120V - 18W LINEAR LENSED SMD LED FIXTURE

Category	Result
TOTAL LUMENS	1273.78
INPUT VOLTAGE (VAC)	120.00
INPUT CURRENT (AMP)	0.16
INPUT POWER (W)	16.62
INPUT POWER FACTOR	0.88
EFFICACY	76.64
COLOR RENDERING INDEX (CRI)	74.67

TASK LIGHTING

RECESSED





RECESSED

6" AIR SEAL IC/NON-IC HOUSINGS

THOMAS[®]
PRO6"
SERIES

PS1

90 watt/150 watt

Depth 7½"

Length 10½"

Width 6½"

Ceiling Open 6½"

- for new construction
- air Seal
- type-IC or non-IC
- inter-locking bar hangers with pre-positioned nails

PS1NSP

Same features as **PS1**, except provided without a socket plate. For use in installations where TRB style fully enclosed eyeball or IC shower trims are used exclusively. Eliminates the need for the installer to remove the socket plate.

PS1NSPQC

Same as **PS1NSP**, except provided with pre-installed quick-connect wire terminals.

PS1CP

Contractor Pack

Includes: Four **PS1** housings and four **TRM30W** white baffle trims



UL/CUL Listed Convertible IC/non-IC



Type-IC

Suitable for direct contact with thermal insulation.

Up to 90 watt maximum lamp when used with **TRB30** trim



Non-IC

For use in non-insulated areas, or when insulation is kept at least 3" away.

Up to 150 watt maximum lamp.

Compatible with all Thomas 6" trims.



Adjustable socket plate provides consistent lamp placement when used with open or baffle trims.



The socket plate is removable for use with fully enclosed, eyeball, or IC shower trims. (Specify **PS1NSP** for optional version provided without the socket plate.)

RECESSED



Higher wattages for non-insulated areas are revealed by peeling off one label.



Large junction box provides four Romex and five conduit knockouts. Listed for through-branch circuit conductors. Cover is hinged to prevent accidental loss.



Includes die-cut plaster shield to protect inside of housing during construction.



PS1RM

90 watt/150 watt

Depth 7½"

Width 6½"

Ceiling Open 6¼"

- for remodel construction
- air Seal
- type-IC or non-IC
- mounts to existing ceilings from ½" to 1¼" thick

6" NON-IC SHALLOW HOUSING

Some trims are not compatible with the PS9. Use only trims specifically noted on pages 268 and 269.



PS9

75 watt

Depth 5¾"

Length 10½"

Width 6½"

Ceiling Open ½"

- for new construction
- non-IC
- inter-locking bar hangers with pre-positioned nails

6" FULLY ENCLOSED TRIMS



TRB30

Black Baffle (shown)

Outside Diameter 8"

Lamp	IC		non-IC	
	Max. Watt	Max. Watt	Max. Watt	Max. Watt
R30	75	75		
PAR30	50	75		
PAR30LN	75	75		
PAR38	90	150		



TRB30W

White Baffle

Outside Diameter 8"

Lamp	IC		non-IC	
	Max. Watt	Max. Watt	Max. Watt	Max. Watt
R30	75	75		
PAR30	50	75		
PAR30LN	75	75		
PAR38	90	150		



TRS30W

White Splay

Outside Diameter 8"

Lamp	IC		non-IC	
	Max. Watt	Max. Watt	Max. Watt	Max. Watt
R30	75	75		
PAR30	75	75		



Fully enclosed trims also support the socket and lamp, so the socket plate must be removed prior to installation. (Or use NSP version.)

6" TRIMS



TRM30

Black Baffle (shown)

Outside Diameter 8"

Lamp	IC		non-IC	
	Max. Watt	Max. Watt	Max. Watt	Max. Watt
R30	75	100		
PAR30	50	75		

PS9 Compatible



TRM30W

White Baffle

Outside Diameter 8"

Lamp	IC		non-IC	
	Max. Watt	Max. Watt	Max. Watt	Max. Watt
R30	75	100		
PAR30	50	75		

PS9 Compatible



THS30CLR

Clear Reflector Trim

Outside Diameter 8"

Lamp	IC		non-IC	
	Max. Watt	Max. Watt	Max. Watt	Max. Watt
R30	75	100		
PAR30	50	75		

PS9 Compatible



Standard 6" trims use coil springs to attach to the socket plate inside the housing. They are independent of the lamp position, and may not be used with any NSP housing.



TR30BN

Brushed Nickel Open Trim

Outside Diameter 8"

Lamp	IC		non-IC	
	Max. Watt	Max. Watt	Max. Watt	Max. Watt
R30	65	75		

PS9 Compatible



TR30W

White Open Trim

Outside Diameter 8"

Lamp	IC		non-IC	
	Max. Watt	Max. Watt	Max. Watt	Max. Watt
R30	65	75		

PS9 Compatible



TR40W

White Open Trim

Outside Diameter 8"

Lamp	IC		non-IC	
	Max. Watt	Max. Watt	Max. Watt	Max. Watt
R40	N/A	150		

RECESSED

6" DIRECTIONAL TRIM



TR18W

White Eyeball

Outside Diameter 8"

Lamp	IC	non-IC
	Max. Watt	Max. Watt
R30	75	75

PS9 Compatible



TR18BN

Brushed Nickel Eyeball

Outside Diameter 8"

Lamp	IC	non-IC
	Max. Watt	Max. Watt
R30	75	75

PS9 Compatible

6" IC SHOWER TRIMS

All shower trims are rated for wet locations. IC shower trims include a reflector which also supports the socket. Use with NSP housings or remove the socket plate from standard housings.



TR6SHR

White Open Shower Trim

For IC or non-IC applications.

Outside Diameter 8"

Lamp	IC	non-IC
	Max. Watt	Max. Watt
PAR38	90	90



TSH12IC

White Albalite Shower Trim

Metal trim ring, with reflector, for IC applications.

Outside Diameter 8"

Lamp	IC	non-IC
	Max. Watt	Max. Watt
A19	25	N/A



TSH16IC

White Drop Opal Shower Trim

Metal trim ring, with reflector, for IC applications.

Outside Diameter 8"

Lamp	IC	non-IC
	Max. Watt	Max. Watt
A19	40	N/A

6" NON-IC SHOWER TRIMS

Non-IC shower trims do not include a reflector. The housing must have a socket plate. Not suitable for use with NSP housings.



TSH12

White Albalite Shower Trim

Aluminum trim ring, no reflector, for non-IC applications.

Outside Diameter 8"

Lamp	IC	non-IC
	Max. Watt	Max. Watt
A19	N/A	60

PS9 Compatible



TSH16


White Drop Opal Shower Trim

Aluminum trim ring, no reflector, for non-IC applications.

Outside Diameter 8"

Lamp	IC	non-IC
	Max. Watt	Max. Watt
A19	N/A	60

PS9 Compatible

 symbol denotes wet location tolerable

RECESSED

5" HOUSINGS



PS5

75 watt
 Depth 8"
 Length 10"
 Width 6"
 Ceiling Open 6"

- for new construction
- air Seal
- type-IC or non-IC
- inter-locking bar hangers with pre-positioned nails



PS5RM

75 watt
 Depth 8"
 Width 6"
 Ceiling Open 6"

- For remodel construction
- Air Seal
- Type-IC or non-IC
- Mounts to existing ceilings
- from 1/2" to 1 1/4" thick

5" TRIMS



TR238W

White Baffle

Outside Diameter 6"

Lamp	Outside Diameter 6"	
	IC	non-IC
R20	50	50
PAR20	50	50
R30	75	75



TR132W

White Open Trim

Outside Diameter 7"

Lamp	Outside Diameter 7"	
	IC	non-IC
R30	75	75
PAR30	75	75
PAR30LN	75	75



TR139W

White Surface Gimbal

Outside Diameter 7"

Lamp	Outside Diameter 7"	
	IC	non-IC
PAR30	50	75



TR221W

White Eyeball

Outside Diameter 7"

Lamp	Outside Diameter 7"	
	IC	non-IC
R20	50	50
PAR20	50	50

RECESSED

4" HOUSINGS



PS4

55 watt
 Depth 6"
 Length 8"
 Width 6"
 Ceiling Open 5"

- for new construction
- non-IC
- inter-locking bar hangers with pre-positioned nails



PS4RM

55 watt
 Depth 6"
 Width 5"
 Ceiling Open 5"

- For remodel construction
- Non-IC
- Mounts to existing ceilings from 1/2" to 1 1/4" thick

4" TRIMS



TR401W

White Step Baffle (shown)

Outside Diameter 5"

Lamp	non-IC Max. Watt
R20	50
PAR20	50
PAR16	55



TR401

Black Step Baffle

Outside Diameter 5"

Lamp	non-IC Max. Watt
R20	50
PAR20	50
PAR16	55



TR408

White Eyeball

Outside Diameter 5"

Lamp	non-IC Max. Watt
R20	50
PAR20	50
PAR16	55

HOUSING AND TRIM KITS FOR NON-INSULATED CEILINGS



DY6408

White open trim
 75W R30 lamp
 Outside diameter 8"



DY64098

White baffle trim
 50W R20 lamp
 Outside diameter 6"



DY6410

White eyeball trim
 50W R20 lamp
 Outside diameter 8"

5" kits include housing and trim. (6" ceiling opening)

- for new and remodel construction
- bar hangers not included

RECESSED

MLE1100-5-30

AXEL

small recess mount retrofit in white

5"W x 2"H

9WLED, 3000K, 90CRI

550 Lumens, Dimmable

includes:

- adjustable 5" and 6" can option
- cutout 5"
- can be hardwired



MLE1101-5-30

AXEL

large recess mount retrofit in white

7"W x 2"H

15WLED, 3000K, 90CRI

850 Lumens, Dimmable

includes:

- adjustable 5" and 6" can option
- cutout 6"
- can be hardwired



MLE1200-5-30

PLANDOME

small surface mount in white

5"W x 1"H

9WLED, 3000K, 90CRI

550 Lumens, Dimmable



MLE1201-5-30

PLANDOME

small surface mount in white

7"W x 1"H

15WLED, 3000K, 90CRI

850 Lumens, Dimmable



MLE1501-5-30

PLANDOME

large surface mount in white

6"W x 1"H

15WLED, 3000K, 90CRI

850 Lumens, Dimmable



RECESSED





RECESSED

STEP LIGHTING





STEP LIGHTING

EZ STEP LED steplight **LED** **ADA**

When it comes to installation ease and personal safety, the EZ Step™ really fits the bill. This innovative LED uses 0.7 watts of energy, and can be installed into any standard single gang outlet box for an attractive lighting solution. Use it in stairways, hallways and corridors; anyplace in your home or office where an added safety or accent light may be needed. Indoor use only. ADA approved product.



EZ STEP LED Double Round steplight for indoor use only

WLE105DR32K-10-98 Brushed Aluminum

WLE105DR32K-10-30 White

WLE105DR32K-10-B Bronze

1 x 0.7W LED, 3200K (CCT)

12VDC 250mA LED Class II Electronic Driver included

surface dimensions

3"W x 4 $\frac{7}{8}$ "H x $\frac{7}{8}$ "D

STEP LIGHTING

BEACON steplight **LED** **ADA**

Whether to amplify outdoor entertainment areas or simply improve the safety and appearance of an indoor stairwell, our Beacon series LED steplights add a sleek aesthetic and inviting glow to any design space. Soothing Opal White lens. Available in Black, White, Brown and Aluminum. Uses standard outlet box. Indoor and Outdoor use.



Product Code	Fixture Dimensions	Lamp
WLE1105C30K-10-30 (White) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1105C30K-10-31 (Black) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1105C30K-10-45 (Brown) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1105C30K-10-98 (Aluminum) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable

APERTURE steplight **LED** **ADA**

Whether to amplify outdoor entertainment areas or simply improve the safety and appearance of an indoor stairwell, our Aperture series LED steplights add a sleek aesthetic and inviting glow to any design space. Attractive finely-ridged aperture with Opal White lens. Choose from Black, White, Brown, or Aluminum finishes. Uses standard outlet box. Indoor and Outdoor use.



Product Code	Fixture Dimensions	Lamp
WLE1106C30K-10-30 (White) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1106C30K-10-31 (Black) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1106C30K-10-45 (Brown) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1106C30K-10-98 (Aluminum) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable

STEP LIGHTING



STEP LIGHTING

ZONE steplight



Whether to amplify outdoor entertainment areas or simply improve the safety and appearance of an indoor stairwell, our Zone series LED steplights add an intriguing aesthetic and inviting glow to any design space. Highly unique semi-spherical profile with discreet task lens and concave, recessed LED. Available in Matte White, Aluminum, and Matte Brown. Indoor and Outdoor use.



Product Code	Fixture Dimensions	Lamp
WSL6210-10-30 (White) Single Lamp Steplight	3" W x 2" D x 3" H	2W LED, 3000K, 80 CRI 160 Lumens, Dimmable
WSL6210-10-45 (Brown) Single Lamp Steplight	3" W x 2" D x 3" H	2W LED, 3000K, 80 CRI 160 Lumens, Dimmable
WSL6210-10-98 (Aluminum) Single Lamp Steplight	3" W x 2" D x 3" H	2W LED, 3000K, 80 CRI 160 Lumens, Dimmable

OUTDOOR





OUTDOOR

TRINITY

8001EW/75

Oil Rubbed Bronze
7"W x 16"H x 9" EXT
1 light x 75W MED
• clear seeded glass



8002EH/75

Oil Rubbed Bronze
9"W x 20"H
2 lights x 60W CAND
• clear seeded glass



8002EW/75

Oil Rubbed Bronze
9"W x 22"H x 11" EXT
2 lights x 60W CAND
• clear seeded glass



8002EP/75

Oil Rubbed Bronze
9"W x 20"H
2 lights x 60W CAND
• clear seeded glass



8003EW/75

Oil Rubbed Bronze
12"W x 26"H x 14" EXT
3 lights x 60W CAND
• clear seeded glass



OUTDOOR



TRINITY

COTSWOLD

8901EW/75

Oil Rubbed Bronze
8"W x 15"H x 8" EXT
1 light x 60W MED
• clear seeded glass



8903EH/75

Oil Rubbed Bronze
13"W x 18"H
3 lights x 60W CAND
• clear beveled glass



8902EW/75

Oil Rubbed Bronze
10"W x 18"H x 9" EXT
2 lights x 60W CAND
• clear seeded glass



8903EP/75

Oil Rubbed Bronze
13"W x 18"H
3 light x 60W CAND
• clear beveled glass



8903EW/75

Oil Rubbed Bronze
13"W x 24"H x 12" EXT
3 light x 60W CAND
• clear seeded glass



OUTDOOR

PRINCE STREET

8701EW/65

Matte Black
8"W x 14"H x 11" EXT
1 light x 75W MED
• clear seeded glass



8721EH/65

Matte Black
10"W x 16"H
1 light x 75W MED
(includes 3' chain, 6' wire)
• clear seeded glass



8711EW/65

Matte Black
10"W x 16"H x 12" EXT
1 light x 75W MED
• clear seeded glass



8721EP/65

Matte Black
10"W x 20"H
1 light x 75W MED
• clear seeded glass



OUTDOOR

MENDHAM

8501EW/70

Hazelnut Bronze
8"W x 16"H x 10" EXT
1 light x 75W MED
• clear glass
• die cast aluminum



8511EH/70

Hazelnut Bronze
9"W x 16"H
1 light x 75W MED
(includes 3' chain, 6' wire)
• clear glass
• die cast aluminum



8511EW/70

Hazelnut Bronze
9"W x 19"H x 12" EXT
1 light x 75W MED
• clear glass
• die cast aluminum



8511EP/70

Hazelnut Bronze
9"W x 22"H
1 light x 75W MED
• clear glass
• die cast aluminum



8521EW/70

Hazelnut Bronze
11"W x 24"H x 15" EXT
1 light x 75W MED
• clear glass
• die cast aluminum



OUTDOOR

MENDHAM

8551EW/70



Hazelnut Bronze

8"W x 16"H x 10"EXT

1 light x 75W MED

- white translucent glass
- die cast aluminum



8561EH/70



Hazelnut Bronze

9"W x 16"H

1 light x 75W MED

{includes 3' chain, 6' wire}

- white translucent glass
- die cast aluminum



8561EW/70



Hazelnut Bronze

9"W x 19"H x 12"EXT

1 light x 75W MED

- white translucent glass
- die cast aluminum



8561EP/70



Hazelnut Bronze

9"W x 22"H

1 light x 75W MED

- white translucent glass
- die cast aluminum



8571EW/70



Hazelnut Bronze

11"W x 24"H x 15"EXT

1 light x 75W MED

- white translucent glass
- die cast aluminum



OUTDOOR



symbol denotes wet location tolerable

RIDGEWOOD

8401EW/65

Matte Textured Black
7"W x 12"H x 9" EXT
1 light x 75W MED
• clear glass



8411EH/65

Matte Textured Black
9"W x 12"H
1 light x 75W MED
(includes 3' chain, 6' wire)
• clear glass



8411EW/65

Matte Textured Black
9"W x 15"H x 11" EXT
1 light x 75W MED
• clear glass



8411EP/65

Matte Textured Black
9"W x 15"H
1 light x 75W MED
• clear glass



8421EW/65

Matte Textured Black
11"W x 18"H x 14" EXT
1 light x 75W MED
• clear glass



OUTDOOR

RIDGEWOOD

8401EW/70

Hazelnut Bronze
7"W x 12"H x 9" EXT
1 light x 75W MED
• clear glass



8411EH/70

Hazelnut Bronze
9"W x 12"H
1 light x 75W MED
{includes 3' chain, 6' wire}
• clear glass



8411EW/70

Hazelnut Bronze
9"W x 15"H x 11" EXT
1 light x 75W MED
• clear glass



8411EP/70

Hazelnut Bronze
9"W x 15"H
1 light x 75W MED
• clear glass



8421EW/70

Hazelnut Bronze
11"W x 18"H x 14" EXT
1 light x 75W MED
• clear glass



OUTDOOR

COVINGTON

SL92287

- Black
8"W x 16"H x 9"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



SL92237

- Black
7"W x 15"H x 8"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



SL92297

- Black
10"W x 18"H x 10"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



SL92257

- Black
8"W x 22"H x 9"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



PL92297

- Black
10"W x 18"H x 10"EXT
1 light x 18W GU24CFL (included)
- etched glass
 - photocell included
 - die-cast aluminum



SL92277

- Black
10"W x 24"H x 10"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



OUTDOOR

COVINGTON

SL922863

- Painted Bronze
8"W x 16"H x 9"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



SL922363

- Painted Bronze
7"W x 15"H x 8" EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



SL922963

- Painted Bronze
10"W x 18"H x 10"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



SL922563

- Painted Bronze
8"W x 22"H x 9"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



PL922963

- Painted Bronze
10"W x 18"H x 10"EXT
1 light x 18W GU24CFL (included)
- etched Glass
 - photocell included



SL922763

- Painted Bronze
10"W x 24"H x 10"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



OUTDOOR



symbol denotes wet location tolerable

COVINGTON

SL901063



- Painted Bronze
10"W x 22"H
1 light x 100W MED
- seeded glass
 - die-cast aluminum
 - post not included



SL90107



- Black
10"W x 22"H
1 light x 100W MED
- seeded glass
 - die-cast aluminum
 - post not included



SL923363



- Painted Bronze
10"W x 14"H
1 light x 100W MED
62" Overall length
{12' wire} {4' chain}
- seeded glass
 - die-cast aluminum



SL92337



- Black
10"W x 14"H
1 light x 100W MED
62" Overall length
{12' wire} {4' chain}
- seeded glass
 - die-cast aluminum



OUTDOOR



CAPE ANN

8301EW/65

Matte Textured Black
8"W x 10"H x 12"EXT
1 light x 75W MED
• clear glass



8301EH/65

Matte Textured Black
8"W x 11"H
1 light x 75W MED
(includes 3' chain, 6' wire)
• clear glass



8301EP/65

Matte Textured Black
8"W x 13"H
1 light x 75W MED
• seeded glass



SHAKER HEIGHTS

8201EW/70

Hazelnut Bronze
7"W x 10"H x 11" EXT
1 light x 75W MED
• clear seeded glass



8201EH/70

Hazelnut Bronze
7"W x 17"H
1 light x 75W MED
(includes 3' chain, 6' wire)
• clear seeded glass



8201EP/70

Hazelnut Bronze
7"W x 11"H
1 light x 75W MED
• clear seeded glass



OUTDOOR

MISSION

SL91047

- Black
6"W x 11"H x 8"EXT
1 light x 100W MED
- aluminum construction
 - cream colored glass panels



SL90077

- Black
9"W x 13"H x 11"EXT
1 light x 100W MED
- aluminum construction
 - cream colored glass panels



SL96657

- Black
6"W x 10"H
1 light x 100W MED
- aluminum construction
 - cream colored glass panels



SL90067

- Black
11"W x 20"H
3 lights x 60W CAND
- aluminum construction
 - cream colored glass panels
 - post not included



SL91067

- Black
11"W x 19"H x 14"EXT
3 lights x 60W CAND
- aluminum construction
 - cream colored glass panels



OUTDOOR



OUTDOOR

TEMPLE HILL

8101EW/65

- Matte Textured Black
10"W x 18"H x 11" EXT
1 light x 75W MED
- clear seeded glass
 - die cast aluminum



8101EH/65

- Matte Textured Black
10"W x 14"H
1 light x 75W MED
(includes 3' chain, 6' wire)
- clear seeded glass
 - die cast aluminum



8111EW/65

- Matte Textured Black
10"W x 21"H x 11" EXT
1 light x 75W MED
- clear seeded glass
 - die cast aluminum



8101EP/65

- Matte Textured Black
10"W x 18"H
1 light x 75W MED
- clear seeded glass
 - die cast aluminum



OUTDOOR

SPRING LAKE

8611EW/65

- Matte Textured Black
6"W x 15"H x 9" EXT
1 light x 75W MED
- clear beveled glass
 - die cast aluminum



8601EH/65

- Matte Textured Black
8"W x 14"H
1 light x 75W MED
{includes 3' chain, 6' wire}
- clear beveled glass
 - die cast aluminum



8601EW/65

- Matte Textured Black
8"W x 17"H x 10" EXT
1 light x 75W MED
- clear beveled glass
 - die cast aluminum



8603EW/65

- Matte Textured Black
10"W x 25"H x 10" EXT
3 light x 60W CAND
- clear beveled glass
 - die cast aluminum



8613EW/65

- Matte Textured Black
10"W x 25"H x 10" EXT
3 light x 60W CAND
- clear beveled glass
 - die cast aluminum



8603EP/65

- Matte Textured Black
10"W x 23"H
3 light x 60W CAND
- clear beveled glass
 - die cast aluminum



OUTDOOR



OUTDOOR

ASHFORD

8601EW/80

Antique Nickel
8"W x 12"H x 8" EXT
1 light x 100W MED
• clear beveled glass



8603EH/80

Antique Nickel
12"W x 21"H
3 lights x 60W CAND
(includes 3' chain, 6' wire)
• clear beveled glass



8602EW/80

Antique Nickel
10"W x 21"H x 10" EXT
2 lights x 60W CAND
• clear beveled glass



8603EP/80

Antique Nickel
13"W x 23"H
3 lights x 60W CAND
• clear beveled glass



8603EW/80

Antique Nickel
13"W x 23"H x 12" EXT
3 lights x 60W CAND
• clear beveled glass



OUTDOOR

ASHFORD

8601EW/60

Black
8"W x 12"H x 8" EXT
1 light x 100W MED
• clear beveled glass



8603EH/60

Black
12"W x 21"H
3 lights x 60W CAND
(includes 3' chain, 6' wire)
• clear beveled glass



8602EW/60

Black
10"W x 21"H x 10" EXT
2 lights x 60W CAND
• clear beveled glass



8603EP/60

Black
13"W x 23"H
3 lights x 60W CAND
• clear beveled glass



8603EW/60

Black
13"W x 23"H x 12" EXT
3 lights x 60W CAND
• clear beveled glass



OUTDOOR

ASHFORD

8601EW/75



Oil Rubbed Bronze
8"W x 12"H x 8" EXT
1 light x 100W MED
• clear beveled glass



8603EH/75



Oil Rubbed Bronze
12"W x 21"H
3 lights x 60W CAND
{includes 3' chain, 6' wire}
• clear beveled glass



8602EW/75



Oil Rubbed Bronze
10"W x 21"H x 10" EXT
2 lights x 60W CAND
• clear beveled glass



8603EP/75



Oil Rubbed Bronze
13"W x 23"H
3 lights x 60W CAND
• clear beveled glass



8603EW/75



Oil Rubbed Bronze
13"W x 23"H x 12" EXT
3 lights x 60W CAND
• clear beveled glass



OUTDOOR



symbol denotes wet location tolerable

ASHFORD

8601EW/85

Antique Brass
8"W x 12"H x 8" EXT
1 light x 100W MED
• clear beveled glass



8603EH/85

Antique Brass
12"W x 21"H
3 lights x 60W CAND
{includes 3' chain, 6' wire}
• clear beveled glass



8602EW/85

Antique Brass
10"W x 21"H x 10" EXT
2 lights x 60W CAND
• clear beveled glass



8603EP/85

Antique Brass
13"W x 23"H
3 lights x 60W CAND
• clear beveled glass



8603EW/85

Antique Brass
13"W x 23"H x 12" EXT
3 lights x 60W CAND
• clear beveled glass



OUTDOOR



OUTDOOR

HERITAGE

SL94137



Black
7"W x 14"H x 7"EXT
1 light x 60W MED
• clear beveled glass



SL94247



Black
9"W x 16"H x 9"EXT
1 light x 100W MED
• clear beveled glass



SL941378



Brushed Nickel
7"W x 14"H x 7"EXT
1 light x 60W MED
• clear beveled glass



SL942478



Brushed Nickel
9"W x 16"H x 9"EXT
1 light x 100W MED
• clear beveled glass



SL941363



Painted Bronze
7"W x 14"H x 7"EXT
1 light x 60W MED
• clear beveled glass



SL942463



Painted Bronze
9"W x 16"H x 9"EXT
1 light x 100W MED
• clear beveled glass



OUTDOOR



BRENTWOOD

SL92427

Black

7"W x 14"H x 7"EXT

1 light x 100W MED

- clear beveled glass
- may use accessory panel **DS1004** to comply with Dark Sky ordinance (order separately)



SL92437

Black

7"W x 26"H x 7"EXT

1 light x 100W MED

- clear beveled glass
- removable tail extension (7"W x 18"H)



PARK AVENUE

SL94727

Black

6"W x 18"H x 6"EXT

1 light x 100W MED

- clear beveled glass



SL94767

Black

7"W x 24"H x 7"EXT

1 light x 100W MED

- clear beveled glass



SL94717

Black

6"W x 12"H x 6"EXT

1 light x 100W MED

- clear beveled glass



SL94707

Black

7"W x 13"H x 8"EXT

1 light x 100W MED"

- clear beveled glass



OUTDOOR



symbol denotes wet location tolerable

HAWTHORNE

SL94517

- Black
8"W x 26"H x 9"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



SL945163

- Painted Bronze
8"W x 26"H x 9"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



SL94527

- Black
8"W x 14"H x 9"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



SL945263

- Painted Bronze
8"W x 14"H x 9"EXT
1 light x 100W MED
- seeded glass
 - die-cast aluminum



PL946263

- Painted Bronze
8"W x 14"H x 9" EXT
1 light x 18W GU24CFL (included)
- white art glass
 - photocell included
 - die-cast aluminum



PL94627

- Black
8"W x 14"H x 9"EXT
1 light x 18W GU24CFL (included)
- white art glass
 - photocell included
 - die-cast aluminum



OUTDOOR

HAWTHORNE

SL942263

- Painted Bronze
 6"W x 9"H x 7"EXT
 1 light x 60W MED
- clear beveled glass panels
 - die-cast aluminum



SL94237

- Black
 6"W x 10"H x 7"EXT
 1 light x 60W MED
- clear beveled glass panels
 - die-cast aluminum



SL94227

- Black
 6"W x 9"H x 7" EXT
 1 light x 60W MED
 HCO* 3"
- clear beveled glass panels
 - die-cast aluminum



PL94237

- Black
 6"W x 10"H x 7" EXT
 1 light x 13W GU24CFL (included)
 HCO* 3"
- etched glass panels
 - photocell included



SL94228

- Matte White
 6"W x 9"H x 7"EXT
 1 light x 60W MED
- clear beveled glass panels
 - die-cast aluminum



SL94238

- Matte White
 6"W x 10"H x 7"EXT
 1 light x 60W MED
- clear beveled glass panels
 - die-cast aluminum



PL948063

- Painted Bronze
 6"W x 9"H x 5"EXT
 1 light x 13W GU24CFL (included)
- etched glass
 - die-cast aluminum
 - photocell included



PL94807

- Black
 6"W x 9"H x 5"EXT
 1 light x 13W GU24CFL (included)
- etched glass
 - die-cast aluminum
 - photocell included



OUTDOOR

OURDOOR ESSENTIALS

SL94697 

Black
5"W x 8"H x 6"EXT
1 light x 60W MED
• clear beveled glass



9231EW/65 

Black
5"W x 9"H x 5"EXT
1 light x 100W MED
• clear glass



SL946963 

Painted Bronze
5"W x 8"H x 6"EXT
1 light x 60W MED
• clear beveled glass



9231EW/75 

Oil Rubbed Bronze
5"W x 9"H x 5"EXT
1 light x 100W MED
• clear glass



CE9261760 

Satin Black
6"W x 12"H x 8"EXT
1 light x 100W MED
• clear seeded glass



9231EW/80 

Brushed Nickel
5"W x 9"H x 5"EXT
1 light x 100W MED
• clear glass



OUTDOOR

OUTDOOR ESSENTIALS

SL94427

- Black
8"W x 18"H x 9"EXT
1 light x 60W MED
- injection molded plastic
 - acrylic panels



SL94407

- Black
8"W x 14"H x 9"EXT
1 light x 60W MED
- injection molded plastic
 - acrylic panels



SL94428

- Matte White
8"W x 18"H x 9"EXT
1 light x 60W MED
- injection molded plastic
 - acrylic panels



SL94408

- Matte White
8"W x 14"H x 9"EXT
1 light x 60W MED
- injection molded plastic
 - acrylic panels



9211EW/65

- Black
6"W x 9"H x 7"EXT
1 light x 60W MED
- white glass



9211EW/75

- Oil Rubbed Bronze
6"W x 9"H x 7"EXT
1 light x 60W MED
- white glass



OUTDOOR

OURDOOR ESSENTIALS

9201EW/65

Black
7"W x 7"H x 8"EXT
1 light x 60W MED
• white glass



9201EW/75

Oil Rubbed Bronze
7"W x 7"H x 8"EXT
1 light x 60W MED
• white glass



SL94357

Black
6"W x 7"H x 7"EXT
1 light x 60W MED
• injection molded plastic
• white acrylic globe



SL94358

Matte White
6"W x 7"H x 7"EXT
1 light x 60W MED
• injection molded plastic
• white acrylic globe



SL928378

Brushed Nickel
12"W x 6"H
2 lights x 60W MED
• etched alabaster style glass



OUTDOOR

OUTDOOR ESSENTIALS

SL7157

Black
5"W x 8"H x 6"EXT
1 light x 75W MED
• clear beveled glass



SL7158

Matte White
5"W x 8"H x 6"EXT
1 light x 75W MED
• clear beveled glass



SL3037

Black
5"W x 7"H
1 light x 60W MED
• clear beveled glass



SL49427

Black
12"W x 11"H x 11"EXT
2 lights x 150W BR40



SL49428

Matte White
12"W x 11"H x 11"EXT
2 lights x 150W BR40



SL494227

Painted Bronze
12"W x 11"H x 11"EXT
2 lights x 150W BR40




SL49468

Matte White
10"W x 6"H x 6"EXT
2 lights x 150W BR40



OUTDOOR



OUTDOOR

OUTDOOR ESSENTIALS

CE931171 

BELLA
Oil Rubbed Bronze
6"W x 11"H x 4"EXT
1 light x 60W MED
• white acrylic diffuser



CE932171 

BELLA
Oil Rubbed Bronze
6"W x 18"H x 4"EXT
2 lights x 60W MED
• white acrylic diffuser



CE930171 

BELLA
Oil Rubbed Bronze
9"W x 10"H x 14"EXT
1 light x 60W MED
• white glass



SL92707 

Black
5"W x 12"H x 8"
1 light x 50W R20
• provides 100% light cut-off
• suitable for coastal regions with light restrictions for turtle nesting areas



SL92708 

Matte White
5"W x 12"H x 8"
1 light x 50W R20
• provides 100% light cut-off
• suitable for coastal regions with light restrictions for turtle nesting areas



Endorsed by Florida Fish & Wildlife for the preservation of turtle nesting areas



Endorsed by Florida Fish & Wildlife for the preservation of turtle nesting areas

OUTDOOR



symbol denotes wet location tolerable



symbol denotes damp location tolerable

thomaslighting.com • 888-202-9605 313

OURDOOR ESSENTIALS

CE9202310



- Oil Rubbed Bronze
10"W x 7"H
2 light x 60W MED
• clear glass



CE9202365



- Satin Nickel
10"W x 7"H
2 light x 60W MED
• clear glass



SL7457



- Black
11"W x 5"H
1 light x 100W MED
• frosted glass
• die-cast aluminum



SL7458



- Matte White
11"W x 5"H
1 light x 100W MED
• etched glass
• die-cast aluminum



SL7577



- Black
8"W x 5"H
1 light x 60W MED
• white plastic diffuser
• injection molded plastic



SL7578



- Matte White
8"W x 5"H
1 light x 60W MED
• white plastic diffuser
• injection molded plastic



SL7597



- Black
10"W x 5"H
2 lights x 60W MED
• white plastic diffuser
• injection molded plastic



SL7598



- Matte White
10"W x 5"H
2 lights x 60W MED
• white plastic diffuser
• injection molded plastic



OUTDOOR



OUTDOOR ESSENTIALS

9102EF/65



Matte Textured Black
8"W x 4"H
2 light x 60W MED
• clear seeded glass



9102EF/40



White
8"W x 4"H
2 light x 60W MED
• clear seeded glass



9002EF/65



Matte Textured Black
10"W x 6"H
2 light x 60W MED
• clear seeded glass



9002EF/40



White
10"W x 6"H
2 light x 60W MED
• clear seeded glass



9102EF/70



Hazelnut Bronze
8"W x 4"H
2 light x 60W MED
• clear seeded glass



9102EF/80



Antique Nickel
8"W x 4"H
2 light x 60W MED
• clear seeded glass



9002EF/70



Hazelnut Bronze
10"W x 6"H
2 light x 60W MED
• clear seeded glass



9002EF/80



Antique Nickel
10"W x 6"H
2 light x 60W MED
• clear seeded glass



OUTDOOR



symbol denotes wet location tolerable

OURDOOR ESSENTIALS

7153EP/73



Charcoal
26"W x 91"H
3 lights x 100W MED
• clear seeded glass



45100CHRC



Charcoal
10"W x 73"H



4501CHRC



Charcoal
14"W x 7"H



45102CHRC



Charcoal
3"W x 4"H



1000-C



Charcoal
6"W x 5"H



OUTDOOR

OUTDOOR ACCESSORIES

SL9118

Black
3"W x 84"H
• outdoor post



43001HB

Hazelnut Bronze
3"W x 84"H
• outdoor post



43001WC

Weathered Charcoal
3"W x 84"H
• outdoor post



43003AGB

Aged Bronze
6"W x 3"H
• outdoor post mount



43003CB

Clay Bronze
8"W x 5"H
• outdoor post mount



43003GH

Graphite
6"W x 3"H
• outdoor post mount



43003HB

Hazelnut Bronze
6"W x 3"H
• outdoor post mount



43003WC

Weathered Charcoal
8"W x 5"H
• outdoor post mount



OUTDOOR



symbol denotes wet location tolerable

LED BULBS

Energy saving dimmable filament bulbs offered in a range of sizes and styles. Low power consumption G9 LED bulb also available.



1110 **LED**
4W LED Med.
400 Lumens, 2700K, 80 CRI
2½"W x 5¾"H



1111 **LED**
3W LED Med.
260 Lumens, 2700K, 80 CRI
1¾"W x 4¼"H



1112 **LED**
6W LED Cand.
530 Lumens, 2700K, 80 CRI
1½"W x 4¼"H



1113 **LED**
7W LED G9
430 Lumens, 3000K, 80 CRI
1½"W x 3"H

VINTAGE FILAMENT BULBS

These dimmable nostalgic light bulbs will enhance the look of any fixture especially those with visible bulbs.



1101
40W Cand.
1"W x 3½"H



1102
60W Med.
1¾"W x 4¼"H



1092
60W Med.
2½"W x 5"H



1099
60W Med.
1¼"W x 7"H



1103
60W Med.
1¼"W x 12"H

BULB TYPES

INDEX

ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE
1092	318	190060217	58, 138	1103BB/20	113, 230	1301PS/20	108, 141	2003FM/10	70, 71, 162
1099	318	190060719	60, 138	1103CH/20	112	1301WS/20	109, 181, 228	2005CH/10	70, 71
1101	318	190061217	58, 125	1103FM/20	75, 112	1302BB/20	109, 228	2009CH/10	70
1102	318	190061719	60, 125	1103FM/20	161	1303BB/20	109, 228	2101PS/10	39, 137
1103	318	190067117	86, 128, 158	1103PL/20	112, 134	1303CH/20	108	2101PS/20	36, 137
1110	318	190067763	88, 128, 158	1104BB/20	113, 230	1303FM/20	108, 160	2101WS/10	39, 172, 174
1111	318	190071217	59, 160	1105CH/20	112	1304BB/20	109, 228	2101WS/20	36, 37, 174
1112	318	190071719	61, 161	1151PS/10	116, 143	1305CH/20	108	2103CH/10	38, 39
1113	318	190109704	106	1151WS/20	117, 181, 231	1351PL/10	110, 133	2103CH/20	36, 37
190005117	86	190110704	106	1152BB/20	117, 231	1351PS/10	110, 141	2103FM/10	39, 161
190005763	88	190111704	107, 141	1152CS/10	116, 134, 159	1351WS/10	111, 181, 229	2103FM/10	161
190006117	86	190112704	106	1153BB/20	117, 231	1352BB/10	111, 229	2103FM/20	36, 161
190006763	88	190113704	106, 159	1153CH/10	114, 116	1353BB/10	111, 229	2103SF/10	39, 155
190016117	87, 201	190114704	107, 215	1153FM/10	77, 114, 116	1353CH/10	110	2103SF/20	36, 155
190016763	89, 201	190115704	107, 215	1153PL/10	116, 134, 135	1353FM/10	110, 160	2105CH/10	39
190017117	201, 211	190116704	107, 215	1154BB/20	117, 231	1354BB/10	111, 229	2105CH/20	36
190017763	89, 201	1000-C	316	1155CH/10	114, 116	1355CH/10	110	2109CH/10	39
190018117	87, 201	1001PS/20	74, 138	1201PL/20	90, 130	1501WS/10	23, 177	2109CH/20	36
190018763	89, 201	1001WS/20	75, 175, 220	1201PS/20	90, 140	1501WS/20	19, 177	2115CH/10	39
190022217	59, 212	1002BB/20	75, 220	1201WS/20	91, 180	1502WS/10	23, 177	2115CH/20	36, 37
190022719	61, 213	1002CS/20	75, 127, 157	1201WS/20	222	1502WS/20	19, 177	2201BB/10	45, 189
190023217	59, 178, 212	1003BB/20	75, 220	1202BB/20	91, 222	1503CH/10	20	2201PS/10	45, 46, 137
190023719	61, 178, 213	1003CH/20	74	1202CS/20	90, 130, 131, 158	1505CH/10	20	2201WS/10	45, 177, 189
190024217	59, 212	1003IS/20	74	1202CS/20	130, 131, 158	1509CH/10	20	2203BB/10	45, 189
190024719	61, 210, 213	1003PL/20	74, 127	1203BB/20	91, 222	1513CH/10	23	2203CH/10	44
190025217	59, 212	1004BB/20	75, 220	1203CH/20	90	1513CH/20	19	2203CS/10	45, 124
190025719	61, 213	1005CH/20	74	1203PL/20	90, 130	1515CH/10	23	2203CS/10	155
190033217	163	1009CH/20	74	1204BB/20	91, 222	1515CH/20	19	2203PL/10	44, 124
190033715	163	1051PS/10	76, 138	1205CH/20	90	1523CH/10	21	2204BB/10	45, 189
190034217	165	1051WS/10	77, 175, 221	1221PL/10	92, 130	1523CH/20	19	2205H/10	44
190035217	165	1052BB/10	77, 221	1251PS/10	92, 140	1525CH/10	21	2209CH/10	44
190036117	86	1052CS/10	77, 127, 157	1251WS/10	92	1525CH/20	18	2401PL/10	49, 125
190036763	88	1053BB/10	77, 221	1251WS/20	180, 223	1529CH/10	21	2401PL/20	47, 48, 125
190040217	57-58	1053CH/10	76	1252BB/10	92	1529CH/20	18	2402SF/10	49, 156
190040719	60	1053FM/10	161	1252BB/20	223	1533CH/10	23	2402SF/20	48, 156
190041217	58	1053IS/10	76	1252CS/10	92, 130	1533CH/20	18	2451WS/10	49, 178
190041719	60	1053PL/10	76, 127	1252CS/10	158	1903CH/10	73	2451WS/20	48, 178
190042217	58	1054BB/10	77, 221	1253BB/10	92	1903CH/20	73	2453CH/10	49
190042719	60	1055CH/10	76	1253BB/20	223	1905CH/10	73	2453CH/20	48
190043217	58, 125, 156	1059CH/10	76	1253CH/10	92	1905CH/20	72, 73	2455CH/10	49
190043719	60, 125, 156	1101PS/20	112, 143	1253PL/10	92, 130	1913CH/10	24	2455CH/20	48
190056117	86, 140	1101WS/20	181, 230	1254BB/10	92	1913CH/20	24	43001HB	317
190056763	88, 140	1101WS/20	113	1254BB/20	223	1915CH/10	24	43001WC	317
190058117	86, 128	1102BB/20	113, 230	1255CH/10	92	1915CH/20	24	43003AGB	317
190058763	88, 128	1102CS/20	112, 134, 159	1301PL/20	108, 133	2003CH/10	70, 71	43003CB	317

INDEX

ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE
43003GH	317	7003FM/40	165	8101EW/65	296	8603EP/80	299	CL781034	167, 183
43003HB	317	7013FM/20	165	8111EW/65	296	8603EP/85	302	CL781131	167, 183
43003WC	317	7013FM/40	165	8201EH/70	293	8603EW/60	300	CL781134	167, 183
4501CHRC	316	7021FM/10	166	8201EP/70	293	8603EW/65	297	CL781231	167, 183
45100CHRC	316	7021FM/20	166	8201EW/70	293	8603EW/75	301	CL781234	167, 183
45102CHRC	316	7021FM/40	166	8301EH/65	293	8603EW/80	299	CL782011	168
5102WS/20	182	7023FM/10	165	8301EP/65	293	8603EW/85	302	CL782012	168
5111WS/20	183	7052FM/10	165	8301EW/65	293	8611EW/65	297	CL782021	168
5121WS/20	183	7053FM/10	165	8401EW/65	288	8613EW/65	297	CL782022	168
5131WS/20	183	7153EP/73	316	8401EW/70	289	8701EW/65	285	CL782031	168
5151WS/10	184, 185	7301FM/10	165	8411EH/65	288	8711EW/65	285	CL782032	168
5151WS/20	185	7301FM/20	165	8411EH/70	289	8721EH/65	285	CL783004	166
5161WS/20	183	7302FM/10	165	8411EP/65	288	8721EP/65	285	CL783014	166
5171WS/20	185	7302FM/20	164, 165	8411EP/70	289	8901EW/75	284	CL783024	166
5181WS/20	182	7303FM/10	165	8411EW/65	288	8902EW/75	284	CN110171	25, 176, 177
5302WS/10	182	7303FM/20	165	8411EW/70	289	8903EH/75	284	CN110321	25
5371WS/10	185	7351FM/40	165	8421EW/65	288	8903EP/75	284	CN110521	25
5381WS/10	182	7352FM/40	165	8421EW/70	289	8903EW/75	284	CN110821	25
5501BB/20	240	7661PS/10	142, 143	8501EW/70	286	9002EF/40	315	CN120041	10, 122
5501BB/30	242	7661PS/20	143	8511EH/70	286	9002EF/65	315	CN120121	11, 174
5502BB/20	240	7672FM/10	162	8511EP/70	286	9002EF/70	315	CN120121	191
5502BB/30	242	7672FM/20	162	8511EW/70	286	9002EF/80	315	CN120151	10, 136
5503BB/20	240	7681PL/10	122	8521EW/70	286	9102EF/40	315	CN120211	11, 191
5503BB/30	242	7681PL/20	122	8551EW/70	287	9102EF/65	315	CN120231	10, 160
5504BB/20	240	7683FM/10	162	8561EH/70	287	9102EF/70	315	CN120281	10, 123, 154
5504BB/30	242	7683FM/20	162	8561EP/70	287	9102EF/80	315	CN120311	11, 191
5551BB/10	241	7691PL/10	122	8561EW/70	287	9201EW/65	310	CN120321	10
5552BB/10	241	7691PL/20	122	8571EW/70	287	9201EW/75	310	CN120411	11, 191
5553BB/10	241	7693FM/10	162	8601EH/65	297	9211EW/65	309	CN120521	10
5554BB/10	241	7693FM/20	162	8601EW/60	300	9211EW/75	309	CN120821	10
5601BB/20	244	7703FY/20	151	8601EW/65	297	9231EW/65	308	CN129041	8, 118, 122
5601BB/30	243	7704FY/10	148	8601EW/75	301	9231EW/75	308	CN129121	9, 174
5602BB/20	244	7704FY/20	148	8601EW/80	299	9231EW/80	308	CN129121	190
5602BB/30	243	7706FY/20	151	8601EW/85	302	ACL12-N-30	257	CN129151	8, 136
5603BB/20	244	7713FY/10	149	8602EW/60	300	ACL18-N-30	257	CN129211	9, 190
5603BB/30	243	7713FY/20	149	8602EW/75	301	ACL24-N-30	257	CN129231	8, 160
5604BB/20	244	7723FY/10	151	8602EW/80	299	ACL36-N-30	257	CN129281	8, 123, 154
5604BB/30	243	7726FY/10	150, 151	8602EW/85	302	ACLJB-N-30	257	CN129311	9, 190
5651BB/10	245	8001EW75	282	8603EH/60	300	CE9202310	314	CN129321	8
5652BB/10	245	8002EH/75	282, 283	8603EH/75	301	CE9202365	314	CN129411	9, 190
5653BB/10	245	8002EP/75	282	8603EH/80	299	CE9261760	308	CN129521	8
5654BB/10	245	8002EW/75	282	8603EH/85	302	CE930171	313	CN129821	8
7002FM/20	165	8003EW/75	282	8603EP/60	300	CE931171	313	CN15711	20, 123
7002FM/40	165	8101EH/65	296	8603EP/65	297	CE932171	313	CN15712	18, 123
7003FM/20	165	8101EP/65	296	8603EP/75	301	CL781031	167, 183	CN15751	20

INDEX

INDEX

ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE
CN15752	18	CN230237	16, 160	CN579171	175, 205	FWN217EB	170	MLE316-5-30K	254
CN15831	21, 123	CN230317	17, 194	CN579172	175, 204	FWN232EB	170	MLE316-5-31K	254
CN15832	19, 123	CN230327	16	CN579211	205	FWN432EB	170	MLE401-5-16M	256
CN15861	21	CN230387	16, 155	CN579212	204	HZ009RSF	251	MLE401-5-30	256
CN15862	19	CN230417	17, 194	CN579311	205	HZ017RSF	251	MLE401-5-31	256
CN160151	6, 136	CN230527	16	CN579312	204	HZ026RSF	251	MLE423-5-16MK	255
CN160171	7, 174, 188	CN230927	16	CN579411	205	HZ035RSF	251	MLE423-5-30K	255
CN160211	7, 188	CN250151	22, 123	CN579412	204	HZ048RSF	251	MLE423-5-31K	255
CN160231	6, 160	CN250341	22	CN600361	159	HZ109RSF	251	MLE426-5-16MK	256
CN160311	7, 188	CN250541	22	CN600362	159	HZ117RSF	251	MLE426-5-30K	256
CN160321	6	CN250641	22	CN734299	166	HZ126RSF	251	MLE426-5-31K	256
CN160381	6, 122	CN251551	22, 123	CN734399	166	HZ135RSF	251	MLE433-5-16MK	255
CN160381	154	CN251641	22	CN770141	120	HZ148RSF	251	MLE433-5-30K	255
CN160411	7, 186, 188	CN570171	181, 225	CN770144	120	HZ309RSF	251	MLE433-5-31K	255
CN160521	6	CN570172	181, 224	CN770148	120	HZ317RSF	251	PL922963	291
CN160821	6	CN570211	225	DY6408	271	HZ326RSF	251	PL92297	290
CN170151	14, 136	CN570212	224	DY64098	271	HZ335RSF	251	PL94237	307
CN170152	12, 136	CN570311	225	DY6410	271	HZ348RSF	251	PL946263	306
CN170171	15, 174, 193	CN570312	224	FCN231BEB	171	LC411-PW-15	120, 121	PL94627	306
CN170172	13, 174, 192	CN570411	225	FCN232EB	171	LC413-10-80	143	PL948063	307
CN170211	15, 193	CN570412	224	FCN432EB	171	LV012RSF	250	PL94807	307
CN170212	13, 192	CN573171	181, 216	FML2000-10-16M	167	LV018RSF	250	PS1	266
CN170311	15, 193	CN573172	181, 217	FML2020-10-16M	167	LV024RSF	250	PS1CP	266
CN170312	13, 192	CN573211	216	FML2030-10-16M	167	LV032RSF	250	PS1NSP	266
CN170321	14	CN573212	217	FML4025-10-16M	167	M209778	50, 51	PS1NSPOC	266
CN170322	12	CN573311	216	FML4050-10-16M	167	M251878	50, 137	PS1RM	267
CN170331	14, 160	CN573312	217	FML4075-10-16M	167	M255078	94, 129	PS4	271
CN170332	12, 160	CN573411	216	FML4225-10-16M	167	M261678	50	PS4RM	271
CN170341	14	CN573412	217	FML4250-10-16M	167	M271878	50, 163	PS5	270
CN170342	12	CN575171	175, 207	FML4525-10-15	168	MLE1100-5-30	272, 273	PS5RM	270
CN170381	14, 154	CN575172	175, 206	FML4550-10-15	168, 169	MLE1101-5-30	272	PS9	267
CN170382	12, 152, 154	CN575211	207	FML4725-10-15	167	MLE1200-5-30	168, 272	SL1217EB	171
CN170411	15, 193	CN575212	206	FML4750-10-15	167	MLE1201-5-30	168, 272	SL123	166
CN170412	13, 192	CN575311	207	FML4925-10-15	167	MLE1500-5-30	168	SL3037	311
CN170521	14	CN575312	206	FML4950-10-15	167	MLE1501-5-30	272	SL3258	165
CN170522	12	CN575411	207	FML5125-AC-30	168	MLE201-5-16M	254	SL3268	165
CN170921	14	CN575412	206	FML5150-AC-31	168	MLE201-5-30	254	SL3288	165
CN170922	12	CN578171	178, 203	FML5175-AC-32	168	MLE201-5-31	254	SL494227	311
CN200141	120	CN578172	178, 179, 202	FML6125-AC-30	168	MLE301-5-16M	253	SL49427	311
CN200142	120	CN578211	203	FML6150-AC-30	168	MLE301-5-30	253	SL49428	311
CN200151	120	CN578212	202	FML6175-AC-30	168	MLE301-5-31	253	SL49468	311
CN200152	120	CN578311	203	FML7125-10-16M	167	MLE313-5-16MK	253	SL705378	167
CN230157	16, 136	CN578312	202	FML7150-10-16M	167	MLE313-5-30K	253	SL706178	246
CN230177	17, 174, 194, 195	CN578411	203	FML7175-10-16M	167	MLE313-5-31K	253	SL710323	239
CN230217	17, 194	CN578412	202	FML801-PW-15	154	MLE316-5-16MK	254	SL710341	95, 239

INDEX

ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE
SL710441	95, 239	SL748278	31, 196	SL805215	68	SL842078	30, 155	SL869378	163
SL714215	69, 227	SL748322	35, 197	SL805278	66	SL843678	166	SL869663	80, 157
SL714278	67, 226	SL748378	31, 196	SL806615	54, 56, 125	SL84368	166	SL869678	78, 157
SL714315	69, 227	SL748422	35, 197	SL806678	52, 125	SL84408	162	SL876278	162
SL714378	67, 226	SL748478	31, 196	SL806715	54	SL845578	165	SL877263	29, 34, 161
SL714415	69, 227	SL748522	35, 197	SL806778	52	SL845678	165	SL878115	163
SL714478	67, 226	SL748578	31, 196	SL806815	54	SL847978	94, 149	SL878178	163
SL714515	69, 227	SL748622	35, 197	SL806878	52	SL853122	185	SL878215	55, 69, 163
SL714578	67, 226	SL748678	31, 196	SL806915	54	SL853163	185	SL878223	162
SL715315	55, 209	SL7577	314	SL806978	52	SL853178	185	SL878278	53, 67, 95, 163
SL715378	53, 208	SL7578	314	SL808122	42	SL854122	33, 177, 197	SL878378	163
SL715415	55, 209	SL758178	236	SL808172	40	SL854178	32, 177, 196	SL880141	26
SL715478	53, 208	SL75824	237	SL808222	42	SL85834	237	SL880162	28
SL7157	311	SL758263	65, 81, 238	SL808272	40	SL860715	68, 127, 157	SL880241	26
SL7158	311	SL758278	63, 79, 239	SL808322	42	SL860778	66, 127, 157	SL880262	28
SL716578	246	SL758363	65, 81, 238	SL808372	40	SL860915	54, 156	SL880341	26
SL716778	246	SL758378	63, 79, 236	SL811363	84	SL860978	52, 156	SL880362	28
SL717222	43, 199	SL75844	237	SL811378	82	SL861078	95, 129, 158	SL881163	80
SL717272	41, 198	SL758463	65, 81, 238	SL811563	84	SL861463	64, 126	SL881178	78
SL717322	43, 199	SL758478	63, 79, 236	SL811578	82	SL861463	156	SL881263	80
SL717372	41, 198	SL75854	237	SL820063	84	SL861478	62, 126, 156	SL881278	78
SL717422	43, 199	SL758563	65, 81, 238	SL820078	82	SL861522	43, 161	SL881363	80
SL717472	41, 198	SL758578	63, 79, 236	SL820663	80, 140	SL861572	41, 161	SL881378	78
SL717522	43, 199	SL75864	237	SL820678	78, 140	SL861622	42, 155	SL891015	54, 138, 139
SL717572	41, 198	SL758663	65, 81, 238	SL823463	64, 126	SL861672	40, 155	SL891078	52, 138
SL73244	246	SL758678	63, 79, 236	SL823478	62, 126	SL863322	34	SL891515	68, 138
SL74024	246	SL7597	314	SL823578	94, 129	SL863378	30	SL891578	66, 138
SL74134	246	SL7598	314	SL823663	64, 126	SL863622	34	SL891615	68, 126
SL741578	246	SL760241	27, 200	SL823678	62, 126	SL863678	30	SL891678	66, 126
SL74184	246	SL760262	29, 200	SL824641	26, 124	SL863922	34	SL891715	68, 127
SL742578	246, 247	SL760341	27, 200	SL824662	28, 124	SL863978	30	SL891778	66, 127
SL744163	235	SL760362	29, 200	SL825363	84, 128, 157	SL866241	26, 154	SL891815	68, 147
SL744178	234	SL760441	27, 200	SL825378	82, 128, 157	SL866262	28, 154	SL891878	66, 147
SL744263	85, 235	SL760462	29, 200	SL825641	26, 136	SL868178	162	SL893422	42, 137
SL744278	83, 234	SL800378	94	SL825662	28, 136	SL868218	162	SL893472	40, 137
SL744363	85, 235	SL801078	94	SL826663	80, 128	SL868263	162	SL893522	42, 124
SL744378	83, 234	SL801178	94	SL826678	78, 128	SL868278	162	SL893572	40, 124
SL744463	85, 235	SL801463	64	SL829163	84, 140	SL869163	163	SL893622	42, 144, 146
SL744478	83, 234	SL801478	62	SL829178	82, 140	SL869178	163	SL893672	40, 146
SL744563	85, 235	SL801563	64	SL829222	34, 124	SL869218	161	SL90067	294
SL744578	83, 234	SL801578	62	SL829278	30, 124	SL869222	163	SL90077	294
SL7457	314	SL801663	64	SL829663	137	SL869263	65, 80, 84, 89, 163	SL901063	292
SL7458	314	SL801678	62	SL829678	30, 137	SL869278	27, 30, 63,	SL90107	292
SL746078	183	SL805115	68	SL829822	34, 137		78, 82, 87, 163	SL91047	294
SL748222	35, 197	SL805178	66	SL842022	34, 155	SL869363	163, 165	SL91067	294

INDEX

INDEX

ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE	ITEM NUMBER	PAGE
SL9118	317	SS03IS/10	44	TK0019704	102	TV0009117	105, 214	ZL317RSF	252
SL922363	291	TC0007117	104, 130	TK0020217	100	TV0010117	105, 214	ZL326RSF	252
SL92237	290	TC0007704	106, 130	TK0020704	102	TV0015704	99, 233	ZL335RSF	252
SL922563	291	TC0008117	105, 141	TK0021217	100	TV0015741	97, 232	ZL348RSF	252
SL92257	290	TC0009117	104	TK0021704	102	TV0016704	99, 233	ZS-CLIP90-N-15	260
SL922763	291	TC0014704	99, 141	TK0022217	32	TV0016741	97, 232	ZS-CLIPADI-N-15	260
SL92277	290	TC0014741	97, 141	TK0022722	33	TV0017704	99, 233	ZS306RSF	261
SL922863	291	TC0015704	98, 158	TK0023217	32	TV0017741	97, 232	ZS310RSF	261
SL92287	290	TC0015741	96, 158	TK0023722	33	TV0018704	99, 233	ZS312RSF	261
SL922963	291	TC0016704	98, 129	TN0003217	67, 175, 226	TV0018741	97, 232	ZS406RSF	261
SL92297	290	TC0016741	96, 129	TN0003715	69, 175	TV0019217	101, 218	ZS410RSF	261
SL923363	292	TC0017704	98, 148	TN0005217	53, 178, 208	TV0019704	103, 219	ZS412RSF	261
SL92337	292	TC0017741	96, 148	TN0005715	55, 178, 209	TV0020217	101, 218	ZS606RSF	261
SL92427	305	TC0018704	98, 129	TN0007117	105, 180, 214	TV0020704	103, 219	ZS610RSF	261
SL92437	305	TC0018741	96, 129	TN0007704	107, 180, 215	TV0021217	101, 218	ZS612RSF	261
SL92707	313	TC0019217	141	TN0009704	99, 180, 233	TV0021704	103, 219	ZSBOX-N-30	260
SL92708	313	TC0019217	100	TN0009741	97, 180, 232	TV0022217	101, 218	ZSBUTT-N-30	260
SL928378	163, 310	TC0019704	102, 141	TN0010217	101, 180, 218	TV0022704	103, 219	ZSCON12-N-30	260
SL941363	304	TC0020217	100, 159	TN0010704	103, 180, 219	UCX2008	252	ZSCON24-N-30	260
SL94137	304	TC0020704	102, 159	TN003715	227	UCX3008	252	ZSL-N-98	260
SL941378	304	TC0021217	100, 133	TR132W	270	WLE105DR32K-10-30	276	ZSPLUG-N-30	260
SL942263	307	TC0021704	102, 133	TR139W	270	WLE105DR32K-10-98	276	ZSR-N-98	260
SL94227	307	TC0022217	100, 133	TR18BN	269	WLE105DR32K-10-B	276	ZST-N-98	260
SL94237	307	TC0022704	102, 132, 133	TR18W	269	WLE1105C30K-10-30	277		
SL94238	307	TC0023217	32, 146	TR221W	270	WLE1105C30K-10-31	277		
SL942463	304	TC0023722	33, 146	TR238W	270	WLE1105C30K-10-45	277		
SL94247	304	TG0002117	104, 159	TR30BN	268	WLE1105C30K-10-98	277		
SL942478	304	THS30CLR	268	TR30W	268	WLE1106C30K-10-30	277		
SL94357	310	TK0003217	66	TR401	271	WLE1106C30K-10-31	277		
SL94358	310	TK0003715	68	TR401W	271	WLE1106C30K-10-45	277		
SL94407	309	TK0008217	52	TR408	271	WLE1106C30K-10-98	277		
SL94408	309	TK0008715	54	TR40W	268	WS1330-10-15	183		
SL94427	309	TK0009117	104	TR6SHR	269	WSL1601-PW-15	182		
SL94428	307, 309	TK0009704	106	TRB30	268	WSL40-5-15	182		
SL945163	306	TK0010117	104	TRB30W	268	WSL6210-10-30	278, 279		
SL94517	306	TK0011117	104	TRM30	268	WSL6210-10-45	279		
SL945263	306	TK0012117	104	TRM30W	268	WSL6210-10-98	279		
SL94527	306	TK0012704	106	TRS30W	268	WSL820-10-16M	182		
SL946963	308	TK0016704	98	TSH12	269	WSL825-10-15M	182		
SL94697	308	TK0016741	96	TSH12IC	269	ZL009RSF	252		
SL94707	305	TK0017704	98	TSH16	269	ZL017RSF	252		
SL94717	305	TK0017741	96	TSH16IC	269	ZL026RSF	252		
SL94727	305	TK0018704	98	TV0007217	53, 208	ZL035RSF	252		
SL94767	305	TK0018741	96	TV0007715	55, 209	ZL048RSF	252		
SL96657	294	TK0019217	100	TV0008117	105, 214	ZL309RSF	252		



ELK
LIGHTING CREATIVITY
elklighting.com

LIGHTING FIXTURES

Lighting fixtures for discerning customers that inspire creativity and reflect a commitment to quality, innovation and style.



DIMOND LIGHTING
dimondlighting.com

PORTABLE TABLE AND FLOOR LAMPS


Inspired by poetry of light and acclaimed for the elegance with which they are executed, Dimond table and floor lamps transcend the boundaries of innovations and style.



DIMOND HOME
dimond-home.com

A PURE CELEBRATION OF STYLE

Discover the beauty of nature and the elegance of modern design. Extraordinary design and superior craftsmanship create an enchanting collection of home accessories.



Sterling
mysterlinghome.com

ACCENT FURNITURE, WALL DECOR & ACCESSORIES


Distinctive, innovative & design-driven home furnishings and accessories that uncover styles of the future, while revitalizing themes from the past.



SW
steinworld.com

ACCENT FURNITURE, WALL DECOR & ACCESSORIES


Established in 1985, Stein World has a rich history as one of the leading pioneers in the furniture industry offering the finest handpainted products from around the world that are inspired by consumer lifestyles, fashion trends and interior design directions.



GUILD MASTER
guildmaster.com

HANDMADE FURNITURE

For over 30 years, the GuildMaster brand has represented the finest in handmade accent furniture. Crafted in solid mahogany using Old World techniques, each piece is truly one of a kind.



POMEROY

pomeroycollection.com

DECORATIVE ACCESSORIES

Great design born of a natural curiosity and playfulness, combined with the discipline of relentless exploration and focus, Pomero is beautiful home accessory products with distinction and functionality.



themirrormasters.com

DECORATIVE MIRRORS

Every mirror is designed with the belief that each one is a piece of art. Each one has the ability to illuminate a room, create ambience and make a powerful statement in a space. Each one is executed with the expectation that it will give a lifetime of character.



ryvyr.com

KITCHEN AND BATH

A unique product offering for kitchen and bath in sophisticated transitional, elegant traditional and modern European designs with form and function.



elkhospitality.com

HOSPITALITY INDUSTRY

ELK Hospitality offers a full range of styles across multiple product categories including lighting fixtures, lamps, furniture, wall décor and decorative accessories.



thomaslighting.com

CONTRACT LIGHTING

A compact, yet versatile and stylish range of lighting designed with the builder and specifier in mind that allows mix and match capabilities across collections.



FOR TOTAL HOME SOLUTIONS



THOMASLIGHTING.COM



12 WILLOW LANE
NESQUEHONING, PA 18240-1228
P: 888-202-0605 • F: 866-613-3264
E: SALES@THOMASLIGHTING.COM

FOR TOTAL HOME SOLUTIONS, VISIT OUR OTHER HOME FURNISHING BRANDS



ELKLIGHTING.COM



DIMONDLIGHTING.COM



LAMPWORKS.COM



DIMOND-HOME.COM



MYSTERLINGHOME.COM



GUILDMASTER.COM



STEINWORLD.COM



POMEROYCOLLECTION.COM



THEMIRRORMASTERS.COM



ELKHOSPITALITY.COM

PERMANENT SHOWROOMS

ATLANTA America's Mart, Building 1-Suites 6D2 & 6E1 | Building 2-Suite 1801
DALLAS Trade Mart, Suites 3309, 3606 & 3664 | World Trade Center, Suites 236, 509, 531 & 539
HIGH POINT IHFC Building, Suites C-402, W-477 | Commerce & Design Building, Suite 1A
LAS VEGAS World Market Center, Building A Suites 344, 346, & 416 | Building C, Suite 696
NEW YORK 12 West 32nd Street, 11th Floor
MISSISSIPPI Tupelo Complex, Building 6, Suite 6018 | TORONTO | HONG KONG